

## Straps for Nonmetallic-Sheathed and Underground Feeder Cable (Continued)



3/4" straps also available in gray or orange

CAT. NO.	MAXIMUM CABLE SIZE	COLOR	PACKAGE AND QUANTITY	STD. CARTON QUANTITY	APPROX. SHIPPING WT. PER CARTON
<b>3/4" STRAP FOR 2 WIRE NM AND UF CABLE UP TO NO. 8, 3 WIRE UF CABLE UP TO NO. 12, AND OTHER CABLE UP TO .750" WIDE</b>					
RA-1455P	3/4"	White	Reclosable Plastic Bag of 100	1000	5 lbs.
RA-1555	3/4"	White	Box of 100	1000	6 lbs.
RA-1560	3/4"	White	Bulk	5000	25 lbs.
RA-1562	3/4"	White	Plastic Pail of 1500	1500	8 lbs.
RA-1566 or RA-1566UV	3/4"	White Black	Kraft Bag of 250	5000	25 lbs.

### STRAPS FOR 3 AND 4 WIRE NM CABLE

RA-1610R	For 14/3, 12/3, and 14/4 NM Cable and other cable up to 5/16" Dia. .312" Dia.	White	Box of 100	1000	6 lbs.
RA-1620R	For 10/3 and 12/4 NM Cable and other cable up to 13/32" Dia. .406" Dia.	White	Box of 100	1000	6 lbs.
RA-1630R	For 8/3 NM Cable and other cable up to 1/2" Dia. .500" Dia.	White	Box of 100	1000	6 lbs.
RA-1640R	For 6/3 NM Cable and other cable up to 9/16" Dia. .563" Dia.	White	Box of 50	500	5 lbs.
RA-1650R	For other round cable and tubing up to 5/8" Dia. .625" Dia.	White	Box of 50	500	6 lbs.



### STRAPS FOR UF CABLE

- The standard color is gray with a UV stabilizer.
- For prolonged outdoor exposure, black colored straps with a UV stabilizer are also available.

UF-2040	For 8/3 UF Cable .336" x 1.077"	Gray	Box of 50	1000	13 lbs.
UF-2050	For 6/3 UF Cable .400" x 1.300"	Gray	Box of 50	1000	17 lbs.



## Straps for Armored Cable (AC) and Metal-Clad (MC) Cable

ACMC-10	For AC and MC Cable from 3/8" (.375) to 1/2" (.500) Dia. 1/2" Dia.	Gray	Box of 50	500	5 lbs.
ACMC-20	For AC and MC Cable from 1/2" (.500) to 5/8" (.625) Dia. 5/8" Dia.	Gray	Box of 50	500	6 lbs.

