

Tapes, Colour Coding

Scotch® 35 Vinyl Electric Tape

Identify leads, splices and terminations. Abrasion and weather resistant 7 mil tape. Excellent mechanical and electrical insulation properties. Wraps smoothly and holds tightly over a wide range of temperatures. Mark safety areas.



UPC Number	Size	Case Qty	Colour
00-054007-10232-8	1/2" x 20'	100	White
00-054007-10224-3	1/2" x 20'	100	Red
00-054007-10240-3	1/2" x 20'	100	Blue
00-054007-10299-1	1/2" x 20'	100	Brown
00-054007-10281-6	1/2" x 20'	100	Gray
00-054007-10265-6	1/2" x 20'	100	Green
00-054007-10273-1	1/2" x 20'	100	Orange
00-054007-10257-1	1/2" x 20'	100	Yellow
00-054007-10885-6	3/4" x 66'	100	Brown
00-054007-10844-3	3/4" x 66'	100	Yellow
00-054007-10836-8	3/4" x 66'	100	Blue
00-054007-00072-3	3/4" x 66'	100	Gray
00-054007-10851-1	3/4" x 66'	100	Green
00-054007-10869-6	3/4" x 66'	100	Orange
00-054007-10810-8	3/4" x 66'	100	Red
00-054007-11271-6	3/4" x 66'	100	Violet
00-054007-10828-3	3/4" x 66'	100	White

Colourflex General Purpose Colour Coding Tape



UPC Number	Product ID	Size	Case Qty	Colour
00-051141-04470-5	Colourflex-BRN	3/4" x 60 ft. roll	100	Brown
00-051141-04474-3	Colourflex-ORA	3/4" x 60 ft. roll	100	Orange
00-051141-04752-2	Colourflex-BLU	3/4" x 60 ft. roll	100	Blue
00-051141-04755-3	Colourflex-GRN	3/4" x 60 ft. roll	100	Green
00-051141-04758-4	Colourflex-RED	3/4" x 60 ft. roll	100	Red
00-051141-04759-1	Colourflex-WHT	3/4" x 60 ft. roll	100	White
00-051141-04760-7	Colourflex-YLW	3/4" x 60 ft. roll	100	Yellow

Tapes, Electrician's Duct Tape

Scotch® 2000 Electrician's Duct Tape

General purpose easy tear vinyl duct tape.



UPC Number	Size	Case Qty
00-054007-43403-0	1.9" x 50 yds	12

Tapes, Friction Tape

3M™ Temflex™ Friction Tape 1755

Buy this versatile friction tape when you need to protect connections or bundle cables and wires. Thicker than vinyl or glass cloth tape. Splice connections with abrasion resistant cotton tape that has insulating rubber adhesive.



UPC Number	Size	Case Qty
00-054007-50217-3	1-1/2" x 82.5'	30
00-054007-50218-0	3/4" x 60'	60
00-054007-50216-6	3/4" x 82.5'	60

Tapes, Glass Cloth

3M™ Glass Cloth Electrical Tape

Insulate hot spots. Provides heat-stable insulation for switches, oven and furnace controls and motor leads. 7 mil tape with pressure sensitive adhesive. Thermosetting and heat stable to 266°F. (Class B temperatures) CSA Certified for 130°F and UL Recognized Component listing for 150°F.



UPC Number	Prod ID	Size	Case Qty
00-054007-15066-4	27	1/2" x 66'	50
00-054007-15074-9	27	3/4" x 66'	50