



LUBRICANTS

3-36® MULTI-PURPOSE LUBRICANT AND CORROSION INHIBITOR

- Multi-purpose lubricant, penetrant and corrosion inhibitor
- Forms a clear, thin film that lubricates, prevents corrosion, displaces moisture and penetrates
- Penetrates through corrosion to loosen frozen parts
- Lubricates without leaving a sticky residue
- VOC compliant
- Accepted for use in Canadian Food Processing Facilities

Part Number	Container Size	Units per Case
73005	312 g Aerosol	12
73009	19 L Pail	1
73011	208 L Drum	1



Use CRC Knock'er Loose® Penetrating Solvent to remove rust and corrosion, and to ease dis-assembly during routine repairs.

KNOCK'ER LOOSE® PENETRATING SOLVENT

- Industrial strength, low viscosity lubricant
- Dissolves rust, grease, gum and corrosion
- Creeps into cracks, seams, threads and joints better than the competition
- Eases the disassembly of machinery, tools and equipment for routine maintenance and emergency repairs
- Loosens rusted and corroded nuts, bolts and frozen components
- Lubricating residue prevents corrosion
- VOC compliant
- Convenient 360° spray valve – can be sprayed from any position

Part Number	Container Size	Units per Case
73020	369 g Aerosol	12

EXTREME DUTY SILICONE

- Premium grade silicone fluid that exhibits superior lubrication and temperature viscosity characteristics
- Reduces friction and galling even on metal-to-metal contact areas
- High temperature (-73°C to 232°C), high pressure (withstands 1200 lbs Falex test)
- High grade release and parting agent
- Clear, non-staining, odorless film resists moisture
- Convenient 360° spray valve – can be sprayed from any position

Part Number	Container Size	Units per Case
73030*	284 g Aerosol	12

SCREWLOOSE® SUPER PENETRANT

- Penetrates through rust and corrosion
- Facilitates fast and easy disassembly of mechanical components, fittings, assemblies and other fasteners
- Clear formula contains no dyes and leaves no mess
- VOC compliant
- Convenient 360° spray valve – can be sprayed from any position

Part Number	Container Size	Units per Case
75330	312 g Aerosol	12

EXTREME DUTY OPEN GEAR & CHAIN LUBE

- A tough, tacky, solid film lubricant used for reducing friction and wear
- Penetrates pores of metal, with exceptional "stay-put" characteristics
- Provides maximum lubrication and shock protection
- Reduces friction and wear
- Contains Molybdenum and Graphite
- Wide temperature range from -31°C to 176°C
- Will not wash or wear because of weather

Part Number	Container Size	Units per Case
73058	340 g Aerosol	12



*This product is labeled extremely flammable. Read and observe the special usage warning on the label. Do not apply while equipment is energized.