

Basic White Reflector (heat lamp) ☆



Basic downlight with low brightness splay. Aluminum reflector finished in white assures efficiency with A and Quad Tube lamps. Wide choice of wattage and lamp types, including heat lamp (1171 only). Economical choice for low budget applications.

Note: For dimming options, please consult the corresponding product Spec Sheet on www.canlyte.com.

<p>1071 White</p>	COMPACT FLUORESCENT		INCANDESCENT		
	NON-IC	IC/AIRSEAL®	NON-IC	IC	IC/AIRSEAL®
	1001F13N120 1001F13N347 1X13W QT*	1004ICF13N120 1004ICXF13N120 1X13W QT*	1002 75W PAR30L* 85W BR30 75W A19 1004IC-CDN 75W PAR30* 85W BR30 52W A19	1002IC 75W PAR30L* 75W BR30 40W A19	1004IC-CDN 50W PAR30 65W BR30 40W A19 1004ICX-CDN 75W PAR30* 65W BR30 52W A19
		REMODELER	REMODELER		REMODELER
		1004ICRF13N120 1X13W QT*	1003RS-CDN 75W PAR30L* 85W BR30 75W A19* 1004ICRS-CDN 75W PAR30* 85W BR30 52W A19		1004ICRS-CDN 50W PAR30 65W BR30 40W A19

<p>1171 White</p>	COMPACT FLUORESCENT		INCANDESCENT		
	NON-IC	IC/AIRSEAL®	NON-IC	IC	IC/AIRSEAL®
	1101F13N120 1101F13N347 1X13W QT* 1101F18N120 1101F18N347 1X18W QT	1104ICF13N120 1X13W QT* 1104ICF18N120 1104ICXF18N120 1X18W QT	1102 250W R40 IR 150W PAR38* 150W BR40 100W A19 1104IC-CDN 150W PAR38* 120W BR40 75W A19	1102IC 90W PAR38 100W BR40 60W A19	1104IC-CDN 75W PAR38 85W BR40 52W A19 1104ICX-CDN 100W PAR38 120W BR40 60W A19
	REMODELER	REMODELER	REMODELER		REMODELER
	1103RF18N120 1103RF18N347 1X18W QT	1104ICRF13N120 1X13W QT* 1104ICRF18N120 1X18W QT	1103RS-CDN 250W R40 IR 150W PAR38* 150W BR40 100W A19 1104ICRS-CDN 150W PAR38* 120W BR40 75W A19		1104ICRS-CDN 75W PAR38 85W BR40 52W A19

*See photometry p. 550 to 552.

Contour ☆



Simple contoured architectural flange for unique new appearance. Specially designed for task areas and wet locations such as showers. Gasket included certified for wet locations with or without gasket.

<p>1084WH White</p>	COMPACT FLUORESCENT		INCANDESCENT		
	NON-IC	IC/AIRSEAL®	NON-IC	IC	IC/AIRSEAL®
			1002 1004IC-CDN 75W PAR30S	1002IC 75W PAR30S	1004IC-CDN 1004ICX-CDN 75W PAR30S
			REMODELER	REMODELER	REMODELER
			1003RS-CDN 1004ICRS-CDN 75W PAR30S		1004ICRS-CDN 75W PAR30S

PAR30S = Short neck lamp only