

**Alzak® Cone** ☆



Specular Alzak® aperture cone controls glare. Aluminum reflector finished in white operates effectively with self-ballasted compact fluorescent and Quad Tube lamps as well as PAR and BR lamps. These trims offer a low iridescence finish.

Note: For dimming options, please consult the corresponding product Spec Sheet on [www.canlyte.com](http://www.canlyte.com).

		COMPACT FLUORESCENT		INCANDESCENT		
		NON-IC	IC/AIRSEAL®	NON-IC	IC	IC/AIRSEAL®
<p><b>1076CL</b> Specular Clear Alzak®</p>		<b>1001F13N120</b> <b>1001F13N347</b> 1X13W QT*	<b>1004ICF13N120</b> <b>1004ICXF13N120</b> 1X13W QT*	<b>1002</b> 75W PAR30L* 85W BR30 100W A19  <b>1004IC-CDN</b> 75W PAR30* 85W BR30 60W A19	<b>1002IC</b> 75W PAR30L* 75W BR30 40W A19	<b>1004IC-CDN</b> 50W PAR30 65W BR30 40W A19  <b>1004ICX-CDN</b> 75W PAR30* 85W BR30 60W A19
			<b>REMODELER</b> <b>1004ICRF13N120</b> 1X13W QT*	<b>REMODELER</b> <b>1003RS-CDN</b> 75W PAR30L* 85W BR30 100W A19  <b>1004ICRS-CDN</b> 75W PAR30* 85W BR30 60W A19		<b>REMODELER</b> <b>1004ICRS-CDN</b> 50W PAR30 65W BR30 40W A19
<p><b>1176CL</b> Specular Clear Alzak®</p>		<b>1101F13N120</b> <b>1101F13N347</b> 1X13W QT*  <b>1101F18N120</b> <b>1101F18N347</b> 1X18W QT	<b>1104ICF13N120</b> 1X13W QT*  <b>1104ICF18N120</b> <b>1104ICXF18N120</b> 1X18W QT	<b>1102</b> 150W PAR38 150W BR40 100W A19  <b>1104IC-CDN</b> 90W PAR38* 120W BR40 60W A19	<b>1102IC</b> 90W PAR38* 100W BR40 60W A19	<b>1104IC-CDN</b> 75W PAR38 65W BR40 40W A19  <b>1104ICX-CDN</b> 90W PAR38* 90W BR40 52W A19
			<b>REMODELER</b> <b>1103RF18N120</b> <b>1103RF18N347</b> 1X18W QT	<b>REMODELER</b> <b>1104ICRF13N120</b> 1X13W QT*  <b>1104ICRF18N120</b> 1X18W QT	<b>REMODELER</b> <b>1103RS-CDN</b> 150W PAR38 150W BR40 100W A19  <b>1104ICRS-CDN</b> 90W PAR38* 120W BR40 60W A19	<b>REMODELER</b> <b>1104ICRS-CDN</b> 75W PAR38 65W BR40 40W A19

\*See photometry p. 550 to 552.