




**6 3/4" Aperture  
Deep Alzak Reflector**

**Lytecaster  
Recessed Downlight**

**1146**



Ceiling Opening : 6 3/4"

Complete fixture consists of Reflector Trim & Frame-in Kit. Select each separately

**REFLECTOR TRIM**

<b>1146CL</b>	Specular Clear Alzak
<b>1146GD</b>	Specular Gold Alzak
<b>1146CCD</b>	Confort Clear Diffuse

**INC FRAME-IN-KIT**

NON-IC	<b>1102</b>
REMODELER	<b>1103RS-CDN</b>

**CFL FRAME-IN-KIT**

NON-IC	<b>1102FH1</b>
NON-IC	<b>1102FH3</b>
NON-IC	<b>1102Q113VF120</b>
NON-IC	<b>1102Q113VF347</b>
NON-IC	<b>1102DH1</b>
NON-IC	<b>1102DH3</b>
NON-IC	<b>1102Q213VF120</b>
NON-IC	<b>1102Q213VF347</b>
NON-IC	<b>1102P2632VG120</b>
NON-IC	<b>1102P2632VG347</b>
IC	<b>1102FH1IC</b>
IC	<b>1102P2632VG120IC</b>

**LAMP**

150W A21	<b>100W A19</b>
150W A21	100W A19

**LAMP**

LAMP	VOLT	BASE
1-13W QT	120V HPF	GX23-2 (2 pin)
1-13W QT	347V HPF	GX23-2 (2 pin)
1 X 13W QT	120V Electronic	G24q-1 (4 pin)
1 X 13W QT	347V Electronic	G24q-1 (4 pin)
2-13W QT	120V HPF	GX23-2 (2 pin)
2-13W QT	347V HPF	GX23-2 (2 pin)
2 X 13W QT	120V Electronic	G24q-1 (4 pin)
2 X 13W QT	347V Electronic	G24q-1 (4 pin)
1-26/32W TTT	120V Electronic	GX24q-3 (4 pin)
1-26/32W TTT	347V Electronic	GX24q-3 (4 pin)
1-13W QT	120V HPF	GX23-2 (2 pin)
1-26/32W TTT	120V	GX24q-3 (4 pin)

**Features**

**Reflector:** Hydroformed aluminum, .050" thick ; 38° shielding angle; specular clear or gold Alzak finish; white trim flange.

**Frame-In-Kit**

**Note:** For complete Frame-In-Kit specifications, see sheet 1102 , 1103R , 1102F and 1102FIC

**Accessories**

**Extra Wide Flange Trim Ring: 1954** ; For most 1100 series Reflector Trim. O.D. 8 5/8".

**Labels : CSA**

Suitable for damp locations.

**TYPE L3-5  
LIGHTOLIER  
1102/1146CCD  
C/W 100A19 LONG  
LIFE LAMP**