

**Section of track**

Includes track, flush dead end, twist-lock mounting clips and additional hardware for direct mounting.

Fast Track single-circuit track enables all the Lytespots to work in tandem. It can be surface or stem mounted on ceilings, and mounted vertically or horizontally on walls, in straight runs or patterns. It can be field cut to the desired length. Capacity is 20 amps at 120V per branch circuit.

To build a straight run or a pattern, order as many sections of track as required (lengths of 2' to 12'), along with the connectors, power feeds and accessories needed for your project.

2'  
**55002AL** Aluminum  
**55002WH** White  
**55002BK** Black  
 Length: 19-7/8"

4'  
**55004AL** Aluminum  
**55004WH** White  
**55004BK** Black  
 Length: 43-7/8"

6'  
**55006AL** Aluminum  
**55006WH** White  
**55006BK** Black  
 Length: 67-7/8"

8'  
**55008AL** Aluminum  
**55008WH** White  
**55008BK** Black  
 Length: 91-7/8"

12'  
**55012AL** Aluminum  
**55012WH** White  
**55012BK** Black  
 Length: 139-7/8"

**Monopoint & Multipoint**



**Monopoint**

Very shallow Monopoint canopy (1/4" high, 4-1/2" diameter) for surface mounting of any single Lytespot over standard outlet box. Includes crossbar.

**6190NAL** Aluminum  
**6190WH** White  
**6190BK** Black



**Multipoint**

Surface mounts up to 3 Lytespots, depending on luminaire size, over any standard outlet box. Track length 11-11/16", width 4-1/2", depth 9/16". Includes crossbar. For compatible Lytespots, please refer to p.626-635 of the Canlyte Resource Guide.

**7619WH** White  
**7619BK** Black


**Power Feeds**



**Live End Invisible Feed**

For direct feed of track mounted flush with ceiling, without using outlet box or canopy.

**55031AL** Aluminum  
**55031WH** White  
**55031BK** Black



**End Feed Kit**

Mounts to end of the track when power is fed from outlet box. Includes live end and flush 4-1/2" square canopy.


**55034AL** Aluminum  
**55034WH** White  
**55034BK** Black



**Live End Feed**

For feeding track mounted flush with ceiling, without using outlet box or canopy. Use with floating invisible feed or with stems (not included).

**55030AL** Aluminum  
**55030WH** White  
**55030BK** Black



**Live End Conduit Adapter**

For feeding power to live end from surface conduit which has 1/2" IPS threaded connector (1" dia. x 3/4" long).

**55033AL** Aluminum  
**55033WH** White  
**55033BK** Black