

F15T8 D ALTO

Product family description
T8 Medium Bi-Pin Linear Fluorescent Lamps.

Features/Benefits

- Requires use of starters.

Applications

- Offer impressive lighting economics for modernizing, expanding facilities or new construction.

Notes


- Rated average life under specified test conditions with lamps turned off and restarted no more frequently than once every 3 operating hours. Lamp life is appreciably longer if lamps are started less frequently. (202)
- Approximate Initial Lumens. The lamp lumen output is based upon lamp performance after 100 hours of operating life, when the output is measured during operation on a reference ballast under standard laboratory conditions. (203)
- For expected lamp lumen output, commercial ballast manufacturers can advise the appropriate Ballast Factor for each of their ballasts when they are informed of the designated lamp. The Ballast Factor is a multiplier applied to the designated lamp lumen output. (204)
- Design Lumens are the approximate lamp lumen output at 40% of the lamp's Rated Average Life. This output is based upon measurements obtained during lamp operation on a reference ballast under standard laboratory conditions. (208)
- Life is based upon household usage of 6 hours average usage per day, 7 days per week. See individual product packaging for details. (240)

| Product data | |
|--------------------------|---|
| Product Number | 378232 |
| Full product name | F15T8 D ALTO |
| Ordering Code | F15T8/D/ALTO |
| Pack type | 1 Lamp |
| Pieces per Sku | 1 |
| Skus/Case | 24 |
| Pack UPC | 046677378233 |
| EAN2US | |
| Case Bar Code | 50046677378238 |
| Successor Product number | |
| Base | Medium Bi-Pin [Medium Bi-Pin Fluorescent] |
| Base Information | Green Base |


| Product data | |
|------------------------------|---------------------|
| Bulb | T8 |
| Packing Type | 1LP [1 Lamp] |
| Packing Configuration | 24 |
| Type | F15T8 |
| Feature | ALTO® |
| Rated Avg. Life [3 hr Start] | 7500 hr |
| Ordering Code | F15T8/D/ALTO |
| Pack UPC | 046677378233 |
| Case Bar Code | 50046677378238 |
| Watts | 15W |
| Mercury (Hg) Content | 1.4 mg |
| Color Code | 54 |
| Color Rendering Index | 79 Ra8 |
| Color Designation | Daylight [Daylight] |
| Color Temperature | 6500 K |
| Initial Lumens | 750 Lm |
| Design Mean Lumens | 660 Lm |
| Nominal Length [inch] | 18 |
| Product Number | 378232 |



F-T8-PH Med Bipin/GB



Base Medium Bi-Pin



F-T8-PH Med Bipin

