

Fast Track and Advent Accessories



Fixed Canopy Kit

4-1/2" diameter. Includes crossbar.

55100AL	Aluminum
55100WH	White
55100BK	Black



Canopy Kit For Sloped Ceilings

Installs over standard outlet box. Adjusts from 0° to 90°. For sloped or cathedral ceiling applications. Includes 4-1/2" diameter canopy, swivel and crossbar.

55101AL	Aluminum
55101WH	White
55101BK	Black



Stem Mounting Kits

For suspending track. Complete kits are made up of two catalogue numbers: one for the stem and the other for the canopy (#55100 or #55101). Use 2 stems for a 4-foot track, three stems for an 8-foot or 12-foot track. For continuous runs, use one stem every 4'. Stems attach to track at any point. Can be field cut to the desired length must be re-threaded (1/8 - 27 1.P.T.). 72" Extension Stem is used to extend stem length. Stem diameter: 1/2".



Sloped Ceiling Adapter

Installs on Monopoint, Multipoint or track. Adjusts from 0° to 90°. For sloped or cathedral ceiling applications. Can be used alone or with Suspension Stems. For compatible Lytespots, please refer to p.810-816 of the Canlyte Ressource Guide.

6079WH	White
6079BK	Black

18" Stem

55102AL	Aluminum
55102MT	Metal Paint
55102WH	White
55102BK	Black

72" Stem

55105AL	Aluminum
55105MT	Metal Paint
55105WH	White
55105BK	Black

72" Extension Stem

55106AL	Aluminum
55106MT	Metal Paint
55106WH	White
55106BK	Black

36" Stem

55103AL	Aluminum
55103MT	Metal Paint
55103WH	White
55103BK	Black

48" Stem

55104AL	Aluminum
55104MT	Metal Paint
55104WH	White
55104BK	Black



Twist-Lock Flush Clips

Set of 6. For Fast Track or Advent.

55066	Zinc plated
--------------	-------------



T-Bar Clips

Set of 6. For grid ceilings. For Fast Track or Advent.

55041	Zinc plated
--------------	-------------



Suspension Stems

For suspending Lytespots on Fast Track or Advent Tracks. Stem diameter: 1/2". For compatible Lytespots, please refer to p.810-816 of the Canlyte Ressource Guide.

6074WH	18" White
6074BK	18" Black
6074MT	18" Metal Paint
6075WH	36" White
6075BK	36" Black
6075MT	36" Metal Paint
6076WH	48" White
6076BK	48" Black
6074MT	48" Metal Paint

Note: Not field cuttable



Surface Clips

Set of 6. For installation on uneven ceilings. For Fast Track or Advent.

55065WH	White
55065BK	Black



Pendant Adapter

Supports cord-mounted luminaires (5 lb max.) and stem or chain luminaires (25 lb max.). Loop (female thread 1/4" - 18 NPS) and chain not included.

7589	White
7589BK	Black



Convenience Outlet

Provides auxiliary source for plug-in equipment. Capacity of 6 amps.

6085	White
-------------	-------