

**FLAT FENDER WASHERS
RONDELLES DE PROTECTION**

**162
Series**

Used for Fender and Body work. Also two washers can be bolted together and used for Heater Hose Hole plugs.



ORDER BY STOCK NUMBER

Standard Package: 100 Pieces

Stock No.	Bolt Size	Outside Dia.	Inside Dia.	Thickness	Stock No.	Bolt Size	Outside Dia.	Inside Dia.	Thickness
162-393	3/16	1"	13/64	3/64	162-397	5/16	1-1/4	11/32	1/16
162-394	3/16	3/4	13/64	3/64	162-398	3/8	1-1/2	13/32	1/16
162-395	1/4	1-1/4	9/32	1/16	162-399	5/16	1-1/2	11/32	1/16
162-396	5/16	1"	11/32	1/16	162-400	1/2	2"	17/32	1/16

GARAGE ASSORTMENT

No. 020-057

Contains 71 Bright Plated Fender Washers for 1/4", 5/16" and 3/8" Bolts. Packed in rigid, transparent plastic container.

020-057



**MACHINERY BUSHINGS
BAGUES DE MACHINERIE**

**162
Series**

These steel repair bushings are used on Agricultural Machinery, Road Machines, Mine and Mill Equipment, Automobiles, Trucks, etc.



ORDER BY STOCK NUMBER

Standard Package: 25 Pieces

Stock No.	Shaft Dia.	Outside Dia.	Gauge	Weight Per 100 pcs.	Stock No.	Shaft Dia.	Outside Dia.	Gauge	Weight Per 100 pcs.
162-610	5/8	1-1/8	18	0.9	162-626	1-1/4	1-7/8	14	3.4
162-611			14	1.5	162-627			10	6.1
162-613	3/4	1-1/4	18	1.0	162-631	1-3/8	2-1/8	18	2.7
162-614			14	1.7	163-632			14	4.6
162-615			10	3.1	162-633			10	8.2
162-616	7/8	1-3/8	18	1.2	162-635	1-1/2	2-1/4	14	4.8
162-617			14	2.0	162-636			10	8.6
162-619	1	1-1/2	18	1.3	162-640	1-3/4	2-1/2	18	3.3
162-620			14	2.2	162-641			14	5.6
162-621			10	4.0	162-642			10	10.0
162-622	1-1/8	1-3/4	18	1.9	162-650	1-7/8	2-7/8	14	8.3
162-623			14	3.1	162-653	2	3	14	8.6
162-624			10	5.6	162-654			10	15.0
162-625	1-1/4	1-7/8	18	2.0	162-657	2-1/8	3-1/8	10	16.3

18 Ga.=.050"; 14 Ga.=.083"; 10 Ga.=.134"

ASSORTMENT

No. 020-875

This assortment is made up of 174 Machinery Bushings selected by popularity. Twenty eight sizes for complete coverage. The 020-875 Assortment includes a 3-colour display board and 13 screw hooks. Ideal for Implement and Machinery dealers.

020-875

