

ROOFING/SIDING SCREWS VIS DE TOITURE

126
Series

'Self Sealing' Indented Hex Washer Head with Weather Sealing Washer

Specially designed screws for attaching metal siding or roofing. Features a neoprene weather sealing washer under the head of screws. High-carbon, zinc plated steel. Also available with painted heads in white, bone, brown and red. Price on application.

ORDER BY STOCK NUMBER

Standard Package: 100 Screws

Stock No.	Size	Hex Head Across Flats	Stock No.	Size	Hex Head Across Flats
126-950	10 x 1	1/4	126-963	14 x 1-1/4	3/8
126-952	10 x 1-1/2	1/4	126-964	14 x 1-1/2	3/8
126-954	10 x 2	1/4	126-966	14 x 2	3/8
126-962	14 x 1	3/8	-	-	-



STOVE BOLTS BOULONS DE POELE

195
Flat

196
Round

- With Hex Nuts
- Round Socket/Slot Combination Drive
- Flat Socket Drive

ORDER BY STOCK NUMBER

Standard Package: 100 Bolts and Nuts

Flat Head			Round Head		
Stock No.	Size	Stock No.	Stock No.	Size	Stock No.
Flat	Round	Size	Flat	Round	Size
195-087	196-087	1/8 x 1/2	195-195	196-195	3/16 x 1-1/4
195-089	196-089	1/8 x 3/4	195-197	196-197	3/16 x 1-1/2
195-091	196-091	1/8 x 1	195-199	196-199	3/16 x 1-3/4
195-093	196-093	1/8 x 1-1/4	195-200	196-200	3/16 x 2
195-095	196-095	1/8 x 1-1/2	195-202	196-202	3/16 x 2-1/2
195-189	196-189	3/16 x 1/2	195-204	196-204	3/16 x 3
195-191	196-191	3/16 x 3/4	195-305	196-305	1/4 x 1/2
195-193	196-193	3/16 x 1	195-306	196-306	1/4 x 5/8
			195-307	196-307	1/4 x 3/4
			195-309	196-309	1/4 x 1
			195-311	196-311	1/4 x 1-1/4
			195-313	196-313	1/4 x 1-1/2
			195-315	196-315	1/4 x 1-3/4
			195-316	196-316	1/4 x 2
			195-317	196-317	1/4 x 2-1/4
			195-318	196-318	1/4 x 2-1/2
			195-320	196-320	1/4 x 3
			195-444	196-444	5/16 x 1
			195-448	196-448	5/16 x 1-1/2
			195-451	196-451	5/16 x 2
			195-453	196-453	5/16 x 2-1/2
			195-455	196-455	5/16 x 3
			195-493	196-493	3/8 x 1-1/2
			195-496	196-496	3/8 x 2
			195-498	196-498	3/8 x 2-1/2
			195-500	196-500	3/8 x 3

STOVE BOLTS ASSORTMENTS ASSORTIMENTS DE BOULONS DE POELE

GARAGE ASSORTMENT ROUND HEAD

No. 020-044

- Contains 68 Stove Bolts from 3/16" x 1/2" to 1/4" x 2".
- Packed in rigid, transparent, plastic container.

FLAT HEAD GARAGE ASSORTMENT

No. 020-045

- Contains 68 Stove Bolts from 3/16" x 1/2" to 1/4" x 2".
- Packed in rigid, transparent, plastic container.

STOVE BOLT UTILITY ASSORTMENT

No. 020-324

Contains 200 Round Head Stove Bolts, from 3/16" x 1/2" to 1/4" x 2".



020-044



020-324

Stove Bolt and Machine Screw Equivalent Sizes

Stove Bolt Diameter	1/8	5/32	3/16	1/4	5/16	3/8
Machine Screw Size	6-32	8-32	10-24	1/4-20	5/16-18	3/8-16