

18.8 Stainless Steel PAN HEAD SOCKET TAPPING SCREWS



**Series
5163**

SIZE No	DIAMETER X LENGTH	PKG QTY	CASE QTY
------------	----------------------	------------	-------------

No.4 Diameter

-040	4X5/16	100	7500
-041	4X3/8	100	7500
-043	4X1/2	100	7500
-044	4X5/8	100	7500
-045	4X3/4	100	7500
-047	4X1	100	7500

No.6 Diameter

-084	6X5/16	100	7500
-085	6X3/8	100	7500
-087	6X1/2	100	7500
-088	6X5/8	100	7500
-089	6X3/4	100	7500
-090	6X7/8	100	7500
-091	6X1	100	7500
-093	6X1 1/4	100	4500
-095	6X1 1/2	100	4500
-097	6X1 3/4	100	3000
-098	6X2	100	3000

No.8 Diameter

-135	8X3/8	100	7500
-137	8X1/2	100	7500
-138	8X5/8	100	7500
-139	8X3/4	100	4500
-140	8X7/8	100	4500
-141	8X1	100	4500
-143	8X1 1/4	100	3000
-145	8X1 1/2	100	3000
-147	8X1 3/4	100	2000
-148	8X2	100	2000
-150	8X2 1/2	100	1600
-152	8X3	100	800

SIZE No	DIAMETER X LENGTH	PKG QTY	CASE QTY
------------	----------------------	------------	-------------

No.10 Diameter

-187	10X3/8	100	7500
-189	10X1/2	100	7500
-190	10X5/8	100	4500
-191	10X3/4	100	4500
-192	10X7/8	100	4500
-193	10X1	100	3000
-195	10X1 1/4	100	3000
-197	10X1 1/2	100	2000
-199	10X1 3/4	100	2000
-200	10X2	100	1600
-202	10X2 1/2	100	1600
-204	10X3	100	800
-206	10X3 1/2	100	800

No.12 Diameter

-246	12X1/2	100	4500
-248	12X3/4	100	4500
-250	12X1	100	3000
-252	12X1 1/4	100	2000
-254	12X1 1/2	100	2000
-257	12X2	100	1600
-259	12X2 1/2	100	1200

No.14 Diameter

-276	14X1/2	100	3000
-278	14X3/4	100	3000
-280	14X1	100	2000
-282	14X1 1/4	100	2000
-284	14X1 1/2	100	1600
-286	14X1 3/4	100	1600
-287	14X2	100	1200
-289	14X2 1/2	100	1200
-291	14X3	100	600

Note: Please use Series and Size No. when ordering:

Example: 4 x 5/16 18.8 Stainless Steel Pan Head Socket Tapping Screws

Series Size No.

5163 -040

Stock Sizes are shown in **HEAVY** type.