

18.8 Stainless Steel PAN HEAD SOCKET TAPPING SCREWS

**Series
5163**



SIZE No	DIAMETER x LENGTH	PKG QTY	CASE QTY
---------	-------------------	---------	----------

No. 4 Diameter

- 040	4X5/16	100	7500
- 041	4X3/8	100	7500
- 043	4X1/2	100	7500
- 044	4X5/8	100	7500
- 045	4X3/4	100	7500
- 047	4X1	100	7500

No. 6 Diameter

- 084	6X5/16	100	7500
- 085	6X3/8	100	7500
- 087	6X1/2	100	7500
- 088	6X5/8	100	7500
- 089	6X3/4	100	7500
- 090	6X7/8	100	7500
- 091	6X1	100	7500
- 093	6X1 1/4	100	4500
- 095	6X1 1/2	100	4500
- 097	6X1 3/4	100	3000
- 098	6X2	100	3000

No. 8 Diameter

- 135	8X3/8	100	7500
- 137	8X1/2	100	7500
- 138	8X5/8	100	7500
- 139	8X3/4	100	4500
- 140	8X7/8	100	4500
- 141	8X1	100	4500
- 143	8X1 1/4	100	3000
- 145	8X1 1/2	100	3000
- 147	8X1 3/4	100	2000
- 148	8X2	100	2000
- 150	8X2 1/2	100	1600
- 152	8X3	100	800

SIZE No	DIAMETER x LENGTH	PKG QTY	CASE QTY
---------	-------------------	---------	----------

No. 10 Diameter

- 187	10X3/8	100	7500
- 189	10X1/2	100	7500
- 190	10X5/8	100	4500
- 191	10X3/4	100	4500
- 192	10X7/8	100	4500
- 193	10X1	100	3000
- 195	10X1 1/4	100	3000
- 197	10X1 1/2	100	2000
- 199	10X1 3/4	100	2000
- 200	10X2	100	1600
- 202	10X2 1/2	100	1600
- 204	10X3	100	800
- 206	10X3 1/2	100	800

No. 12 Diameter

- 246	12X1/2	100	4500
- 248	12X3/4	100	4500
- 250	12X1	100	3000
- 252	12X1 1/4	100	2000
- 254	12X1 1/2	100	2000
- 257	12X2	100	1600
- 259	12X2 1/2	100	1200
- 257	12X2	100	1600

No. 14 Diameter

- 276	14X1/2	100	3000
- 278	14X3/4	100	3000
- 280	14X1	100	2000
- 282	14X1 1/4	100	2000
- 284	14X1 1/2	100	1600
- 286	14X1 3/4	100	1600
- 287	14X2	100	1200
- 289	14X2 1/2	100	1200
- 291	14X3	100	600

Note: Please use Series and Size No. when ordering:

Example: 4 x 5/16 18.8 Stainless Steel Pan Head Socket Tapping Screws

Series Size No.
5163 - 040

Stock Sizes are shown in **HEAVY** type.