

AN INTRODUCTION TO...


# STAINLESS STEEL

# ACIER INOXYDABLE

...UNE INTRODUCTION.

[www.hpaulin.com](http://www.hpaulin.com)

For a full listing of Stainless Steel, please refer to our current catalogue or visit our website to download a PDF version.



**HEX BOLTS**

**CARRIAGE BOLTS**

**LAG BOLTS**

**SOCKET HEAD CAP SCREWS**

**FINISHED HEX NUTS**

**NYLON INSERT STOP NUTS**

**HEX MACHINE SCREW NUTS**

**WASHERS**

**COTTER PINS**

**THREADED RODS**

**MACHINE SCREWS**



## 18.8 STAINLESS STEEL HEX BOLTS BOULONS HEX EN ACIER INOXYDABLE 18,8

**5000 Series**

Corrosion resistant Type 300 Series (18% chromium - 8% nickel). Used in marine applications, food processing equipment and wherever resistance to most acids and chemicals is required. Non-magnetic. UNC thread.



Order by stock number.

Stock No.	Size	Std. Pkg.	Stock No.	Size	Std. Pkg.	Stock No.	Size	Std. Pkg.	Stock No.	Size	Std. Pkg.
5000-307	1/4-20 x 3/4	100	5000-442	5/16-18 x 3/4	100	5000-487	3/8-16 x 3/4	100	5000-577	1/2-13 x 3/4	25
5000-309	1/4-20 x 1	100	5000-444	5/16-18 x 1	100	5000-489	3/8-16 x 1	100	5000-579	1/2-13 x 1	25
5000-313	1/4-20 x 1-1/2	100	5000-448	5/16-18 x 1-1/2	100	5000-493	3/8-16 x 1-1/2	100	5000-583	1/2-13 x 1-1/2	25
5000-316	1/4-20 x 2	100	5000-451	5/16-18 x 2	100	5000-496	3/8-16 x 2	100	5000-586	1/2-13 x 2	20
5000-318	1/4-20 x 2-1/2	50	5000-453	5/16-18 x 2-1/2	50	5000-498	3/8-16 x 2-1/2	50	5000-588	1/2-13 x 2-1/2	20
5000-320	1/4-20 x 3	25	5000-455	5/16-18 x 3	25	5000-500	3/8-16 x 3	25	5000-590	1/2-13 x 3	10

## 18.8 STAINLESS STEEL CARRIAGE BOLTS BOULONS DE CARROSSE ACIER INOXYDABLE 18,8

**5002 Series**



Order by stock number.

Stock No.	Size	Std. Pkg.	Stock No.	Size	Std. Pkg.	Stock No.	Size	Std. Pkg.
5002-309	1/4-20 x 1	100	5002-444	5/16-18 x 1	50	5002-489	3/8-16 x 1	50
5002-313	1/4-20 x 1-1/2	100	5002-448	5/16-18 x 1-1/2	50	5002-493	3/8-16 x 1-1/2	50
5002-316	1/4-20 x 2	100	5002-451	5/16-18 x 2	50	5002-496	3/8-16 x 2	25
5002-318	1/4-20 x 2-1/2	50	5002-453	5/16-18 x 2-1/2	25	5002-498	3/8-16 x 2-1/2	25
5002-320	1/4-20 x 3	50	5002-455	5/16-18 x 3	25	5002-500	3/8-16 x 3	25
5002-324	1/4-20 x 4	25	5002-459	5/16-18 x 4	25	5002-504	3/8-16 x 4	10

## 18.8 STAINLESS STEEL LAG BOLTS TIRE-FOND ACIER INOXYDABLE 18,8

**5003 Series**



Order by stock number.

Stock No.	Size	Std. Pkg.	Stock No.	Size	Std. Pkg.	Stock No.	Size	Std. Pkg.	Stock No.	Size	Std. Pkg.
5003-309	1/4-20 x 1	50	—	5/16-18 x 1	—	5003-493	3/8-16 x 1-1/2	50	5003-586	1/2-13 x 2	50
5003-313	1/4-20 x 1-1/2	50	5003-448	5/16-18 x 1-1/2	50	5003-496	3/8-16 x 2	50	5003-588	1/2-13 x 2-1/2	25
5003-316	1/4-20 x 2	50	5003-451	5/16-18 x 2	50	5003-498	3/8-16 x 2-1/2	25	5003-590	1/2-13 x 3	25
5003-318	1/4-20 x 2-1/2	25	5003-453	5/16-18 x 2-1/2	25	5003-500	3/8-16 x 3	25	5003-594	1/2-13 x 4	20
5003-320	1/4-20 x 3	25	5000-455	5/16-18 x 3	25	5000-504	3/8-16 x 4	20			
5003-324	1/4-20 x 4	20	5000-459	5/16-18 x 4	20						

## 18.8 STAINLESS STEEL SOCKET HEAD CAP SCREWS BOULONS DE PRESSION ACIER INOXYDABLE 18,8

**5006 UNC**



Order by stock number.

Stock No.	Size	Std. Pkg.	Stock No.	Size	Std. Pkg.	Stock No.	Size	Std. Pkg.	Stock No.	Size	Std. Pkg.
5006-309	1/4-20 x 1	100	5006-444	5/16-18 x 1	100	5006-489	3/8-16 x 1	100	5006-579	1/2-13 x 1	50
5006-313	1/4-20 x 1-1/2	100	5006-448	5/16-18 x 1-1/2	100	5006-493	3/8-16 x 1-1/2	100	5006-583	1/2-13 x 1-1/2	50
5006-316	1/4-20 x 2	100	5006-451	5/16-18 x 2	100	5006-496	3/8-16 x 2	50	5006-586	1/2-13 x 2	50
5006-318	1/4-20 x 2-1/2	100	5006-453	5/16-18 x 2-1/2	100	5006-498	3/8-16 x 2-1/2	50	5006-588	1/2-13 x 2-1/2	25
5006-320	1/4-20 x 3	50	5006-455	5/16-18 x 3	50	5006-500	3/8-16 x 3	50	5006-590	1/2-13 x 3	25

## 18.8 STAINLESS STEEL FINISHED HEX NUTS ÉCROUS HEX ACIER INOXYDABLE 18,8

**5026**  
Series

Order by stock number.

Stock No.	Bolt Size	Std. Pkg.
5026-014	1/4-20	100
5026-016	5/16-18	100
5026-018	3/8-16	100
5026-022	1/2-13	50



## 18.8 STAINLESS STEEL NYLON INSERT STOP NUTS ÉCROUS À BLOCAGE NYLON INOXYDABLE 18,8

**5034**  
Series

Order by stock number.

Stock No.	Bolt Size	Std. Pkg.
5034-006	6-32	100
5034-008	8-32	100
5034-010	10-24	100
5034-011	10-32	100
5034-014	1/4-20	100
5034-016	5/16-18	100
5034-018	3/8-16	100
5034-022	1/2-13	50



## 18.8 STAINLESS STEEL HEX MACHINE SCREW NUTS ÉCROUS POUR VIS DE MÉCANIQUE ACIER INOXYDABLE 18,8

**5035**  
Series

Order by stock number.

Stock No.	Bolt Size	Std. Pkg.
5035-006	6-32	100
5035-008	8-32	100
5035-010	10-24	100
5035-014	1/4-20	100



*For a complete listing of non-ferrous and stainless fasteners see separate Papco<sup>®</sup> Corrosion Resistant Catalogue.*

## 18.8 STAINLESS STEEL WASHER RONDELLES ACIER INOXYDABLE 18,8

**5055**  
Series

### 18.8 Flat Washers

Order by stock number.

Stock No.	Bolt Size	I.D.	O.D.	Thickness	Std. Pkg.
5055-206	No. 6	.156	3/8	.031	100
5055-208	No. 8	.174	3/8	.031	100
5055-210	No. 10	.203	7/16	.031	100
5055-214	1/4	.281	5/8	.050	100
5055-216	5/16	.345	3/4	.050	100
5055-218	3/8	.406	7/8	.050	100
5055-222	1/2	.531	1-1/4	.062	50



**5056**  
Series

### 18.8 Finishing Washers

Order by stock number.

Stock No.	Screw Size	Std. Pkg.
5056-971	No. 6	100
5056-973	No. 8	100
5056-975	No. 10	100
5056-979	1/4	100



**5057**  
Series

### 18.8 Fender Washers

Order by stock number.

Stock No.	Bolt Size	O.D.	Std. Pkg.
5057-394	No. 10	1	100
5057-395	1/4	1-1/4	100
5057-396	5/16	1-1/2	100
5057-398	3/8	1-1/2	100
5057-400	1/2	2	50



**5058**  
Series

### 18.8 Regular Lock Washers

Order by stock number.

Stock No.	Bolt Size	Std. Pkg.
5058-014	1/4	100
5058-016	5/16	100
5058-018	3/8	100
5058-022	1/2	100



**18.8 STAINLESS COTTER PINS  
GOUPILLES ACIER INOXYDABLE 18,8**

**5080**  
Series



Order by stock number.

Stock No.	Size	Std. Pkg.
5080-091	3/32 x 1	100
5080-095	3/32 x 1-1/2	100
5080-141	1/8 x 1	100
5080-145	1/8 x 1-1/2	100
5080-148	1/8 x 2	100
5080-171	5/32 x 1-1/2	100
5080-174	5/32 x 2	100

**18.8 STAINLESS STEEL THREADED ROD  
TIGES FILETÉES ACIER INOXYDABLE 18,8**

**5091**  
Series



Std. Pkg. as required.

Order by stock number.

Stock No.	Size	Stock No.	Size
5091-310	10-24 x 36"	5091-354	1/4-20 x 72"
5091-314	1/4-20 x 36"	5091-356	5/16-18 x 72"
5091-316	5/16-18 x 36"	5091-358	3/8-16 x 72"
5091-318	3/8-16 x 36"	5091-362	1/2-13 x 72"
5091-322	1/2-13 x 36"	5091-364	5/8-11 x 72"
5091-324	5/8-11 x 36"	5091-366	3/4-10 x 72"
5091-326	3/4-10 X36"		

Note: Fine Thread 36" long Threaded Rods are available – price on application.

**18.8 STAINLESS MACHINE SCREWS  
VIS DE MÉCANIQUE INOXYDABLE 18,8**

**5113**  
OVAL



**5114**  
PAN

PHILLIPS

Order by stock number.

Stock No.	Size	Std. Pkg.
5113-087	5114-087 6-32 x 1/2	100
5113-091	5114-091 6-32 x 1	100
5113-141	5114-141 8-32 x 1	100
5113-193	5114-193 10-24 x 1	100
5113-197	5114-197 10-24 x 1-1/2	100
5113-200	5114-200 10-24 x 2	100
5113-313	5114-313 1/4-20 x 1-1/2	100
5113-316	5114-316 1/4-20 x 2	100

**18.8 STAINLESS TAPPING SCREWS  
VIS TARAUEUSES INOXYDABLE 18,8**

**5162**  
Series



SQUARE DRIVE

Order by stock number.

Stock No.	Size	Std. Pkg.
5162-089	6 x 3/4	100
5162-139	8 x 3/4	100
5162-141	8 x 1	100
5162-193	10 x 1	100
5162-195	10 x 1-1/4	100
5162-197	10 x 1-1/2	100
5162-254	12 x 1-1/2	100

**18.8 STAINLESS TAPPING SCREWS - TYPE A  
VIS TARAUEUSES INOXYDABLE 18,8**

**5163**  
PAN



**5165**  
OVAL

Order by stock number.

Stock No.	Size	Std. Pkg.
5163-043	5165-043 4 x 1/2	100
5163-089	5165-089 6 x 3/4	100
5163-091	5165-091 6 x 1	100
5163-139	5165-139 8 x 3/4	100
5163-141	5165-141 8 x 1	100
5163-191	5165-191 10 x 3/4	100
5163-193	5165-193 10 x 1	100

## 18.8 STAINLESS STEEL 6-LOBE TRIM SCREWS VIS FINITION À SIX PANS ACIER INOXYDABLE 18,8

**231**  
Series



### CHROME PLATED

OVAL 6-LOBE HEAD 18.8 STAINLESS		
Part No.	Dia x Length	Qty.
231-205	4.2 x 20 mm	25
231-209	4.2 x 30 mm	25
231-213	4.2 x 40 mm	25
231-219	4.2 x 55 mm	25

### BLACK OXIDE

OVAL 6-LOBE HEAD 18.8 STAINLESS		
Part No.	Dia x Length	Qty.
231-206	4.2 x 20 mm	25
231-210	4.2 x 30 mm	25



### CHROME PLATED

PAN 6-LOBE HEAD 18.8 STAINLESS		
Part No.	Dia x Length	Qty.
231-251	4.2 x 20 mm	25
231-257	4.2 x 35 mm	25

### BLACK OXIDE

PAN 6-LOBE HEAD 18.8 STAINLESS		
Part No.	Dia x Length	Qty.
231-252	4.2 x 20 mm	25
231-264	4.2 x 50 mm	25

## STAINLESS GARAGE ASSORTMENT ASSORTIMENT DE GARAGE INOXYDABLE

### No. 020-212

Contains 110 pieces - 8 sizes of Pan and Oval Socket 18.8 Stainless Steel Tapping Screws and 2 sizes of 18.8 Stainless Finishing Washers packed in a transparent plastic box.



020-212

## MARINE FASTENERS MASTER ASSORTMENT ASSORTIMENT GÉNÉRAL D'ATTACHES MARIN

This Master Assortment is ideal for the boat owner for attaching railings, brackets, swivels, posts and other marine equipment and accessories. Each product is fully illustrated on the price coded lid label. Excellent for self-serve sales. Metal box with high-strength, moulded plastic compartments and safety locking lid.

### No. 020-673

Contains 20 sizes of Stainless Steel Tapping Screws, Wood Screws, Machine Screws, Nuts and Finishing Washers.



020-673

## PLASTIC ASSORTMENT KITS ASSORTIMENTS DE PLASTIQUE

### No. 021-600

#### S.S. MARINE KIT #1 BOLTS, NUTS & WASHERS

Contains 514 pieces, 3 types of bolts, 4 types of nuts and 3 types of washers.



021-600

### No. 021-601

#### S.S. MARINE KIT #2 SCREWS, WASHERS & BITS

Contains 648 pieces, 3 types of screws, 2 types of driver bits and washers.



021-601

For more information on Plastic Assortment S.S. Marine Kits No. 021-600 & No. 021-601 please refer to pages 9 & 12.