

**Series
5055****18.8 Stainless Steel
FLAT WASHERS**

SIZE No	SCREW OR BOLT SIZE	PKG QTY	CASE QTY
- 202	#2	100	7500
- 204	#4	100	7500
- 206	#6	100	7500
- 208	#8	100	7500
- 210	#10	100	7500
- 212	#12	100	7500
- 214	1/4	100	7500
- 216	5/16	100	7500
218L	3/8 (1 O.D.)	100	3000
2181S	3/8 (7/8 O.D.)	100	4500

SIZE No	SCREW OR BOLT SIZE	PKG QTY	CASE QTY
- 220	7/16	50	2250
- 222	1/2	50	1500
- 224	5/8	25	1125
- 226	3/4	20	600
- 228	7/8	20	400
- 230	1	20	400
- 232	1 1/8	10	200
- 234	1 1/4	10	200
- 238	1 1/2	10	120

Note: Please use Series and Size No. when ordering:

Example: #2 18.8 Stainless Steel Flat Washers

Series Size No.
5055 -202

Stock Sizes are shown in **HEAVY** type.

**Series
5056****18.8 Stainless Steel
COUNTERSUNK FINISHING
WASHERS**

SIZE No	SCREW OR BOLT SIZE	PKG QTY	CASE QTY
- 971	#6	100	7500
- 973	#8	100	7500
- 975	#10	100	7500


SIZE No	SCREW OR BOLT SIZE	PKG QTY	CASE QTY
- 977	#12	100	4500
- 979	1/4	100	4500
- 981	5/16	100	3000

Note: Please use Series and Size No. when ordering:

Example: #6 18.8 Stainless Steel Countersunk Finishing Washers

Series Size No.
5056 -971

Stock Sizes are shown in **HEAVY** type.

**Series
5057****18.8 Stainless Steel
FENDER WASHERS**

SIZE No	SCREW OR BOLT SIZE	INSIDE DIAMETER	OUTSIDE DIAMETER	THICKNESS	PKG QTY	CASE QTY
- 394	#10	0.203	1"	0.062	100	2400
- 395	1/4	0.281	1-1/4"	0.078	100	1600
- 396	5/16	0.343	1-1/2"	0.078	100	1600
- 398	3/8	0.390	1-1/2"	0.078	100	1600
- 400	1/2	0.562	2"	0.100	50	600

Note: Please use Series and Size No. when ordering:

Example: #10 18.8 Stainless Steel Fender Washers

Series Size No.
5057 -394

Stock Sizes are shown in **HEAVY** type.