

**Commercial Grade  
AC Toggle Switches**

15A, 120/277V/AC; 20A, 120/277V/AC  
Single-Pole, Double-Pole, 3-Way, 4-Way

**AC Toggle Switches, Back & Side Wire**




| Rating<br>A | V/AC    | Description               | Color Suffix    | Catalog No.  |   |   |  |
|-------------|---------|---------------------------|-----------------|--------------|---|---|--|
| 15          | 120/277 | Single-Pole, Toggle       | B, GY, LA, V, W | □ CSB115__   | • | • |  |
|             |         | Single-Pole, Small Toggle | A, LA, V, W     | □ CSB115ST__ | • | • |  |
|             |         | Double-Pole, Toggle       | B, GY, LA, V, W | □ CSB215__   | • | • |  |
|             |         | 3-Way, Toggle             | B, GY, LA, V, W | □ CSB315__   | • | • |  |
|             |         | 3-Way, Small Toggle       | A, B, LA, V, W  | □ CSB315ST__ | • | • |  |
|             |         | 4-Way, Toggle             | B, GY, V, W     | □ CSB415__   | • | • |  |
| 20          | 120/277 | Single-Pole, Toggle       | B, GY, LA, V, W | □ CSB120__   | • | • |  |
|             |         | Double-Pole, Toggle       | B, GY, LA, V, W | □ CSB220__   | • | • |  |
|             |         | 3-Way, Toggle             | B, GY, LA, V, W | □ CSB320__   | • | • |  |
|             |         | 4-Way, Toggle             | B, GY, V, W     | □ CSB420__   | • | • |  |

\* Not NOM Spec.


**AC Toggle Switches, Side Wire**




| Rating<br>A | V/AC    | Description                 | Color Suffix           | Catalog No. |   |   |  |
|-------------|---------|-----------------------------|------------------------|-------------|---|---|--|
| 15          | 120/277 | Single-Pole, Compact Toggle | A, B, BK, GY, LA, V, W | □ CS115__   | • | • |  |
|             |         | Double-Pole, Compact Toggle | B, BK, GY, LA, V, W    | □ CS215__   | • | • |  |
|             |         | 3-Way, Compact Toggle       | B, BK, GY, LA, V, W    | □ CS315__   | • | • |  |
|             |         | 4-Way, Compact Toggle       | B, GY, LA, V, W        | □ CS415__   | • | • |  |
| 20          | 120/277 | Single-Pole, Compact Toggle | A, B, BK, GY, LA, V, W | □ CS120__   | • | • |  |
|             |         | Double-Pole, Compact Toggle | B, BK, GY, LA, V, W    | □ CS220__   | • | • |  |
|             |         | 3-Way, Compact Toggle       | B, BK, GY, LA, V, W    | □ CS320__   | • | • |  |
|             |         | 4-Way, Compact Toggle       | B, GY, LA, V, W        | □ CS420__   | • | • |  |



CSB320



CSB415



CS320

**Accessories for Commercial Specification Grade Switches**

| Description  | Catalog No. |   |
|--|-------------|---|
| 1-Gang, standard size toggle, 302/304 stainless steel wallplate  | □ 93071     | • |
| 2-Gang, standard size toggle, 302/304 stainless steel wallplate  | □ 93072     | • |
| 1-Gang, standard size toggle, unbreakable nylon wallplate, red   | □ 5134RD    | • |
| 2-Gang, standard size toggle, unbreakable nylon wallplate, white | □ 5139W     | • |
| 4-Gang, standard size toggle, unbreakable nylon wallplate, white | □ 5154      | • |



93071



93072



5124RD



5139W



5154

**Color Ordering Information:**

For ordering devices, include Catalog No. followed by the Color Suffix: A (Almond), B (Brown), BK (Black), GY (Gray), LA (Light Almond), V (Ivory), W (White)



**Specification Information:** 120/277V/AC Commercial Toggle: E-41  
Specifications and availability are subject to change without notice.

Indicates NAFTA Compliant - Page R-30

Build-To-Spec Customizable Devices - Page E-6