



## Mid-size screwless wallplates

### Product description


1-Gang, 2-Gang, 3-Gang, 4-Gang, 5-Gang, 6-Gang




1-Gang 2-Gang




3-Gang




4-Gang



5-Gang




6-Gang




1-Gang 2-Gang



3-Gang



4-Gang



1-Gang

### Screwless decorator wallplates

Description	Material	Color suffix	Catalog no.	
1-Gang	Polycarbonate	A, B, BB, BK, GY, LA, V, W	<input type="checkbox"/> PJS26__	•
2-Gang	Polycarbonate	A, B, BB, BK, LA, V, W	<input type="checkbox"/> PJS262__	•
3-Gang	Polycarbonate	A, BB, BK, LA, V, W	<input type="checkbox"/> PJS263__	•
4-Gang	Polycarbonate	A, BK, LA, V, W	<input type="checkbox"/> PJS264__	•
5-Gang	Polycarbonate	A, BK, LA, V, W	<input type="checkbox"/> PJS265__	•
6-Gang	Polycarbonate	A, BK, LA, V, W	<input type="checkbox"/> PJS266__	•

### Toggle wallplates

Description	Material	Color suffix	Catalog no.	
1-Gang	Polycarbonate	A, B, BB, BK, LA, V, W	<input type="checkbox"/> PJS1__	•
2-Gang	Polycarbonate	A, B, BB, BK, LA, V, W	<input type="checkbox"/> PJS2__	•
3-Gang	Polycarbonate	A, LA, V, W	<input type="checkbox"/> PJS3__	•
4-Gang	Polycarbonate	A, LA, V, W	<input type="checkbox"/> PJS4__	•

### Duplex receptacle wallplates

Description	Material	Color suffix	Catalog no.	
1-Gang	Polycarbonate	A, B, BB, BK, LA, V, W	<input type="checkbox"/> PJS8__	•

### Color ordering information:

For ordering devices, include Catalog no. followed by the Color suffix: A (Almond), B (Brown), BB (Brushed Bronze), BK (Black), GY (Gray), LA (Light Almond), V (Ivory), W (White)

A	B	BB	BK	GY	LA	V	W
(Almond)	(Brown)	(Brushed Bronze)	(Black)	(Gray)	(Lt. Almond)	(Ivory)	(White)

**Certification information:** Aspire series wallplates are cULus Listed to UL5154D, file no. E33216; ; PJ series wallplates are cULus Listed.

**Specification information:** K-22

**Compliances, specifications and availability are subject to change without notice.**

RoHS compliant – Page Q-30