

# METALWORKING/ WELDING

## SPATTER-FREE™ **WELDER'S ANTI-SPATTER**

- Prevents spatter from adhering to surrounding metal surfaces during welding
- · Eliminates the need to chisel, grind or wire brush after welding
- Water-based formula allows easy clean-up without the use of solvent cleaners
- Does not contain silicone
- · Contains no ODCs
- · Rust inhibiting additive prevents flash rust on in-process and surrounding metal surfaces
- Non-hazardous decomposition
- Low odor

Part	Container	Units per
Number	Size	Case
73083	397 g Aerosol	12

#### ZINC MATETM

- High-performance coating of >92% pure zinc that electrochemically bonds with ferrous metals to form a galvanic cell. Zinc-Mate is an excellent touch-up for damaged galvanized coatings
- · Actively fights rust and corrosion with a film of >92% pure zinc
- Protects base metal even when scratched. abraded, or dented
- · Fast-drying, dries to the touch in 15 minutes
- · Excellent weldability

Part	Container	Units per
Number	Size	Case
73054*	369 g Aerosol	12
18413	3.785 L Can	1

#### **BRIGHT ZINC-IT®**

- · Epoxy-ester based, light duty sacrificial zinc coating
- Inhibits corrosion and provides high-shine, bright metallic finish
- Excellent touch-up and repair of bright finish. hot-dip galvanized surfaces
- · Protects base metal even when scratched or abraided
- Fast-drying, dries to the touch in 15 minutes

Part	Container	Units per
Number	Size	Case
18414*	369 g Aerosol	12

# TESTING

### SMOKE TEST® BRAND **SMOKE DETECTOR TESTER**

- · Simulates smoke to provide a true, functional test for smoke detectors
- Aerosol spray extends user reach up to 6'. allows testing to be done while standing safely on the floor
- No harmful residue, plastic safe, non-staining
- Contains no Class I or Class II Ozone Depleting Chemicals
- UL<sup>®</sup> Listed

Part	Container	Units per
Number	Size	Case
72105*	71 g Aerosol	12

UL® is a registered trademark of UL LLC.

#### **LEAK DETECTOR**

- Highlights all leaks, even under low pressure
- Non-flammable
- Water-based formula no oils, silicones or harmful solvents
- Aerosol package enables fast and easy application with no waste or spillage
- No odor

Part	Container	Units per
Number	Size	Case
74503	510 g Aerosol	12

# INSECT MANAGEMENT

### **BUG BLAST<sup>TM</sup> WASP & HORNET KILLER**

- Knocks down and kills wasps, hornets, fire ants, scorpions and black widow spiders
- · Contains no chlorinated solvents
- · Safe on most plastics
- CRC trigger provides a dense, accurate spray that will reach over 20 feet to drench harmful insects and their nests
- High dielectric strength of 47,600 volts
- · Extension tube doubles as a locking mechanism

Part	Container	Units per
Number	Size	Case
72010	397 a Aerosol w/ Trigger	12

# HAND CLEANERS

## MECHANIX ORANGE™ CITRUS LOTION HAND **CLEANER WITH PUMICE**

- Formulated with the natural cleaning power of citrus
- · Fast, yet gentle hand cleaner is pH balanced
- · Highly concentrated and very effective at cleaning the toughest soil, grime, ink, oil and paint
- Use with or without water
- · Contains no harsh solvents
- · Biodegradable formula
- · Fortified with pumice for deep cleaning power
- Conditions skin to leave hands feeling clean

Part Number	Container Size	Units per Case
74090	474 mL Bottle	12
74091	3.785 L Bottle w/ Pump	4



<sup>\*</sup>This product is labeled extremely flammable. Read and observe the special usage warning on the label. Do not apply while equipment is energized.