

# BLADES



## FatMax® Snap-Off Blades

- 75% longer life\*
- 35% sharper\*
- 20% stronger\*

\*Than traditional Stanley Snap-Off Blades

SKU #	SIZE	NUMBER OF BLADES	POINTS ON BLADE	LENGTH		THICKNESS	BOX QTY	CARTON QTY	UPC
				IN.	MM				
11-718	18mm	5	8	4-1/4	108	.020	10	50	076174117189
11-718L	18mm	50	8	4-1/4	108	.020	4	24	076174760606
11-718T	18mm	10	8	4-1/4	108	.020	10	50	076174760545
11-725	25mm	5	7	5-1/2	140	.027	6	36	076174117257
11-725L	25mm	50	7	5-1/2	140	.027	2	24	076174760613
11-725T	25mm	10	7	5-1/2	140	.027	4	48	076174760552



## Super Heavy-Duty Quick-Point™ Blades

- Replacement blade for the Stanley® 1" Snap-Off Knife (10-425)
- Fits most 25mm snap-off blade knives

SKU #	SIZE	NUMBER OF BLADES	POINTS ON BLADE	LENGTH		THICKNESS	BOX QTY	CARTON QTY	UPC
				IN.	MM				
11-325	25mm	5	7	5-1/2	140	.027	6	36	076174760385
11-325T	25mm	10	7	5-1/2	140	.027	4	48	076174113259



## Quick-Point™ Blades

- Replacement blade with 8 cutting points
- Fits Stanley® 10-218, 10-480, 10-380, 10-280, 10-220, 10-481 and 10-151 Snap-Off Blade Knives and most other 18mm snap-off blade knives

SKU #	SIZE	NUMBER OF BLADES	POINTS ON BLADE	LENGTH		THICKNESS	BOX QTY	CARTON QTY	UPC
				IN.	MM				
11-301	18mm	3	8	4-1/4	108	.020	10	50	076174113013
11-301K	18mm		8	4-1/4	108	.020	12	48	076174113013
11-301L	18mm	50	8	4-1/4	108	.020	4	24	076174799231
11-301T	18mm	10	8	4-1/4	108	.020	10	100	076174799248

## Snap-Off Hook Blades



- 4 cutting points per blade
- Each snap-off hook blade is equivalent to 2 regular hook blades
- Ideal for cutting asphalt shingles, roofing felt, tar paper

SKU #	SIZE	NUMBER OF BLADES	POINTS ON BLADE	LENGTH		THICKNESS	BOX QTY	CARTON QTY	UPC
				IN.	MM				
11-618	18 mm	5	4	4-1/8	105	.065	10	50	076174116182
11-618L	18mm	20	4	4-1/8	105	.065	5	25	076174760620
11-618T	18mm	10	4	4-1/8	105	.065	10	50	076174760521
11-625	25mm	5	4	5-1/4	132	.065	6	36	076174116250
11-625L	25mm	20	4	5-1/4	132	.065	2	24	076174760637
11-625T	25mm	10	4	5-1/4	132	.065	4	48	076174760538