

Additional Power-Return Rules from Klein



Power-Return Rule – Offset Tape-Stop™

Cat. No.	UPC No. 0-92644+	Blade Length	Width	Weight (lbs.)
915-26	91526-0	16' (5 m)	1" (25 mm)	.61



915-26

Power-Return Steel Rules – Double-Sided

Cat. No.	UPC No. 0-92644+	Blade Length	Width	Weight (lbs.)
908-12	86080-5	12' (3.5 m)	5/8" (16 mm)	.33
908-16	86081-2	16' (5 m)	1" (25 mm)	.60
908-25	86082-9	25' (7.5 m)	1" (25 mm)	.90
908-7.5ME	86084-3	7.5 m (25')	25 mm (1")	.90
908-30	86083-6	30' (9 m)	1" (25 mm)	1.10



908-25

Power-Return Steel Rules – Magnetic Dual-End Hook, Double-Sided Blade

Cat. No.	UPC No. 0-92644+	Blade Length	Width	Weight (lbs.)
918-16RE	86085-0	16' (5 m)	1" (25 mm)	.60
918-25RE	86086-7	25' (7.5 m)	1" (25 mm)	.90
918-7.5ME-RE	86088-1	7.5 m (25')	25 mm (1")	.90
918-30RE	86087-4	30' (9 m)	1" (25 mm)	1.10



918-25RE

Power-Return Steel Rules – Rare Earth Magnetic Tip

Cat. No.	UPC No. 0-92644+	Blade Length	Width	Weight (lbs.)
916-16RE	86076-8	16' (5 m)	1" (25 mm)	.63
916-25RE	86073-7	25' (7.5 m)	1" (25 mm)	.90
916-7.5ME-RE	86078-2	7.5 m (25')	25 mm (1")	.90
916-30RE	86077-5	30' (9 m)	1" (25 mm)	1.10



916-25RE

Klein Tools offers a wide selection of Leather and Nylon Tape Measure Holders, Pouches, Tool Bags, Tool Belts and Tool Belt Accessories.

View the complete selection in our catalog or online @ kleintools.com.

All dimensions are in inches and (millimeters) unless otherwise specified.

▲WARNING:

- Always wear approved eye protection.
- Protect hands when cleaning magnetic tip. Use gloves or cloth.
- Avoid magnetic contact with sensitive electronic or computer equipment.
- NOT insulated. Do NOT use on live circuits.

▲WARNING:

- To avoid personal injury and damage to this tool, do not allow the tape blade to retract into case at full speed.
- Do NOT open case. Spring motor is under tension, and opening case may cause injury.