
Service entrance masts and accessories




Service entrance masts and accessories

	Std.	lb/kg	Cat ===	Reference
Description 11/2 Fataras and 1004	pkg.	100 pcs	Cat. no.	no.
	20	105/47.1	MM104	1
- · · · · · · · · · · · · · · · · · · ·	10	130/59	MM105	_
•	10	200/90	MM202	
,	50	50/22.7	MM380	2
	50	50/22.7	MM380A	
3 : : : 5 : : : : : : : : : : : : : : :	20	125/56	MM101	3
3 31 3	20	164/74	MM5101	-
	10	300/136	MM201	_
	10	360/163	MM801	
•	50	50/22.7	MM390	4
	20	100/45.4	MM300	5
	50	14/6.3	MM500	6
	20	36/16.3	MM501	
	10	150/68	MM502	7
Roof flange, comes with steel collar	10	180/81	MM503	8
Roof flange, comes with neoprene colla	10	140/63	MM505N	
Roof flange, comes with neoprene collar 1¼ in	10	140/63	MM5505N	
⅓ in. dia. "U" bolt mast clamp	20	125/56	MM250	9
Pipe strap, comes with two ¾ in. x 4 in. lag screws	50	40/18.1	MM251	10
Pipe strap, comes with two ¾ in. x 5 in. lag screws	50	40/18.1	MM255	
Pipe strap only, no lag screws	50	30/13.6	MM252	
Support clamp, comes with % in. x 10 in. fully threaded bolt and 4 in. x 4 in. square washer	20	225/102	MM400	11
Clamp only, no bolt and washe	20	110/50	MM401	
Support clamp, comes with % in. x 4½ in. fully threaded bolt and 4 in. x 4 in. square washer	20	215/97	MM445	
Support clamp, comes with ⅓ in. x 10 in. bolt	20	215/97	MM5400	-
8 ft. x 2½ in. outside diameter masi	50	2,800/1272	MM8	12
9 ft. x 2½ in. outside diameter masi	50	3,300/1500	мм9см	-
10 ft. x 2½ in. outside diameter masi	50	3,500/1590	MM10	-
	50	4,200/1909	MM12	-
	20	235/106	MM600	13
	20	190/86	MM601	
Spacer only (less strap, bolt and washer) (suggested for brick applications with MM201 less pipe strap)	20	150/68	MM602	-
	20	119/54	MM602LD	-
5 5	20	200/90	MM603	-
	25	36/16.3	MM100	14
	25	44/20	MM140	-
1¼ in. Male reduce	25	44/20	MM140M	-
				-
1½ in. Female reduce	25	44/20	MM150	-
	25	44/20	MM150M	_
	25	44/20	MM200	-
	25	44/20	MM200M	
·	1	40/18	MH200	15
· · ·	10	103/46.82	MH40	
<u> </u>	10	52/23.6	MM506N	16
· · · · · · · · · · · · · · · · · · ·	10	100/45	MM806N	
	10	93/42.3	MM507DN	17
	10	150/68	MM604	18
	25	50/22.7	MM605	19
Service mast ground clamp, wire range: 8–1/0 AWG	50	85/38.6	MM700	20
2 in. Entrance cap for old style 2¾ in. service masts	10	200/90	MM202P	21
4 in. entrance head	11	590/268	CIEFA-4	
2 in. Female reducer for old style 2% in. service masts	20	44/20	MM200P	22
2½ in. one-piece coupler (check the installation standards in your region before using the product)	30	45/21	MC250	23

Service Masts

Guy kits for 2½ in. masts

Descriptio	Consists of	Qty.	Cat. no.
			¼ in. Guy kit
Mast guy attachmen	MM380	1	MM914
Guy thimble	GT516	2	
Guy en	GE14	1	
20 ft. of ¼ in. guy wir	GW14110	1	
Guy clam	GC902	1	
Roof bracke	RB404	1	
Lag screv	T404-CM	1	
			5⁄16 in. Guy kit
Mast guy attachmen	MM380	1	MM9516
Guy thimbl	GT516	1	
Guy en	GE516	1	
20 ft. of ⁵⁄16 in. guy wir	GW516110	1	
Guy clam	GC902	1	
5⁄8 in. x 12 in. Bent thimble eye bo	BTE512	1	
Round washe	RA725	1	



Mast kits suitable for British Columbia

Descriptio	Consists of	Qty.	Cat. No.
Entrance ca	MM104	1	KIT-100BCMH
Light-duty rac	MM101	1	
Flange comes with neoprene colla	MM505N	1	
"U" bolt clam	MM250	3	
Mast couple	MH200	1	
Entrance ca	MM104	1	KIT-100BCMN
Light-duty rac	MM101	1	
Flange comes with neoprene colla	MM505N	1	
"U" bolt clam	MM250	3	
1¼ In. Female reduce	MM140	1	
Entrance ca	MM104	1	MMK1-NMH
Light-duty rac	MM101	1	
Flange comes with neoprene colla	MM505N	1	
Support clam	MM400	3	
Mast couple	MH200	1	
Entrance ca	MM202	1	KIT-200BCMH
Heavy-duty rac	MM201	1	
Flange comes with neoprene colla	MM505N	1	
"U" bolt clam	MM250	3	
Mast couple	MH200	1	
Entrance ca	MM202	1	MMK2-NMH
Heavy-duty rac	MM201	1	
Flange comes with neoprene colla	MM505N	1	
Support clam	MM400	3	
Mast couple	MH200	1	

Service masts

Mast kits suitable for Alberta

KIT-1 1/4 – 100 A

	Cat. no.	Qty.	Consists of	Description
	This mast kit is used in c	onjunction with 1¼ in.	rigid conduit	
KIT-1 1/4	KIT-1 1/4	1	MM5104A	1¼ in. Throat entrance cap
		1	MM5101	Light-duty spool rack
		1	MM5505N	Roof flange complete with neoprene collar
The state of the s		1	MM5400	Support clamp complete with ½ in. x 10 in. bolt

KIT2-CM - 100 A

Description	Consists of	Qty.	Cat. no.
	gid conduit	junction with 2 in. rig	This mast kit is used in co
2 in. Throat entrance cap	CIEFSA-2	1	KIT2-CM
Light-duty spool rack	MM5101	1	
Roof flange complete with neoprene collar	MM505N	1	
Support clamp complete with ½ in. x 10 in. bolt	MM5400	2	
1¼ in. Bottom female reducer	MM5140	1	

____ KIT-2-AL – 200 A

Consists of	Qty.	Cat. no.	
MM202	1	KIT-2-AL	KIT-2-AL
MM5101	1		
MM505N	1		
MM5400	2		
MM200M	1		
	MM202 MM5101 MM505N MM5400	1 MM202 1 MM5101 1 MM505N 2 MM5400	KIT-2-AL 1 MM202 1 MM5101 1 MM505N 2 MM5400

MB-110 – 100 A

Cat. no.	Qty.	Consists of	Description
MB-110	1	MM104	1¼ in. Entrance cap
	1	MM201	Heavy-duty spool rack
	1	MM505N	Roof flange complete with neoprene collar
	3	MM400	Support clamp complete with $\%$ in. x 10 in. fully threaded bolt and 4 x 4 washer
6. 00 a	1	MM140	1¼ in. Female reducer

Mast kits suitable for Manitoba and Saskatchewan

Descriptio	Consists of	Qty.	Cat. no.
Entrance ca	MM104	1	KIT-100MJ
1¼ in. Reduce	MM140M	1	
Light-duty rac	MM101	1	
Flange complete with neoprene colla	MM505N	1	
Strap complete with ¾ in. x 4 in. Lag bo	MM251	2	
Support clam	MM400	1	
Entrance ca	MM104	1	KIT-100MN
1¼ in. Reduce	MM140M	1	
Light-duty rac	MM101	1	_
Flange complete with neoprene colla	MM505N	1	_
Strap complete with ¾ in. x 5 in. lag bo	MM255	3	
Entrance ca	MM104	1	KIT-100MH
Light-duty rac	MM101	1	_
Flange complete with neoprene colla	MM505N	1	_
Strap complete with ¾ in. x 4 in. lag bo	MM251	3	
Mast couple	MH200	1	
Entrance ca	MM202	1	KIT-200AM
Heavy-duty rac	MM201	1	_
2 in. Male reduce	MM200M	1	
Flange complete with neoprene colla	MM505N	1	
Strap complete with % in. x 5 in. lag bo	MM255	3	
Entrance ca	MM202	1	KIT-200MH
Heavy-duty rac	MM201	1	
Flange complete with neoprene colla	MM505N	1	_
Strap complete with ¾ in. x 5 in. lag bo	MM255	3	_
Mast couple	MH200	1	_
Entrance ca	MM202	1	KIT-200MJ
2 in. Male reduce	MM200M	1	_
Heavy-duty rac	MM201	1	
Flange complete with neoprene colla	MM505N	1	
Strap complete with ¾ in. x 4 in. lag bo	MM251	1	_
Support clam	MM400	1	_
Entrance ca	MM202	1	MMK2-NMH
Heavy-duty rac	MM201	1	_
Flange complete with neoprene colla	MM505N	1	_
Support clam	MM400	3	_
Mast couple	MH200	1	_

Service masts

Mast kits suitable for Ontario

Cat. no.	Qty.	Consists of	Description
KIT-100HDM	1	MM104	Entrance cap
	1	MM140M	1¼ in. Male reducer
	1	MM201	Heavy-duty rack
	1	MM503	Flange complete with steel collar
	3	MM255	Strap complete with
			¾ in. x 5 in. lag bolts
KIT-100MH	1	MM104	Entrance cap
	1	MM101	Light-duty rack
	1	MM505N	Flange complete with neoprene collar
	3	MM251	Strap complete with ¾ in. x 4 in. lag bolt
	1	MM200	Female reducer
KIT-100MN	1	MM104	Entrance cap
	1	MM140M	1¼ in. Male reducer
	1	MM101	Light-duty rack
	1	MM505N	Flange complete with neoprene collar
	3	MM255	Strap complete with % in. x 5 in. lag bolt
KIT-100NMH	1	MM104	Entrance cap
	1	MM101	Light-duty rack
	1	MM505N	Flange complete with neoprene collar
	1	MM400	Support clamp
	1	MM200	Female reducer
MMK1	1	MM104	Entrance cap
	1	MM101	Light-duty rack
	1	MM140M	1¼ in. Male reducer
	1	MM503	Flange complete with steel collar
	3	MM400	Support clamp
MMK-1N	1	MM104	Entrance cap
	1	MM101	Light-duty rack
	1	MM505N	Flange complete with neoprene collar
	3	MM400	Support clamp
	1	MM140M	1¼ in. Male reducer
MMK1-NMH	1	MM104	Entrance cap
	1	MM101	Light-duty rack
	1	MM505N	Flange complete with neoprene collar
	3	MM400	Support clamp
	1	MH200	Mast coupler
KIT-200MH	1	MM202	Entrance cap
	1	MM201	Heavy-duty rack
	1	MM200M	2 in. Male reducer
	1	MM505N	Flange complete
	3	MM255	with neoprene collar Strap complete with
		1-11-12-33	% in. x 5 in. lag bolt

Cat. no.	Qty.	Consists of	Description
KIT-200AM	1	MM202	Entrance cap
	1	MM201	Heavy-duty rack
	1	MM505N	Flange complete with neoprene collar
	3	MM255	Strap complete with ¾ in. x 5 in. lag bolt
	1	MH200	Mast coupler
KIT-200NMH	1	MM202	Entrance cap
	1	MM201	Heavy-duty rack
	1	MM505N	Flange complete with neoprene collar
	3	MM400	Support clamp
	1	MM200	Female reducer
MMK2	1	MM202	Entrance cap
	1	MM201	Heavy-duty rack
	1	MM200M	2 in. Male reducer
	1	MM503	Flange complete with steel collar
	3	MM400	Support clamp
MMK-2N	1	MM202	Entrance cap
	1	MM201	Heavy-duty rack
	1	MM505N	Flange complete with neoprene collar
	3	MM400	Support clamp
	1	MM200M	2 in. Male reducer
MMK2-NMH	1	MM202	Entrance cap
	1	MM201	Heavy-duty rack
	1	MM505N	Flange complete with neoprene collar
	3	MM400	Support clamp
	1	MH200	Mast coupler

Mast kits suitable for Quebec

Cat. no.	Qty.	Consists of	Description
KIT-100MN	1	MM104	Entrance cap
	1	MM140M	1¼ in. Male reducer
	1	MM101	Light-duty rack
	1	MM505N	Flange complete
			with neoprene collar
	3	MM255	Strap complete with $\frac{3}{6}$ in. x 5 in. lag bolts
KIT-100MH	1	MM104	Entrance cap
	1	MM101	Light-duty rack
	1	MM505N	Flange complete with neoprene collar
	3	MM251	Strap complete with 3/6 in. x 4 in. lag bolts
	1	MH200	Mast coupler
KIT-100MNF	1	MM104	Entrance cap
	1	MM140M	1¼ in. Male reducer
	1	MM101	Light-duty rack
	3	MM251	Strap complete with % in. x 4 in. lag bolts
KIT-150AM	1	MM105	1½ in. entrance cap
	1	MM201	Heavy-duty rack
	1	MM505N	Flange complete with neoprene collar
	3	MM251	Strap complete with % in. x 4 in. lag bolts
	1	MM150M	1½ in. Male adaptor
KIT-200AM	1	MM202	Entrance cap
	1	MM201	Heavy-duty rack
	1	MM200M	2 in. Male reducer
	1	MM505N	Flange complete with neoprene collar
	3	MM255	Strap complete with % in. x 5 in. lag bolts
KIT-200AMGR	1	MM202	Entrance cap
	1	MM201	Heavy-duty rack
	1	MM200M	2 in. Male reducer
	1	MM505N	Flange complete with neoprene collar
	3	MM255	Strap complete with 3/8 in. x 5 in. lag bolts
	1	MM700	Service mast ground clamp
KIT-200MH	1	MM202	Entrance cap
	1	MM201	Heavy-duty rack
	1	MM505N	Flange complete
			with neoprene collar
	3	MM255	Strap complete with % in. x 5 in. lag bolts
	1	MH200	Mast coupler

Cat. no.	Qty.	Consists of	Description
KIT-100HDM	1	MM104	Entrance cap
	1	MM140M	1¼ in. Male reducer
	1	MM201	Heavy-duty rack
	1	MM503	Flange complete with steel collar
	3	MM255	Strap complete with % in. x 5 in. lag bolts
KIT-200-PVC	1	SS401-E	Spool rack
	1	E998J	2 in. Entrance cap
	3	E977JC	2 in. Strap
	1	PH20	2 in. Hub PVC
	2	E943J	2 In. Male adaptor
	2	CI1716	2 in. Locknut
	1	E986J	2 in. LB type
	1	CIDUCT1	Duct seal
	1	UA9AJCB-UPC	2 in. PVC elbow
KIT-200AM-CP	1	MM202	2 in. Entrance cap
	1	MM201	Spool rack
	1	MM505N	Floor flange
	1	MM200M	2 in. Male reducer
	3	MM251	Strap complete with % in. x 4 in. lag bolts
	2	E943J	2 in. Male adaptor
	2	CI1716	2 in. Locknut
	1	E986J	2 in. Entrance cap
	1	DUCT SEAL	Duct seal
	1	UA9AJCB-UPC	2 in. PVC elbow
KIT-200MH-CP	1	MM202	2 in. Entrance cap
	1	MM201	Spool rack
	1	MM505N	Roof flange
	1	MH200	2 in. Mast coupler
	3	MM251	Strap complete with % in. x 4 in. lag bolts
	2	E943J	2 in. Male adaptor
	2	CI1716	2 in. Locknut
	1	E986J	2 in. Entrance cap
	1	CIDUCT1	Duct seal
	1	UA9AJCB-UPC	2 in. PVC elbow

Service masts

Mast kits suitable for Quebec and for all regions

KIT-200-PVC - Quebec

	Cat. no.	Qty.	Consists of	Description
	This mast kit rigid conduit	is used	d in conjunction	with 2 in.
	KIT-200-PVC	1	SS401-E	Spool rack
		1	E998J	2 in. Entrance cap
		3	E977JCIM	2 in. Strap
		1	PH20	2 in. Hub PVC
		2	E943J	2 in. Male adaptor
		2	CI1716	2 in. Locknut
		1	E986J	2 in. LB type
		1	CIDUCT1	Duct seal
		1	UA9AJCB-UPC	2 in. PVC elbow

KIT-200AM-CP – Quebec

	Cat. no.	Qty.	Consists of	Description
	This mast kit is rigid conduit	s used i	n conjunction	with 2 in.
.0	KIT-200AM-CP	1	MM202	2 in. Entrance cap
		1	MM201	Spool rack
3000		1	MM505N	Roof flange
		1	MM200M	2 in. Male reducer
		3	MM251	2 in. Pipe strap (comes with lag screws)
		2	E943J	2 in. Male adaptor
		2	CI1716	2 in. Locknut
		1	E986J	2 in. Entrance cap
		1	CIDUCT1	Duct seal
		1 U	A9AJCB-UPC	2 in. PVC elbow

KIT-200MH-CP - Quebec

	Cat. no.	Qty.	Consists of	Description
0	KIT-200MH-CP	1	MM202	2 in. Entrance cap
	1	1	MM201	Spool rack
3000		MM505N	Roof flange	
		1	MH200	2 in. Mast coupler
		3	MM251	2 in. Pipe strap, comes with lag screws ¾ x 4 in.
	2	E943J	2 in. Male adaptor	
	-	2	CI1716	2 in. Locknut
	-	1	E986J	2 in. Entrance cap
	-	1	CIDUCT1	Duct seal
	-	1	UA9AJCB- UPC	2 in. PVC elbow

KIT-400MH – For all regions

	Cat. no.	Qty.0	Consists of	Description
	This mast kit rigid conduit		in conjunct	ion with 4 in.
C. C.	KIT-400MH	1	CIEFA-4	4 in. Entrance head
Control of the	3	1	MM801	Heavy-duty spool rack
		1	MM806N	Roof flange
		1	MH40	4 in. Mast coupler
		3	CI1532	Pipe strap comes with lag screws (6) 3% x 5 in.

Mast kits suitable for New Brunswick and Newfoundland

New Brunswick

Cat. no.	Qty.	Consists of	Description
KIT-100	1	MM104	Entrance cap
	1	MM140M	1¼ in. Male reducer
	3	MM251	Strap complete with % in. x 4 in. lag bolts
	1	MM505N	Flange complete with neoprene collar
KIT-100NBMH	1	MM104	Entrance cap
	3	MM251	Strap complete with % in. x 4 in. lag bolts
	1	MH200	Mast coupler
	1	MM505N	Flange complete with neoprene collar
KIT-200	1	MM202	Entrance cap
	1	MM200M	2 in. Male reducer
	3	MM251	Strap complete with % in. x 4 in. lag bolts
	1	MM505N	Flange complete with neoprene collar
KIT-200MH	1	MM202	Entrance cap
	1	MM201	Heavy-duty spool rack
	1	MH200	Mast coupler
	3	MM255	Strap complete with % in. x 5 in. lag bolts
	1	MM505N	Flange complete with neoprene collar
KIT-206NBMH	1	MM202	Entrance cap
	1	MH200	Mast coupler
	3	MM251	Strap complete with % in. x 4 in. lag bolts
	1	MM506N	All-neoprene roof flange
KIT-200NBMH	1	MM202	Entrance cap
	1	MH200	Mast coupler
	3	MM251	Strap complete with % in. x 4 in. lag bolts
	1	MM505N	Flange complete with neoprene collar
KIT-106NBMH	1	MM104	Entrance cap
	1	MM506N	All neoprene roof flange
	3	MM251	Strap complete with % in. x 4 in. lag bolts
	1	MH200	Mast coupler

Newfoundland

Cat. no.	Qty.	Consists of	Description
KIT-100MH	1	MH200	Mast coupler
	1	MM104	Entrance cap
	1	MM101	Light-duty spool rack
	3	MM251	Strap complete with % in. x 4 in. lag bolts
	1	MM505N	Flange complete with neoprene collar
KIT-100NBMH	1	MM104	Entrance cap
	3	MM251	Strap complete with 3⁄6 in. x 4 in. lag bolts
	1	MH200	Mast coupler
	1	MM505N	Flange complete with neoprene collar
KIT-205LDMH	1	MM202	Entrance cap
	1	MM101	Light-duty spool rack
	3	MM251	Strap complete with % in. x 4 in. lag bolts
	1	MH200	Mast coupler
	1	MM505N	Flange complete with neoprene collar

Service masts

Mast kits suitable for Nova Scotia and Prince Edward Island

Nova Scotia

Cat. no.	Qty.	Consists of	Description
KIT-100MN	1	MM104	Entrance cap
	1	MM140M	1¼ in. Male reducer
	1	MM101	Light-duty spool rack
	3	MM255	Strap complete with ¾ in. x 5 in. lag bolts
	1	MM505N	Flange complete with neoprene collar
KIT-100	1	MM104	Entrance cap
	1	MM140M	1¼ in. Male reducer
	3	MM251	Strap complete with 3/8 in. x 4 in. lag bolts
	1	MM505N	Flange complete with neoprene collar
KIT-100NSMH	1	MM104	Entrance cap
	4	MM251	Strap complete with 3/8 in. x 4 in. lag bolts
	1	MM505N	Flange complete with neoprene collar
	1	MH200	Mast coupler
KIT-200AM	1	MM202	Entrance cap
	1	MM201	Heavy-duty spool rack
	3	MM255	Strap complete with 3/6 in. x 5 in. lag bolts
	1	MM200M	2 in. Male reducer
	1	MM505N	Flange complete with neoprene collar
KIT-200	1	MM202	Entrance cap
	1	MM200M	2 in. Male reducer
	3	MM251	Strap complete with 3/6 in. x 4 in. lag bolts
	1	MM505N	Flange complete with neoprene collar
KIT-200NSMH	1	MM202	Entrance cap
	1	MH200	Mast coupler
	3	MM251	Strap complete with ¾ in. x 4 in. lag bolts
	1	MM505N	Flange complete with neoprene collar

Prince Edward Island

Cat. no.	Qty.	Consists of	Description
KIT-100MH	1	MM104	Entrance cap
	1	MM101	Light-duty spool rack
	3	MM251	Strap complete with 3⁄4 in. x 4 in. lag bolts
	1	MM505N	Flange complete with neoprene collar
	1	MH200	Mast coupler
KIT-106NBMH	1	MM104	Entrance cap
	3	MM251	Strap complete with 36 in. x 4 in. lag bolts
	1	MH200	Mast coupler
	1	MM506N	All-neoprene roof flange
KIT-200MH	1	MM202	Entrance cap
	1	MM201	Heavy-duty spool rack
	1	MH200	Mast coupler
	3	MM255	Strap complete with % in. x 5 in. lag bolts
	1	MM505N	Flange complete with neoprene collar
KIT-200NBMH	1	MM202	Entrance cap
	1	MH200	Mast coupler
	3	MM251	Strap complete with % in. x 4 in. lag bolts
	1	MM505N	Flange complete with neoprene collar
KIT-206NBMH	1	MM202	Entrance cap
	1	MH200	Mast coupler
	3	MM251	Strap complete with % in. x 4 in. lag bolts
	1	MM506N	All-neoprene roof flange