

ROD ACTUATOR FOR POSITION SWITCH 3SE51/52 PLASTIC  
ROD 200MM, FORM D DIAMETER 6MM W. TERMINAL



<b>Product designation</b>	actuator for part-turn actuator
<b>Manufacturer's article number</b>	
<ul style="list-style-type: none"> <li>of the supplied operating lever</li> </ul>	<a href="#">3SE5000-0AA82</a>

**General technical data:**

<b>Product function</b>	No
<ul style="list-style-type: none"> <li>positive opening</li> </ul>	
<b>Protection class IP</b>	IP65/IP67
<b>Shock resistance</b>	
<ul style="list-style-type: none"> <li>acc. to IEC 60068-2-27</li> </ul>	30 g / 11 ms
<b>Vibration resistance</b>	
<ul style="list-style-type: none"> <li>acc. to IEC 60068-2-6</li> </ul>	0.35 mm/5g
<b>Mechanical service life (switching cycles)</b>	
<ul style="list-style-type: none"> <li>typical</li> </ul>	15 000 000
<b>Equipment marking</b>	
<ul style="list-style-type: none"> <li>acc. to DIN EN 61346-2</li> </ul>	T
<ul style="list-style-type: none"> <li>acc. to DIN EN 81346-2</li> </ul>	T
<b>Active principle</b>	mechanical

**Enclosure:**

Coating of the enclosure	Other types
--------------------------	-------------

### Drive Head:

Shape of the switch head	rod
Outer diameter of the switch head	6 mm

### Communication/ Protocol:

Design of the interface	without
-------------------------	---------


### Ambient conditions:

<b>Ambient temperature</b>	
<ul style="list-style-type: none"> <li>during operation</li> <li>during storage</li> </ul>	-25 ... +85 °C -40 ... +90 °C

### Installation/ mounting/ dimensions:


Mounting position	any
Mounting type	screw fixing

### Certificates/approvals

General Product Approval	Declaration of Conformity	Test Certificates	other
 CSA	 UL		 EG-Konf.
		<a href="#">spezielle Prüfbescheinigungen</a> <a href="#">n</a>	<a href="#">Bestätigungen</a>

### Further information

- Information- and Downloadcenter (Catalogs, Brochures,...)**  
<http://www.siemens.com/industrial-controls/catalogs>
- Industry Mall (Online ordering system)**  
<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=3SE50000AA82>
- Cax online generator**  
<http://support.automation.siemens.com/WW/CAXorder/default.aspx?lang=en&mlfb=3SE50000AA82>
- Service&Support (Manuals, Certificates, Characteristics, FAQs,...)**  
<https://support.industry.siemens.com/cs/ww/en/ps/3SE50000AA82>
- Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...)**  
[http://www.automation.siemens.com/bilddb/cax\\_de.aspx?mlfb=3SE50000AA82&lang=en](http://www.automation.siemens.com/bilddb/cax_de.aspx?mlfb=3SE50000AA82&lang=en)



last modified:

11.03.2016