



## Conveniently control your lights or appliances from anywhere

WWP10

Conveniently control your lights and power from anywhere using the Legrand Smart Lights mobile app, Amazon Alexa, the Google Assistant, and other popular control platforms. In the app, use Scenes to create the perfect ambiance in your home. With automated schedules, sync your lights with sunrise and sunset, or program to simulate occupancy while you're away. Legrand dimmers also use less energy than ordinary switches, with automated options available to promote enhanced energy savings.

Ideal for residential and light commercial applications, the Smart Wi-Fi radiant switch is the simple solution to all your customers' smart lighting requirements.




Android is a trademark of Google LLC.



## FEATURES & BENEFITS

- Plug into an open outlet and smart enable any lamp, small appliance or motor up to 1/2 HP
- Works with iOS and Android smart phones for control while at home or halfway around the world
- Schedule lights on/off automatically, group lights, and create Scenes
- Perfect for lamps, fans, coffee makers, and more
- Works with motors up to 1/2 HP
- White LED locator light glows when device is off for easy location in the dark
- Wi-Fi switch is compatible with other standards and has an app available on Android and Apple
- Additional compatibility is Works with Google, Works with Amazon, Its OCF certified, Wi-Fi Certified

## COMPLIANCE

 cULus Listed, UL916. File E495025  
FCC Class B Part 15, IC. Works with Alexa  
Works with the Google Assistant, OCF Certified, Wi-Fi Certified

RoHS Compliant



## ORDERING INFORMATION

CATALOG NUMBER	DESCRIPTION	RATING	NEMA	COMPLIANCE	COLORS	COO
WWP10CCV2	Smart Plug-In Switch, Wi-Fi	Incandescent /halogen 1800W, Ballast 15A standard/electronic, LED 5A, 1/2 HP motor	5-15R, 120V		White	China

## VERTICAL MARKETS

- Residential

## COMPATIBILITY



OPEN CONNECTIVITY  
FOUNDATION™



## DOWNLOAD THE APP



**Smart Light**



Download the  
iOS Legrand app



Download  
the Google  
Legrand app

TECHNICAL SPECIFICATIONS

**3rd Party Compliance**

cULus Listed, UL916. File E495025  
 FCC Class B Part 15, IC. Works with Alexa  
 Works with the Google Assistant, OCF Certified, Wi-Fi Certified.


**Performance**

**ELECTRICAL**

Supply Voltage	120 VAC
Maximum Rated Load	Incandescent /halogen 1800W, Ballast 15A standard/ electronic, LED 5A, 1/2 HP motor
Frequency	60Hz
Installation	Single-Pole or 3-Way

**MECHANICAL**

Enclosure Material	Indoor Use Only
--------------------	-----------------



**Materials**

Paddle	Polycarbonate	Terminal	Brass
Back Body	Polycarbonate		

**App**

Android Requirements	Android 5.0 or higher with camera
Apple IOS Requirements	iOS 10.0 or higher with camera

**Radio**

Wi-Fi	Certified IEEE802.11 b/g/n Wi-Fi® 2.4GHz radio. Supports IPv6 addressing to conform to EU standards.
-------	---

**Warranty**

Limited Lifetime Warranty