


Conveniently dim your lights from anywhere

WWRL50xx

Conveniently control your lights and power from anywhere using the Legrand Smart Lights mobile app, Amazon Alexa, the Google Assistant, and other popular control platforms. In the app, use Scenes to create the perfect ambiance in your home. With automated schedules, sync your outdoor lights with sunrise and sunset, or program to simulate occupancy while you're away. Legrand dimmers also use less energy than ordinary switches, with automated options available to promote enhanced energy savings.


Ideal for residential and light commercial applications, the Smart Tru-Universal Dimmer, Wi-Fi is the simple solution to all your customers' dimming challenges.



FEATURES & BENEFITS

- **Simple Calibration via android and iOS apps allows users to set the dimmer to virtually any 120V dimmable load**
- **Convenient operation combines On/Off Decorator switch**
- **Touch rocker for simple dimming operation**
- **Preset, Single-Pole and 3-Way operation**
- **Sleek, ergonomic design that matches today's styles**
- **Works with iOS and Android smart phones for control while at home or halfway around the world**
- **White LED locator light glows when device is off for easy location in the dark**
- **Works with virtually any dimmable lamp and load on typical residential and light commercial wiring (with the exception of 0-10V LED drivers)**

COMPLIANCE

 cULus Listed, UL1472, CSA-C22.2 No. 184.1-95.
Conforms to NEMA WD-1 and WD-6. FCC Class B Part 15, IC. Works with Alexa
Works with the Google Assistant, OCF Certified, Wi-Fi Certified.

RoHS Compliant.



ORDERING INFORMATION

| CATALOG NUMBER | DESCRIPTION | RATING | NEMA | COMPLIANCE | COLORS | COO |
|----------------|---|---|---------------|------------|----------------------------|-------|
| WWRL50WHCCV2 | Smart Tru-Universal Dimmer, Wi-Fi. Preset Single-Pole & 3-Way up to 50 Feet with HMR Remote | Fwd: 700W Inc/ELV 4.5A EFL/CFL/LED 500VA MLV REV. 450W INC/ELV 2.1A EFL/CFL/LED | 120 VAC, 60Hz | | White | China |
| WWRL50LACCV2 | Smart Tru-Universal Dimmer, Wi-Fi. Preset Single-Pole & 3-Way up to 50 Feet with HMR Remote | Fwd: 700W Inc/ELV 4.5A EFL/CFL/LED 500VA MLV REV. 450W INC/ELV 2.1A EFL/CFL/LED | 120 VAC, 60Hz | | Light Almond | China |
| WWRL50NICCV2 | Smart Tru-Universal Dimmer, Wi-Fi. Preset Single-Pole & 3-Way up to 50 Feet with HMR Remote | Fwd: 700W Inc/ELV 4.5A EFL/CFL/LED 500VA MLV REV. 450W INC/ELV 2.1A EFL/CFL/LED | 120 VAC, 60Hz | | Nickel | China |
| HMRTC | Multi-Location Remote Single-Pole, 3-Way | N/A | 120VAC, 60Hz | | Ivory, White, Light Almond | China |
| HMRW | Multi-Location Remote Single-Pole, 3-Way | N/A | 120VAC, 60Hz | | White | China |
| HMRKITLA | Multi-Location Remote Dimmer, Interchangeable Faceplate | N/A | | | Light Almond | China |
| HMRKITNI | Multi-Location Remote Dimmer, Interchangeable Faceplate | N/A | | | Nickel | China |
| HMRKITW | Multi-Location Remote Dimmer, Interchangeable Faceplate | N/A | | | White | China |

COMPATIBILITY



OPEN CONNECTIVITY FOUNDATION™



DOWNLOAD THE APP



Smart Light



Download the iOS Legrand app



Download the Google Legrand app

TECHNICAL SPECIFICATIONS

3rd Party Compliance

cULus Listed, UL1472, CSA-C22.2 No. 184.1-95.
 Conforms to NEMA WD-1 and WD-6. FCC Class B Part 15, IC. Works with Alexa
 Works with the Google Assistant, OCF Certified, Wi-Fi Certified.

Performance

ELECTRICAL

| | |
|--------------------|---|
| Supply Voltage | 120 VAC |
| Maximum Rated Load | FWD: 700W INC/ELV, 4.5A EFL/CFL/LED, 500VA MLV REV: 450W INC/ELV, 2.1A EFL/CFL/LED |
| Frequency | 60Hz |
| Installation | Single-Pole or 3-Way |

MECHANICAL

| | |
|--------------------|-----------------|
| Enclosure Material | Indoor Use Only |
|--------------------|-----------------|

Materials

| | | | |
|-----------|---------------|-------------|---|
| Paddle | Polycarbonate | Termination | 6" long, 14 AWG, 105C 600V stranded wires |
| Back Body | Polycarbonate | | |

App


| | |
|------------------------|-----------------------------------|
| Android Requirements | Android 5.0 or higher with camera |
| Apple IOS Requirements | iOS 10.0 or higher with camera |

Radio


| | |
|-------|---|
| Wi-Fi | Certified IEEE 802.11 b/g/n Wi-Fi 2.4GHz radio. Supports IPv4 and IPv6 addressing. |
|-------|---|

Warranty

Limited Lifetime Warranty



WWRL50WH



HMRW

VERTICAL MARKETS

- Residential