


Pivot Adjustment allows user to position the ratchet mechanism to clear bandana knots and pony-tails.



Replaceable, Top Comfort Pad
Sweat-wicking and breathable padding with anti-microbial and odor control materials; machine washable. Prevents straps from digging into your head.
(Replacement part # KHHTOPPAD)



Ratchet Adjustment – Large knob mechanism allows for easy one-hand adjustment, even with gloves on.



Rear Neck Pad
Soft, non-slip rear pad provides excellent cushion and grip.

Flexible, Open-Frame Design
allows suspension to conform to user's head, provides optimal fit, and improved ventilation.

Multi-Point Adjustment
allows user to choose the best position for enhanced fit and comfort.

Replaceable, Sweatband
Front and side coverage; sweat-wicking and breathable padding with anti-microbial and odor control materials; machine washable.
(Replacement part # KHHSWTBND)

Chin Strap Attachment Points
Chin Strap is sold separately.
(#KHHSTRP)

From a culture of innovation and customer obsession, Klein Tools Hard Hats were designed and engineered to address the long-ignored hard hat dissatisfaction with comfort and proper fit. Developed with a focus on optimal safety, comfort and fit, these hard hats are equipped with unique features to enhance user experience in demanding jobsite environments. Long-term comfort and proper fit are achieved with an adjustable, flexible, open-frame suspension that hugs your head for a secure fit, coupled with a padded, sweat-wicking band and replaceable top pad. Vented models add further comfort with large adjustable vents to improve air circulation. All models feature patent pending accessory mounts on the front and back to easily and precisely attach Klein Tools' exclusive Jobsite Headlamps—no straps needed!

**CAUTION
HARD HAT
AREA**

NON-VENTED CLASS E

Specifically built with electricians and linemen in mind, these non-vented hard hats are tested up to 20kV.

Class E, Type 1 hard hat meets ANSI Z89.1-2014, CSA Z94.1-15 and EN397:2012+A1:2012 – Lateral Deformation (LD) standards

Available in Cap Style and Full Brim

VENTED CLASS C

Built for the demands of general construction, plumbing, carpentry and iron worker use, these hard hats include adjustable vents that can be opened and closed. These hard hats do not provide electrical protection.


Class C, Type 1 hard hat meets ANSI Z89.1-2014, CSA Z94.1-15 and EN397:2012+A1:2012 – Lateral Deformation (LD) standards

Available in Cap Style and Full Brim



LARGER VENTS = BETTER VENTILATION

The adjustable vents can be opened or closed for maximum air circulation.



HEADLAMP/MAGNETIC WORKLIGHT KHH56220

Included on some models and also sold separately, our worklight has a built-in tab that allows quick release without removing hard hat, tilts up to 62°, switches between spotlight and floodlight modes and has a built-in magnet on back that attaches to metal surfaces. Also sold separately. (#KHH56220)

ACCESSORY MOUNTS

Patent-pending accessory mounts ensure the Klein headlamp is always properly positioned, on **front or back** - with **NO STRAP** needed!

RECHARGEABLE AUTO-OFF HEADLAMP sold separately. (#56034)



REVERSE DONNING

Suspension can be easily adjusted to wear hard hat frontwards or backwards



UNIVERSAL ACCESSORY SLOTS

on both sides for hearing protection, face shield, and more.

NON-VENTED CLASS E



VENTED CLASS C

Cat. No.	UPC 0-92644+	Hard Hat Description	Vented	Class	Shell Color
60100	60076-0	Cap Style	NO	E	White
60107	60078-4	Cap Style with Light*			White
60900	60085-2	Cap Style with Light*			Orange
60400	60081-4	Full Brim Style			White
60406	60083-8	Full Brim Style with Light*			White
60105	60077-7	Cap Style	YES	C	White
60113	60079-1	Cap Style with Light*			White
60901	60086-9	Cap Style with Light*			Orange
60401	60082-1	Full Brim Style			White
60407	60084-5	Full Brim Style with Light*			White

*Includes headlamp KHH56220 with 3 x AAA batteries

ACCESSORIES

Cat. No.	UPC 0-92644+	Description	Lumens	Batteries	Battery Life	Drop Protection
KHH56220	56043-9	Alkaline Headlamp/ Magnetic Worklight	Spotlight: 150; Floodlight: 50	3 x AAA	Spotlight: 6 hrs.; Floodlight: 10 hrs	6 ft (1.8 m)
56034	56034-7	Rechargeable Auto-Off Headlamp	Spot/High: 200; Flood/Low: 100	Rechargeable Internal, Li-Ion, 3.7V / 1700 mAh	Spot/High: 12 hrs.; Flood/Low: 22 hrs.	10 ft (3m)




KHH56220



56034

REPLACEMENT PARTS

Cat. No.	UPC 0-92644+	Description	Package Quantity
KHHSPN	60087-6	Hard Hat Suspension System	1
KHHTOPPAD	60088-3	Hard Hat Suspension Top Pad	3
KHHSWTBND	60089-0	Hard Hat Suspension Sweatband	3
KHHSTRP	60119-4	Hard Hat Chin Strap	1



KHHTOPPAD

KHHSPN

KHHSWTBND

KHHSTRP



See our complete line of
Personal Protective Equipment

www.kleintools.com



© 2019 Klein Tools, Inc.
Lincolnshire, IL 60069
82810 Rev. 04/19 A