



STERIGUARD™ ANTIMICROBIAL 12/3 SEOW/STOW INDUSTRIAL PORTABLE CORD

PS123AM | [Pass & Seymour](#)

FEATURES & BENEFITS

SteriGuard™ 12/3 SEOW/STOW Antimicrobial Cord provides excellent protection against the growth of microbes on all surfaces. Independent testing proves the ability of these devices to inhibit the growth of Escherichia coli, Gram (-) and Staphylococcus aureus, Gram (+) providing long lasting benefits to manufacturers' beyond conventional cleaning methods. Industrial Portable Cord is manufactured using heavy-duty SEOW/STOW cord for maximum durability and longevity to meet the most demanding industrial and construction applications. SteriGuard provides a cost-effective way to add additional safety precautions and unequalled assurance that every feasible step has been taken in the interest of consumer protection. In addition, the SteriGuard™ Anti-Microbial Industrial Portable Cord paired with SteriGuard™ Anti-Microbial plugs and connectors are a complete anti-microbial solution

- UL/CSA Listed
- Custom cords are engineered to order for desired length specifications and NEMA type configurations
- Patent Pending
- Anti-microbial Additives Embedded in polymer and inhibits Growth of Bacteria, Molds, Mildews and Fungi
- Anti-microbial Additive Resistant to Scuffing and Cleaning
- Escherichia (E.Coli): - Log reduction > 4.8, reduced surface bacteria by > 99.99%
- Staphylococcus (Staph), MRSA: - Log Reduction > 4.3, reduces surface bacteria by > 99.97%
- Salmonella – Log Reduction > 3.6, reduces surface bacteria by > 99.97%
- RoHS Compliant (Non-Halogenated)
- Independently tested and Certified to JIS Z2801 standards
- Resistant to High Pressure Hose-down applications
- Additives are embedded in both the cord and wiring devices
- SteriGuard™ Anti-microbial Industrial Portable Cord is ideal for a wide range of applications including food and beverage preparation, processing, & packaging; agriculture, pharmaceutical, and health care

SPECIFICATIONS

GENERAL INFO

Type: Cord

Special Features: Watertight, NEMA

LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

CSA Listing Info: C22.2 No. 42M

CSA Listed: Yes
cUL Standard: Yes
UL Listing No: UL498
UL Standard: Yes
UN SPSC: 39121402

CORD INFORMATION

Cord Length US: 12/3 SEOW/STOW, Consult your Legrand rep for additional construction sizes

TECHNICAL INFORMATION

Material: Thermoplastic Elastomer/ Rubber
Operating Temperature (Celsius): -50°C- 150°C
Volts: 600V

BUY AMERICAN ACT COMPLIANCE

Country Of Origin: UNITED STATES OF AMERICA
Buy American Act Status: Buy American Act Compliant

