

# Arrow Hart industrial grade locking devices



AHCL520P



AHCL520C



AHCL520R





















AHCL520FO



AHCL520FI

## 20A Industrial grade locking devices

Pole-Wire	V/AC	NEMA	Description	Color	Catalog no.
2P-2W	250	 	Safety grip plug	Black & white	CWL220P
			Safety grip connector	Black & white	CWL220C
		Single receptacle	Black	CWL220R	
		Flanged outlet	Black & white	CWL220FO	
		2P-3W	125	 	Color coded ultra grip plug
Color coded ultra grip connector	Yellow & black				AHCL520C
Color coded single receptacle	Yellow & black				AHCL520R
Single receptacle, isolated ground	Orange				IGL520R
Color coded flanged outlet	Yellow & black		AHCL520FO		
Color coded flanged inlet	Yellow & black		AHCL520FI		
250	 		Color coded ultra grip plug	Blue & black	AHCL620P
			Color coded ultra grip connector	Blue & black	AHCL620C
		Color coded single receptacle	Blue & black	AHCL620R	
		Single receptacle, isolated ground	Orange	IGL620R	
		Color coded flanged outlet	Blue & black	AHCL620FO	
		Color coded flanged inlet	Blue & black	AHCL620FI	
277	 	Color coded ultra grip plug	Gray & black	AHCL720P	
		Color coded ultra grip connector	Gray & black	AHCL720C	
		Color coded single receptacle	Gray & black	AHCL720R	
		Single receptacle, isolated ground	Orange	IGL720R	
		Colored coded flanged outlet	Gray & black	AHCL720FO	
		Colored coded flanged inlet	Gray & black	AHCL720FI	
347	 	Safety grip plug	Black & white	L2420P	
		Single receptacle	Black	L2420R	
480	 	Colored coded ultra grip plug	Red & black	AHCL820P	
		Colored coded ultra grip connector	Red & black	AHCL820C	
		Colored coded single receptacle	Red & black	AHCL820R	
		Single receptacle, isolated ground	Orange	IGL820R	
		Colored coded flanged outlet	Red & black	AHCL820FO	
		Colored coded flanged inlet	Red & black	AHCL820FI	
600	 	Auto grip plug	Black & white	CWL920P	
		Auto grip connector	Black & white	CWL920C	
		Single receptacle	Black	CWL920R	
		Flanged outlet	Black & white	CWL920FO	
		Flanged inlet	Black & white	CWL920FI	
		3P-3W	125/250	 	Safety grip plug
Safety grip connector	Gray				7314C
Single receptacle	Black			7310B	
Flanged outlet	Gray			7328N	
Flanged inlet	Gray			7327N	
 	Colored coded ultra grip plug			Orange & black	AHCL1020P
	Colored coded ultra grip connector		Orange & black	AHCL1020C	
	Colored coded single receptacle		Orange & black	AHCL1020R	
	Colored coded flanged outlet		Orange & black	AHCL1020FO	
	Colored coded flanged inlet		Orange & black	AHCL1020FI	

**Accessories:**  
page 18

**Dimensions & cord diameters:**  
pages 19-21

**Spec information:**  
pages 22-26

**Compliances:**  
pages 27-29

Compliances, specifications and availability are subject to change without notice.

# Arrow Hart industrial grade locking devices



AHCL1430P



AHCL1430C



AHCL1430R










AHCL1430FO



AHCL1430FI

## 30A Industrial grade locking devices

Pole-Wire	V/AC	NEMA	Description	Color	Catalog no.
3P-3W	600	 L13-30R L13-30P	Auto grip plug, 3-phase	Black & white	CWL1330P
			Auto grip connector, 3-phase	Black & white	CWL1330C
		Single receptacle, 3-phase	Black	CWL1330R	
		Flanged outlet, 3-phase	Black & white	CWL1330FO	
		Flanged inlet, 3-phase	Black & white	CWL1330FI	
3P-4W	125/250	 L14-30R L14-30P	Color coded ultra grip plug	Orange & black	AHCL1430P
			Color coded ultra grip connector	Orange & black	AHCL1430C
			Color coded single receptacle	Orange & black	AHCL1430R
			Single receptacle, isolated ground	Orange	IGL1430R
			Color coded flanged outlet	Orange & black	AHCL1430FO
	Color coded flanged inlet	Orange & black	AHCL1430FI		
	250	 L15-30R L15-30P	Color coded ultra grip plug, 3-phase	Blue & black	AHCL1530P
			Color coded ultra grip connector, 3-phase	Blue & black	AHCL1530C
			Color coded single receptacle, 3-phase	Blue & black	AHCL1530R
			Single receptacle, isolated ground, 3-phase	Orange	IGL1530R
Color coded flanged outlet, 3-phase			Blue & black	AHCL1530FO	
Color coded flanged inlet, 3-phase	Blue & black	AHCL1530FI			
480	 L16-30R L16-30P	Color coded ultra grip plug, 3-phase	Red & black	AHCL1630P	
		Color coded ultra grip connector, 3-phase	Red & black	AHCL1630C	
		Color coded single receptacle, 3-phase	Red & black	AHCL1630R	
		Color coded flanged outlet, 3-phase	Red & black	AHCL1630FO	
		Color coded flanged inlet, 3-phase	Red & black	AHCL1630FI	
600	 L17-30R L17-30P	Color coded ultra grip plug, 3-phase	Black & black	AHCL1730P	
		Color coded ultra grip connector, 3-phase	Black & black	AHCL1730C	
		Color coded single receptacle, 3-phase	Black & black	AHCL1730R	
		Color coded flanged outlet, 3-phase	Black & black	AHCL1730FO	
		Color coded flanged inlet, 3-phase	Black & black	AHCL1730FI	
4P-4W	120/208	 Receptacle Plug	Ultra grip plug, 3-phase	Black & white	AH3431N
			Ultra grip connector, 3-phase	Black & white	AH3433N
		Color coded single receptacle, 3-phase	Blue & black	AHCL3430R	
		Flanged outlet, 3-phase	Black & white	AH3436N	
		Flanged inlet, 3-phase	Black & white	AH3434N	
	 L18-30R L18-30P	Color coded ultra grip plug, 3-phase	Blue & black	AHCL1830P	
		Color coded ultra grip connector, 3-phase	Blue & black	AHCL1830C	
		Color coded single receptacle, 3-phase	Blue & black	AHCL1830R	
		Color coded flanged outlet, 3-phase	Blue & black	AHCL1830FO	
		Color coded flanged inlet, 3-phase	Blue & black	AHCL1830FI	

**Accessories:**  
page 18

**Dimensions & cord diameters:**  
pages 19-21

**Spec information:**  
pages 22-26

**Compliances:**  
pages 27-29

**Compliances, specifications and availability are subject to change without notice.**

# Arrow Hart industrial grade locking devices



AHCL2130P



AHCL2130C



AHCL2130R















AHCL2130FO



AHCL2130FI

## 30A Industrial grade locking devices

Pole-Wire	V/AC	NEMA	Description	Color	Catalog no.			
4P-4W	277/480	  L19-30R L19-30P	Color coded ultra grip plug, 3-phase	Red & black	AHCL1930P			
			Color coded ultra grip connector, 3-phase	Red & black	AHCL1930C			
		Color coded single receptacle, 3-phase	Red & black	AHCL1930R				
		Color coded flanged outlet, 3-phase	Red & black	AHCL1930FO				
		Color coded flanged inlet, 3-phase	Red & black	AHCL1930FI				
347/600	277/480	  L20-30R L20-30P	Color coded ultra grip plug, 3-phase	Black & black	AHCL2030P			
			Color coded ultra grip connector, 3-phase	Black & black	AHCL2030C			
			Color coded flanged outlet, 3-phase	Black & black	AHCL2030R			
			Color coded flanged outlet, 3-phase	Black & black	AHCL2030FO			
			Color coded flanged inlet, 3-phase	Black & black	AHCL2030FI			
4P-5W	120/208	  L21-30R L21-30P	Color coded ultra grip plug, 3-phase	Blue & black	AHCL2130P			
			Ultra grip plug, 3-phase, flat cable	Black & white	AHL2130PF			
			Color coded ultra grip connector, 3-phase	Blue & black	AHCL2130C			
			Ultra grip connector, 3-phase, flat cable	Black & white	AHL2130CF			
			Color coded single receptacle, 3-phase	Blue & black	AHCL2130R			
			Single receptacle, isolated ground, 3-phase	Orange	IGL2130R			
			Color coded flanged outlet, 3-phase	Blue & black	AHCL2130FO			
			Color coded flanged inlet, 3-phase	Blue & black	AHCL2130FI			
			240/415	120/208	  L26-30R L26-30P	Ultra grip plug, 3-phase	Black & white	AHL2630P
						Ultra grip connector, 3-phase	Black & white	AHL2630C
Single receptacle, 3-phase	Black	AHL2630R						
Single receptacle, isolated ground, 3-phase	Orange	IG2630R						
277/480	120/208	  L22-30R L22-30P	Color coded ultra grip plug, 3-phase	Red & black	AHCL2230P			
			Ultra grip plug, 3-phase, flat cable	Black & white	AHL2230PF			
			Color coded ultra grip connector, 3-phase	Red & black	AHCL2230C			
			Ultra grip connector, 3-phase, flat cable	Black & white	AHL2230CF			
			Color coded single receptacle, 3-phase	Red & black	AHCL2230R			
			Single receptacle, isolated ground, 3-phase	Orange	IGL2230R			
			Color coded flanged outlet, 3-phase	Red & black	AHCL2230FO			
			Color coded flanged inlet, 3-phase	Red & black	AHCL2230FI			
			347/600	120/208	  L23-30R L23-30P	Color coded ultra grip plug, 3-phase	Black & black	AHCL2330P
						Ultra grip plug, 3-phase, flat cable	Black & white	AHL2330PF
Color coded ultra grip connector, 3-phase	Black & black	AHCL2330C						
Ultra grip connector, 3-phase, flat cable	Black & white	AHL2330CF						
Color coded single receptacle, 3-phase	Black & black	AHCL2330R						
Single receptacle, isolated ground, 3-phase	Orange	IGL2330R						
Color coded flanged outlet, 3-phase	Black & black	AHCL2330FO						
Color coded flanged inlet, 3-phase	Black & black	AHCL2330FI						

**Accessories:**  
page 18

**Dimensions & cord diameters:**  
pages 19-21

**Spec information:**  
pages 22-26

**Compliances:**  
pages 27-29

**Compliances, specifications and availability are subject to change without notice.**