

NOTES:

- I. COMPLIES WITH NEC SECTION 406.9 (B) (I) AND 590.4 (D) (2) FOR "EXTRA DUTY" OUTLET BOX HOODS -- NOW REQUIRED FOR ANY INSTALLATION OTHER THAN ONE- AND TWO-FAMILY DWELLINGS.
- 2. UNIVERSAL: ACCEPTS GFCI, DUPLEX, SWITCH AND UP TO 1-3/8" ROUND DEVICES.
- 3. 2CKPM (MEDIUM DEPTH COVER) CAN BE USED FOR ALL STANDARD ELECTRICAL CORDS AND PLUGS.
- 2CKPL (LONG DEPTH COVER) CAN BE USED WHEN HEAVY DUTY ELECTRICAL CORDS OR EXTRA LARGE PLUGS ARE USED.
- 5. STAINLESS STEEL HINGE PIN FOR EXTRA DURABILITY.
- 6. KEYHOLE MOUNTING FOR FAST INSTALLATION.
- 7. PRE-ADHERED GASKET.
- 8. WASP GUARD AT CORD EXIT TO KEEP OUT UN-WANTED PESTS.
- 9. MOUNTS VERTICALLY.
- IO. LOCKABLE
- II. REQUIRED BY THE NATIONAL ELECTRIC CODE FOR WET LOCATIONS.
- 12. INCLUDES DEVICE ADAPTER PLATES AND MOUNTING SCREWS (NOT SHOWN IN ILLUSTRATION).
- 13. COVERS OPEN TO AN ANGLE OF 120°.
- 14. AVAILABLE COLORS: GRAY, WHITE, BRONZE. A CAT. NO. WITHOUT A COLOR LETTER AFTER (LIKE 2CKPM) HAS GRAY BASE AND CLEAR HOOD.

| GENERAL NOTES | | | - | 5 |
|--|---|-----------|----------|-------------|
| I. ALL DIMENSIONS ARE FOR REFERENCE ONLY. | | | | homas Betts |
| 2. DIMENSIONS IN BRACKETS [] ARE IN METRIC UNITS. | DESCRIPTION: 2CKPM AND 2CKPL | | | |
| REVISIONS | TWO-GANG UNIVERSAL WHILE-IN-USE EXTRA DUTY COVERS | | | |
| | | | | |
| FOR APPROVAL SIGNATURES | ORIGINAL PROJECT NO / (ERN NO) | SHEET NO: | REV. NO: | DRAWING NO: |
| & RELEASE DATE. PROJECT NO: (002D000395) | 0020000395 / (2014313) | 1 OF 1 | 1 | WSD-001102 |