








Identification Cable Ties

Self-locking Ty-Rap® identification ties are available in both single and multiple configurations. They may be marked with the special Thomas & Betts black or red marking pen which produces a permanent legend, or they can be heat stamped. Because the ties serve the dual purpose of tying and identifying, you will achieve extra economies. They can be applied with the standard Ty-Rap® tying tools used for regular ties. Nylon 6/6 UV weather-resistant version available (add suffix "-x").



Std. Cat. No.	Bulk Cat. No.	Body Width (in./mm)	Length (in./mm)	Max. Wire Bundle Dia. (in./mm)	Military Standard Part No.	Marking Pad Size (in.) W x H	Tensile Strength (lb./N)	Std. Pkg.	Bulk Pkg.
Ty-Rap® Identification Cable Ties									
TY551M	TY51M	0.09/2.29	3.60/91.44	0.63/16.00	MS3368-5	1 x 0.313	18/80.07	100	500
TY5512M	TY512M		8.30/210.82	2.00/50.80	-	1 x 0.313			1,000
TY553M	TY53M		4.00/101.60	0.63/16.00	-	0.813 x 0.359		50	500
TY5532M	TY532M		8.40/213.36	2.00/50.80	-	0.813 x 0.359		100	1,000
-	TY153M	0.10/2.54	4.35/110.49	0.63/16.00	-	0.781 x 1	-	-	500
TY546M	TY46M	0.18/4.57	7.10/180.34	1.75/44.45	MS3368-1	0.5 x 0.875	50/222.40	100	1,000
TY548M	TY48M	0.19/4.83	14.20/360.68	4.00/101.60	MS3368-2	0.5 x 2.125			50
TY546MD	TY46MD		7.25/184.15	1.75/44.45	MS3368-3	1.172 x 1		100	500
TY546MT	TY46MT				MS3368-4	1.210 x 1		-	2.48 x 1
TY546MF	TY46MF								



Custom Heat Stamping

Thomas & Betts' Custom Heat Stamping provides an economical way to fasten and identify cable bundles. Mark nylon cable ties, identification cable ties, and identification plates to suit your application.

- 1/16 in., 1/8 in., 3/16 in. characters available
- Standard Type: Gothic Capitol
- Character sizes can be mixed from line to line on Identification cable ties
- Alphanumeric and Sequential numbering available
- Six digit sequential numbering available in 1/8" characters

- Eight digit sequential numbering available in 1/16" and 3/16" characters
- The following colours of heat stamping are available – Black, Blue, Green, Red, Yellow, Orange and White
- Special logos and different type styles can be accommodated when camera ready artwork is provided
- Minimum order quantity is 3000 pieces per catalogue number and message

Contact your Regional Sales Office for pricing, availability, quotation and order entry.