

EMT

Conduit Fittings, Accessories and Entrance Heads



CILRL-1/2 / CILRL-2

CITA-1/2 / CITA-2



Combined LL/LR  
Left and right  
application



Cat. No.	Trade Size (in.)	Dimensions (in.)		
		A	B	C
<b>EMT Conduit Fittings - "LRL" Type (Cast Aluminum)</b>				
CILRL-1/2	1/2	4-7/16	1-11/16	2-1/8
CILRL-3/4	3/4	5-3/16	1-7/8	2-1/4
CILRL-1	1	6	2-3/16	2-1/2
CILRL-1-1/4	1-1/4	7-15/16	2-3/4	3-1/2
CILRL-1-1/2	1-1/2	7-15/16	3-1/4	3-1/2
CILRL-2	2	10-3/16	3-11/16	4-1/8
<b>EMT Conduit Fittings - "T" Type (Cast Aluminum)</b>				
CITA-1/2	1/2	4-7/8	1-3/8	2-1/16
CITA-3/4	3/4	5-9/16	1-3/4	2-1/8
CITA-1	1	6-1/2	2	2-1/2
CITA-1-1/4	1-1/4	8-11/16	2-5/8	3-1/2
CITA-1-1/2	1-1/2	8-11/16	3	3-9/16
CITA-2	2	10-7/8	3-1/4	4-3/16

Covers and gaskets are included with all aluminum conduit fittings  
Types CILRL and CITA are also suitable for use with rigid conduit

CIBC-1/2 / CIBC-2



Cat. No.	Trade Size (in.)
<b>Blank Covers for Aluminum Conduit Fittings (Stamped Aluminum)</b>	
CIBC-1/2	1/2
CIBC-3/4	3/4
CIBC-1	1
CIBC-1-1/4	1-1/4
CIBC-2	2

For 1-1/2, use CIBC-1-1/4

CIG-1/2 / CIG-2



Cat. No.	Trade Size (in.)
<b>Gaskets for Aluminum Conduit Fittings (Neoprene)</b>	
CIG-1/2	1/2
CIG-3/4	3/4
CIG-1	1
CIG-1-1/4	1-1/4
CIG-2	2

For 1-1/2, use CIG-1-1/4

CIEFSA-1/2 / CIEFSA-4



Cat. No.	Trade Size (in.)
<b>Service Entrance Heads (Cast Aluminum)</b>	
CIEFSA-1/2	1/2
CIEFSA-3/4	3/4
CIEFSA-1	1
CIEFSA-1-1/4	1-1/4
CIEFSA-1-1/2	1-1/2
CIEFSA-2	2
CIEFSA-2-1/2	2-1/2
CIEFSA-3	3
CIEFSA-3-1/2	3-1/2
CIEFSA-4	4

Consult page D10 for technical specifications