

Flush Service Floor Boxes

Innovative 3-Gang Round Floor Box for Power, Data and AV.

Round Floor Boxes for Power and Communications: 68-HP Series

NEW!

Unmatched Flexibility to configure any combination of power and communications devices

- Accepts standard devices from any manufacturer, including duplex, GFCI, locking, hospital grade or isolated ground receptacles
- Accommodates a wide variety of multi-media devices through the use of rectangular adapters

Combines the Capacity of a 3-gang box with the **Affordability** of a round non-metallic floor box

- 6" diameter round non-metallic floor box — the largest in the industry
- Large inline hubs for power and data wiring: 1" for power, 1½" for data



No leveling, gluing or aligning for an Easy Installation

- No wasted time leveling the box before the concrete is poured — simply cut the box at the appropriate height after the pour
- No gluing — stainless steel retention bars secure the mounting frame to the box
- Round design — no need to align the box with walls during installation



Stainless Steel Bars

Easy-to-Use Covers Made of Durable solid brass and aluminum

- Stands up to heavy carts, cleaning equipment, and general floor traffic
- Convenient slide latch provides tool-less access to devices
- Lid lies flat while in use to minimize obstructions above floor level



Slide Latch for Tool-less Access

Furniture-Feed and Cast Iron options for a Comprehensive floor box solution

- Dual-voltage furniture-feed covers transition power and communications wiring from the floor into modular furniture
- Cast iron box with a non-metallic collar for slab-on-grade or metallic conduit applications



1" Hub for Power,
1½" Hub for Data



Flush Service Floor Boxes





68-HP Floor Boxes (continued)



68-HP
6" Round Non-Metallic
Floor Box




68-HP-CI
Cast Iron Floor Box with 6" Round
Non-Metallic Collar




CAT. NO.	DESCRIPTION	MINIMUM CONCRETE DEPTH		
		FLUSH	FURNITURE FEED	STANDARD PACK QTY.
68-HP	6" Round Non-Metallic Floor Box	4"	3 1/2"	4
68-HP-CI	Cast Iron Floor Box with 6" Round Non-Metallic Collar	4 1/2"	4"	1

Flush Covers for 68-HP Series

- Slide latch for tool-less access to devices
- Lid lies flat when box is in use
- Requires Flush Mounting Kit (Cat. No. 68-HP-FMK) to mount cover (see [page A-145](#))



68-HP-FC-ALM
Solid brass cover
with brushed finish



Pull slide latch to release lid



CAT. NO.	DESCRIPTION	STD. PACK QTY.
68-HP-FC-ALM	Flush Cover — Solid Aluminum with Brushed Finish, 1,000 lb. Load Rating	4
68-HP-FC-BRS	Flush Cover — Solid Brass with Brushed Finish, 1,500 lb. Load Rating	4
68-HP-FC-BLK	Flush Cover — Solid Aluminum with Black Powder-Coated Finish, 1,000 lb. Load Rating	4