

Construction grade receptacles

Combines safe, rugged, reliable performance with ease-of-installation


Arrow Hart construction grade receptacles are designed to provide a dependable, long lasting user experience while increasing the speed and efficiency of installation

Construction grade 5262 & 5362 series features & benefits

Automatic grounding system eliminates need for bonding jumper in grounded metal enclosures

Nylon face resists high impact and chemical abuse

Patented screw catch captures wallplate screw eliminating hand threading of screw, lost screws and cross-threading



Extra long/wide mounting strap maintains assembly security and helps reach oversize cutouts

0.031" thick triple wipe brass line contacts minimize heat rise and maximize plug retention

Additional features & benefits

- Available in 15A & 20A duplex configurations, including tamper resistant and ArrowLink modular styles
- Convenient built-in #10 and #12 AWG wire strippers
- Tri-combo head terminal and mounting screws

Compliances, specifications and availability are subject to change without notice.



www.eaton.com
www.eaton.com/arrowhart

Commercial grade receptacles


Commercial grade straight blade receptacles

Product description


2-pole, 3-wire grounding
Dual voltage
15A, 125/250V/AC
NEMA 5-15R, 6-15R




829



826




815



1876


Dual voltage commercial grade receptacle

Rating		NEMA	Description	Color	Catalog no.	
A	V/AC					
15	125/ 250	5-15R/ 6-15R	Dual voltage duplex receptacle, side wire	V	□ 829V	








Commercial grade straight blade receptacles

Product description

2-pole, 3-wire grounding
15A, 250V/AC
20A, 250V/AC
NEMA 6-15R, 6-20R



Commercial grade receptacles

Rating		NEMA	Description	Color suffix	Catalog no.	  
A	V/AC					
15	250	6-15R	Duplex receptacle, side wire	B, V, W	□ 826_Δ	
			Single receptacle, side wire	B, V, W	□ 816_	
20	250	6-20R	Duplex receptacle, side wire	B, V, W	□ 815_Δ	
			Single receptacle, side wire	A, B, BK, LA, V, W	□ 1876_	

^Δ Fed Spec certified

Decorator commercial grade receptacle

Rating		NEMA	Description	Color	Catalog no.	  
A	V/AC					
20	250	6-20R	Single receptacle, back & side wire	W	□ 6450W	


Color ordering information:

For ordering devices, include Catalog no. followed by the Color suffix: A (Almond), B (Brown), BK (Black), LA (Light Almond), V (Ivory), W (White)

A	B	BK	LA	V	W
(Almond)	(Brown)	(Black)	(Lt. Almond)	(Ivory)	(White)

Specification information: Commercial receptacles: A-33

Compliances, specifications and availability are subject to change without notice.

 Build-to-spec customizable devices - Page A-6

 Indicates NAFTA compliant - Page Q-32

 RoHS compliant - Page Q-32