



DIGITAL AUDIO FOUR-ROOM, SINGLE-SOURCE KIT, WHITE

AU7154-WH | [On-Q](#)

FEATURES & BENEFITS

The AU7154-WH is a four-room, single-source Digital Audio Kit. Conveniently supplying all of the core components necessary to install a four-room Digital Audio System with digital source accessibility, this kit comes complete with (4) AU7010-WH Digital Audio Amplified Keypads, (1) AU7000 Digital Audio Distribution Module, (1) AU7001 Digital Audio Input Module, (1) PW1020 Digital Audio Power Distribution Module, (1) PW1060 Power Supply, and (1) PW7760 Power Supply.

Check out the [Digital Audio mobile app](#).

- Comes complete with all core components for a four-room, single-source Digital Audio System with digital source accessibility
- Built-in access to streaming services including, Spotify, iHeartRadio, Pandora, Napster, SiriusXM, and TuneIn
- Allows streaming of networked digital content from iTunes, Windows Media Player libraries, and mobile devices
- Provides 20 watts of Class D power per zone
- Conveniently controllable through both included keypads as well as free, intuitive Android or iOS apps for smartphones and tablets
- Provides all core components needed to install a four-room, single-source Digital Audio System with digital source accessibility
- Structured wiring based to offer easy installation and a repeatable solution
- Simple setup using smartphone or tablet, no PC required

*Streaming services subject to geographic availability. Service subscriptions may be required.

SPECIFICATIONS

GENERAL INFO

Cable Type: Connect Cat5e or better and speaker wire 18-16 gauge.

Color: White

Size: 11.25" x 7.75" x 14.5"

Termination: 1264.22 cu. in.

Connection Type: RJ45 connections and removeable pheonix screw down terminals

Type: Low Voltage, Audio System

Special Features: 4-Zone, 1-Source Digital Audio System

Style: Decorator Keypad; Structured wiring cabinet (not included)

LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

FCC Standard: Yes

UL Standard: Yes

DIMENSIONS

Depth (Metric): 368.3mm

Depth (US): 14.5"

Width (Metric): 285.75mm

Width (US): 11.25"

Primary Packaging Weight (Metric): 2.5 kg

Product Weight (Metric): 2.5 kg

Product Weight (US): 5.5 lbs

Volume: 1264.22 cu. in.

Weight: 5.5 lbs

Height: 7.75"

TECHNICAL INFORMATION

Connection Method: Ethernet network

Mounting: Wall Mount/Enclosure Mount

Power Requirements: 24 VDC 60W Power Supply / 12 VDC 18W Power Supply

Supported Standards: FCC, UL

Watts: 20W 8Ω

Connection Location: Data Control Interface: Ethernet/Digital Keypad

BUY AMERICAN ACT COMPLIANCE

Country Of Origin: CHINA