


# OMNIBOX™ SERIES FLOOR BOXES

## Omnibox Series Powder-Coated Aluminum Cover Plates Ordering Information

### 828R-TCAL

Powder-Coated Aluminum Duplex Cover Plate




**828R-TCAL-BK, 828R-TCAL-GY, 828R-TCAL-BS, 828R-TCAL-NK, 828R-TCAL-BZ**

Flip lids. Can also be used with a 106 type communication adapter.

### 829CKAL-3/4

Powder-Coated Aluminum Cover Plate




**829CKAL-3/4BK, 829CKAL-3/4GY, 829CKAL-3/4BS, 829CKAL-3/4NK, 829CKAL-3/4BZ**

Power or communication plate with 2" [51mm] and 3/4" [19.1mm] plugs. Covers are available in five decorative colors: black, gray, brass, nickel and bronze.

**NOTE:** Acceptable for use with threaded conduit when passing through power cables.

### 828GFITCAL


Powder-Coated Aluminum Rectangular Cover Plate



**828GFITCAL-BK, 828GFITCAL-GY, 828GFITCAL-BS, 828GFITCAL-NK, 828GFITCAL-BZ**


Allows for mounting of a duplex receptacle (Duplex or GFCI style) with a rectangular flip cover.

### 828MAAP AV Adapter Plate



Sheet metal adapter plate that accepts two (2) Legrand AVIP or Extron® Electronics MAAP style device plates (sold separately). For use with 828GFITC or 828GFITCAL cover plates (sold separately).

### 829CKAL-1 Powder-Coated Aluminum Cover Plate




**829CKAL-1BK, 829CKAL-1GY, 829CKAL-1BS, 829CKAL-1NK, 829CKAL-1BZ**

Power or communication plate with 2" [51mm] and 1" [25mm] plugs. Covers are available in five decorative colors: black, gray, brass, nickel and bronze.

**NOTE:** Acceptable for use with threaded conduit when passing through power cables.

## Omnibox Series Nonmetallic Cover Plate Flanges Ordering Information


### 817PCC 1-Gang Nonmetallic Carpet Flange



**817PCC-BLK, 817PCC-BRN**

For Ortronics® connectivity use with 829PFLRT Cover. For Activate™ connectivity use with 829PFL Cover. Accepts Ortronics® MAB6TJ TracJack and MAB3S2 Series II adapters and Wiremold CM Series inserts, sold separately.

### 827PCC 2-Gang Nonmetallic Carpet Flange



**827PCC-BLK, 827PCC-BRN**

For Ortronics® connectivity use with 829PFLRT Cover. For Activate™ connectivity use with 829PFL Cover. Accepts Ortronics® MAB6TJ TracJack and MAB3S2 Series II adapters and Wiremold CM Series inserts, sold separately.

**NOTE:** UL Listed for tile, terrazzo, and carpet floors. Brass covers and flanges are not interchangeable with aluminum or nonmetallic covers and flanges. Nonmetallic covers are interchangeable with aluminum flanges.

# WALKERDUCT® UNDERFLOOR DUCT SYSTEMS

## Walkerduct Underfloor Duct Systems Service Fitting Compatibility

PRODUCT FAMILY	CATALOG NUMBER	ACTIVATION LOCATION		SERVICE CAPACITY			SERVICE COMPATIBILITY			MATERIAL/COLORS				
		Flush	Pedestal	Single Service	Dual Service	Triple Service	Power	Communication	Audio/Visual	Polycarbonate	Aluminum	Brass	Gray	Black
	817B	•		•			•	•				•		
	827B	•			•		•	•				•		
	837B	•				•	•	•				•		
	817PCC	•		•			•	•		•				•
	827PCC	•			•		•	•		•				•
	837PCC	•				•	•	•		•				•
	818TCAL	•		•			•	•			•			
	828TCAL	•			•		•	•			•			
	838TCAL	•				•	•	•			•			
	S165B	•		•			•					•		
	S165BLK/BRN	•		•						•				•
	S166B	•		•				•				•		
	S166BLK/BRN	•		•				•		•				•
	S175BLK/BRN	•		•			•			•				•
	PSRC9TC	•		•			•				•	•	•	•
	PSRC9AMDTC	•		•				•			•	•	•	•
	PSRC9FFTC	•		•				•			•	•	•	•
	1204BF		•	•				•				•		
	1204AL		•	•				•			•			
	1223BF		•	•			•					•		
	1223AL		•	•			•				•			
	MP4		•	•			•	•	•		•			
	MP8		•		•		•	•	•		•			
	MP8-1		•		•		•	•	•		•			
	525A		•	•				•	•		•			
	525B		•	•				•	•		•			
	525C		•	•				•	•		•			
	525D		•	•				•	•		•			
	525F		•	•			•				•			
	25G		•	•			•				•			
	525H		•	•			•				•			
	525I		•	•			•				•			
	525J		•	•			•	•	•		•			
	525RT		•	•				•			•			
525ACT		•	•				•			•				