

Quick Change D’VersiBIT® System Kit

NEW PRODUCT



- All the same great features as a traditional flexible drill bit, but with even more flexibility and versatility.
- Simplifies the frustrating and time-consuming process of installing wire or cable inside existing walls.
- For use when drilling between studs and joists.
- Can use with any type of bit with a 1/4" quick change hex on it, such as spade bits, auger bits or drill bits for increased application flexibility.
- Replace only the bit as it wears rather than the entire bit and shaft for lower overall cost of ownership.
- Quickly and easily switch from drilling to pulling with the quick change pulling grip. No more fiddling with hooking a pulling grip to the bit.

SPECIFICATIONS

	Dimensions	Weight
941	1.2 x 8.5 x 40.7" (30.5 x 215.9 x 1033.8mm)	1.67 lbs (.76kg)
941-18	.85 x 2.75 x 21.75" (21.6 x 69.9 x 5552.4mm)	0.6 lbs (.27kg)
941-36	.85 x 2.75 x 39.75" (21.6 x 69.9 x 1009.6mm)	0.73 lbs (.33kg)
60A-3/4	1.25 x 3.75 x 8.25" (31.7 x 95.2 x 209.5mm)	0.34 lbs (.15kg)
60C-3/4	1.06 x 3.75 x 8.25" (26.9 x 95.2 x 209.5mm)	0.34 lbs (.15kg)
125Q	9.3 x 3.6 x 1.2" (236 x 91 x 30.5mm)	0.04 lbs (.02kg)
150Q	1 x 3.25 x 12" (25.4 x 82.5 x 304.8mm)	0.12 lbs (.05kg)
168Q	12 X 3.6 X 1.2" (304 x 91 x 30.5mm)	0.06 lbs (.03kg)
712P	.8 x 8 x 9.8" (20.3 x 203.2 x 248.9mm)	0.43 lbs (.19kg)
921	.5 x 5 x 39.25" (12.7 x 127 x 996.9mm)	1.15 lbs (.52kg)
921-12	.5 x 4 x 15" (12.7 x 101.6 x 381mm)	0.31 lbs (.14kg)
921-18	2.25 x 5 x 21.5" (57.1 x 127 x 539.7mm)	0.68 lbs (.31kg)
921-24	.5 x 4 x 22.5" (12.7 x 101.6 x 571.5mm)	1.07 lbs (.48kg)
921-36	2.25 x 5 x 39.5" (57.1 x 127 x 1003.3mm)	0.74 lbs (.33kg)
60A-5/8	1.25 x 3.75 x 8.25" (31.7 x 95.2 x 209.5mm)	0.31 lbs (.14kg)
60A-7/8	1.28 x 3.75 x 8.25" (32.5 x 95.2 x 209.5mm)	0.36 lbs (.16kg)
60A-1	1.3 x 3.75 x 8.25" (33 x 95.2 x 209.5mm)	0.38 lbs (.17kg)

CAT. NO.	UPC NO.	DESCRIPTION
941	31388	D’Versibit, Quick Change, Starter Kit
941-18	31390	D’Versibit, Extention 1/4 x 18 (POP)
941-36	31389	D’Versibit, Extention 1/4 x 36 (POP)
60A-3/4	12417	Bit, Auger, Quick Change 3/4A (POP)
60C-3/4	31391	Bit, Auger, Quick Change 3/4C (POP)
125Q	12791	Grip, Quick Change 3/8 x 1/4 (POP)
150Q	12792	Grip, Quick Change 1/2 x 1/4 (POP)
168Q	12793	Grip, Quick Change 3/4 x 1/4 (POP)
712P	38350	Tool, Placement (Pkg’d - All Bits)
921	12411	Quick Change Extention System Kit (POP)
921-12	12412	Extension, Quick Change 3/16 x 12 (POP)
921-18	12413	Extension, Quick Change 3/16 x 18 (POP)
921-24	12414	Extension, Quick Change 3/16 x 24 (POP)
921-36	12415	Extension, Quick Change 3/16 x 36 (POP)
60A-5/8	12416	Bit, Auger, Quick Change 60A - 5/8 (POP)
60A-7/8	12418	Bit, Auger, Quick Change 60A - 7/8 (POP)
60A-1	10538	Bit, Auger, Quick Change (1A) (POP)