

DRILL/TAPS

Electrician's Drill/Driver Set

**NEW
PRODUCT**



- 1/4" Quick Change technology.
- Professional grade driver bits.
- Titanium Nitride coated self-centering high speed drill bits.
- High quality shock resistant case stays intact even after accidental drops.
- Hammer drill rated carbide grade tips and hardened shank masonry drill bits.
- Hardened forged magnetic nut drivers fit most TapCon® fasteners.
- Quick release chuck with precise fit.
- Includes security bits that fit most security fasteners frequently used in public facilities.

CAT. NO.	UPC NO.	DESCRIPTION
DDKIT-1-68	26313	68-Piece Electrician's Drill/Driver Kit
EXT-3	19194	Magnetic Bit Extension
HSS-SET	26317	High Speed Titanium Coated Drill Bit Set (1/8", 3/16", 1/4")
MAS-SET	26318	Masonry Drill Bit Set (5/32", 3/16", 1/4", 3/8")
NDS-SET	26320	Magnetic Nut Driver Set (1/4", 5/16", 3/8")
QCS-1	26312	1/4" Quick Change Chuck
SBSET-1-14	19205	Security Driver Bit Set (Spanner Security Bits-#6, #8, #10, #12, Torx Security Bits-T10, T15, T20, T25, T27, T30, Hex Security Bits-1/8", 9/64", 5/32", 3/16")



VIDEO

A PRODUCT VIDEO IS AVAILABLE. SCAN THIS QR CODE OR VISIT:
www.youtube.com/GreenleeDEMO



SPECIFICATIONS	DDKIT-1-68	EXT-3	HSS-SET	MAS-SET
Length	12.32" (313 mm)	5.88" (149 mm)	7.88" (200 mm)	7.88" (200 mm)
Width	10.75" (273 mm)	2.88" (73 mm)	5.50" (139 mm)	5.50" (139 mm)
Height	1.95" (49 mm)	.84" (21 mm)	.77" (19 mm)	.77" (19 mm)
Weight	2.35 lbs (1.06 kg)	.07 lbs (.03 kg)	.2 lbs (.09 kg)	.28 lbs (.13 kg)



SPECIFICATIONS	NDS-SET	QCS-1	SBSET-1-14
Length	5.88" (149 mm)	5.88" (149 mm)	6.88" (174 mm)
Width	2.88" (73 mm)	2.88" (73 mm)	3.88" (98 mm)
Height	.82" (20 mm)	.84" (21 mm)	1.47" (37 mm)
Weight	.19 lbs (.09 kg)	.1 lbs (.12 kg)	.26 lbs (.12 kg)