


# MP2-31R

[Print View..](#)  
[Print to Pdf..](#)

## General Information

<b>Extended Product Type:</b>	MP2-31R
<b>Product ID:</b>	1SFA611101R3101
<b>EAN:</b>	7320500266946
<b>Catalog Description:</b>	MP2-31R Pushbutton
<b>Long Description:</b>	Modular Pushbutton - Maintained - Flush - Red - Illuminated - Chrome metal - No contact block



## Categories

Products » Low Voltage Products and Systems » Control Products » Pilot Devices » Operator and Pilot Lights

## Ordering

<b>EAN:</b>	7320500266946
<b>Minimum Order Quantity:</b>	10 piece
<b>Customs Tariff Number:</b>	85369001

## Dimensions

<b>Product Net Width:</b>	0.029 m
<b>Product Net Height:</b>	0.029 m
<b>Product Net Depth:</b>	0.033 m
<b>Product Net Weight:</b>	0.031 kg

## Container Information

<b>Package Level 1 Units:</b>	1 piece
<b>Package Level 1 Width:</b>	0.11 m
<b>Package Level 1 Height:</b>	0.029 m
<b>Package Level 1 Length:</b>	0.15 m
<b>Package Level 1 Gross Weight:</b>	0.031 kg

## Environmental

<b>Ambient Air Temperature:</b>	Operation -25 ... +70 °C Storage -30 ... +85 °C
<b>RoHS Status:</b>	Following EU Directive 2002/95/EC August 18, 2005 and amendment

## Additional Information

<b>Actuator Type:</b>	Flush
<b>Bezel Material:</b>	Chrome metal
<b>Block:</b>	No contact block
<b>Color:</b>	Red
<b>Function:</b>	Maintained
<b>IIT Publishing Status:</b>	Level 0 - Information enabled
<b>Illumination:</b>	Illuminated
<b>Mechanical Durability:</b>	2 million
<b>Product Main Type:</b>	MP2
<b>Product Name:</b>	Pushbutton

<b>Product Range:</b>	Modular
<b>Product Type:</b>	MP
<b>RoHS Date:</b>	0635 4

---

### Certificates and Declarations (Document Number)

---

<b>Declaration of Conformity - CE:</b>	1SFA1-83
<b>RoHS Information:</b>	1SFC151011D0203

---

### Classifications

---

<b>E-nummer:</b>	3715311
<b>ETIM 4.0:</b>	EC002024 - Accessories for control circuit devices
<b>ETIM 5.0:</b>	EC002024 - Accessories for control circuit devices
<b>Object Classification Code:</b>	S
<b>UNSPSC:</b>	39121512

---