


1

Catalog Number Selection

Catalog Number Selection is for illustrative purposes only and not to be used to create new catalog numbers.

Illuminated Pushbuttons



^① Silver bezel only.

Product Selection

Illuminated Pushbuttons, Flush, Momentary

M22-DL-G-K01-G



Complete Devices

| Button Color | Contact Block Configuration ^① | Light Unit Voltage | Silver Bezel Catalog Number | Black Bezel Catalog Number | Metal Bezel Catalog Number |
|-----------------|--|--------------------|-----------------------------|----------------------------|----------------------------|
| Red | NC | 12–30 Vac/Vdc | M22-DL-R-K01-R | M22S-DL-R-K01-R | M22M-DL-R-K01-R |
| | NC | 85–264 Vac | M22-DL-R-K01-230R | M22S-DL-R-K01-230R | M22M-DL-R-K01-230R |
| | 2NC | 12–30 Vac/Vdc | M22-DL-R-K02-R | M22S-DL-R-K02-R | M22M-DL-R-K02-R |
| | 2NC | 85–264 Vac | M22-DL-R-K02-230R | M22S-DL-R-K02-230R | M22M-DL-R-K02-230R |
| Green | 1NO/1NC | 12–30 Vac/Vdc | M22-DL-R-K11-R | M22S-DL-R-K11-R | M22M-DL-R-K11-R |
| | 1NO/1NC | 85–264 Vac | M22-DL-R-K11-230R | M22S-DL-R-K11-230R | M22M-DL-R-K11-230R |
| | NO | 12–30 Vac/Vdc | M22-DL-G-K10-G | M22S-DL-G-K10-G | M22M-DL-G-K10-G |
| | NO | 85–264 Vac | M22-DL-G-K10-230G | M22S-DL-G-K10-230G | M22M-DL-G-K10-230G |
| M22M-DL-G-K01-G | 2NO | 12–30 Vac/Vdc | M22-DL-G-K20-G | M22S-DL-G-K20-G | M22M-DL-G-K20-G |
| | 2NO | 85–264 Vac | M22-DL-G-K20-230G | M22S-DL-G-K20-230G | M22M-DL-G-K20-230G |
| | 1NO/1NC | 12–30 Vac/Vdc | M22-DL-G-K11-G | M22S-DL-G-K11-G | M22M-DL-G-K11-G |
| | 1NO/1NC | 85–264 Vac | M22-DL-G-K11-230G | M22S-DL-G-K11-230G | M22M-DL-G-K11-230G |
| White | NO | 12–30 Vac/Vdc | M22-DL-W-K10-W | M22S-DL-W-K10-W | — |
| | NO | 85–264 Vac | M22-DL-W-K10-230W | M22S-DL-W-K10-230W | M22M-DL-W-K10-230W |
| | 2NO | 12–30 Vac/Vdc | M22-DL-W-K20-W | M22S-DL-W-K20-W | — |
| | 2NO | 85–264 Vac | M22-DL-W-K20-230W | M22S-DL-W-K20-230W | M22M-DL-W-K20-230W |
| | 1NO/1NC | 12–30 Vac/Vdc | M22-DL-W-K11-W | M22S-DL-W-K11-W | — |
| | 1NO/1NC | 85–264 Vac | M22-DL-W-K11-230W | M22S-DL-W-K11-230W | M22M-DL-W-K11-230W |

Note

^① All NC contact blocks are positively driven contact. ⊖

1

Illuminated Pushbuttons, Flush, Momentary**M22-DL-G****M22S-DL-G****M22M-DL-G****M22-DGL-G****Operators Only** [Ⓢ]

| Button Color | Silver Bezel Catalog Number | Black Bezel Catalog Number | Metal Bezel Catalog Number |
|--------------|--------------------------------|-------------------------------|-------------------------------|
| Red | M22-DL-R | M22S-DL-R | M22M-DL-R |
| Green | M22-DL-G | M22S-DL-G | M22M-DL-G |
| White | M22-DL-W | M22S-DL-W | M22M-DL-W |
| Blue | M22-DL-B | M22S-DL-B | M22M-DL-B |
| Yellow | M22-DL-Y | M22S-DL-Y | M22M-DL-Y |
| Amber | M22-DL-A | M22S-DL-A | M22M-DL-A |

Silver Guarded

| Button Color | Silver Bezel Catalog Number |
|--------------|--------------------------------|
| Red | M22-DGL-R |
| Green | M22-DGL-G |
| White | M22-DGL-W |
| Blue | M22-DGL-B |
| Yellow | M22-DGL-Y |

Note

[Ⓢ] Includes contact block mounting adapter.

1

Illuminated Pushbuttons, Extended, Momentary

M22-DLH-R-K11-R



M22S-DLH-R-K11-R



Complete Devices

| Button Color | Contact Block Configuration ^① | Light Unit Voltage | Silver Bezel Catalog Number | Black Bezel Catalog Number | Metal Bezel Catalog Number |
|--------------|--|--------------------|-----------------------------|----------------------------|----------------------------|
| Red | 1NO/1NC | 12–30 Vac/Vdc | M22-DLH-R-K11-R | M22S-DLH-R-K11-R | M22M-DLH-R-K11-R |
| | 1NO/1NC | 85–264 Vac | M22-DLH-R-K11-230R | M22S-DLH-R-K11-230R | M22M-DLH-R-K11-230R |
| Green | 2NO | 12–30 Vac/Vdc | M22-DLH-G-K20-G | M22S-DLH-G-K20-G | M22M-DLH-G-K20-G |
| | 2NO | 85–264 Vac | M22-DLH-G-K20-230G | M22S-DLH-G-K20-230G | M22M-DLH-G-K20-230G |
| White | 2NO | 12–30 Vac/Vdc | M22-DLH-W-K20-W | M22S-DLH-W-K20-W | M22M-DLH-W-K20-W |
| | 2NO | 85–264 Vac | M22-DLH-W-K20-230W | M22S-DLH-W-K20-230W | M22M-DLH-W-K20-230W |

Complete Press-to-Test Units

| Button Color | Light Unit Voltage | Silver Bezel Catalog Number | Black Bezel Catalog Number |
|--------------|--------------------|-----------------------------|----------------------------|
| Red | 12–30 Vac/Vdc | M22-T-R-R | M22S-T-R-R |
| Blue | | M22-T-B-B | M22S-T-B-B |
| Yellow | | M22-T-Y-W | M22S-T-Y-W |
| Green | | M22-T-G-G | M22S-T-G-G |
| White | | M22-T-W-W | M22S-T-W-W |
| Red | 85–264 Vac | M22-T-R-230R | M22S-T-R-230R |
| Blue | | M22-T-R-230B | M22S-T-B-230B |
| Yellow | | M22-T-Y-230W | M22S-T-Y-230W |
| Green | | M22-T-G-230G | M22S-T-G-230G |
| White | | M22-T-W-230W | M22S-T-W-230W |

Operators Only ^②

M22-DLH-R



M22S-DLH-R



M22M-DLH-R



| Button Color | Silver Bezel Catalog Number | Black Bezel Catalog Number | Metal Bezel Catalog Number |
|--------------|-----------------------------|----------------------------|----------------------------|
| Red | M22-DLH-R | M22S-DLH-R | M22M-DLH-R |
| Green | M22-DLH-G | M22S-DLH-G | M22M-DLH-G |
| White | M22-DLH-W | M22S-DLH-W | M22M-DLH-W |
| Blue | M22-DLH-B | M22S-DLH-B | M22M-DLH-B |
| Yellow | M22-DLH-Y | M22S-DLH-Y | M22M-DLH-Y |
| Amber | M22-DLH-A | M22S-DLH-A | M22M-DLH-A |

Silver Guarded

M22-DGLH-R



| Button Color | Silver Bezel Catalog Number |
|--------------|-----------------------------|
| Red | M22-DGLH-R |
| Green | M22-DGLH-G |
| White | M22-DGLH-W |
| Blue | M22-DGLH-B |
| Yellow | M22-DGLH-Y |

Notes

- ^① All NC contact blocks are positively driven contact. ⊖
- ^② Includes contact block mounting adapter.