

CE4T-10R-11

ABB contact for Canada [Print to Pdf..](#)

General Information

Extended Product Type:	CE4T-10R-11
Product ID:	1SFA619550R1071
EAN:	7320500260838
Catalog Description:	CE4T-10R-11 Emergency Stop
Long Description:	Compact Emergency Stop - Twist release - Mushroom 40mm - Red - Non-illuminated - Black plastic - 1NO+1NC



Categories

Products » Low Voltage Products and Systems » Control Products » Pilot Devices » Operator and Pilot Lights

Ordering

EAN:	7320500260838
Minimum Order Quantity:	1 piece
Customs Tariff Number:	85369001

Dimensions

Product Net Width:	0.030 m
Product Net Height:	0.040 m
Product Net Depth:	0.073 m
Product Net Weight:	0.036 kg

Container Information

Package Level 1 Units:	10 piece
Package Level 1 Width:	0.1 m
Package Level 1 Height:	0.04 m
Package Level 1 Length:	0.1 m
Package Level 1 Gross Weight:	0.036 kg

Environmental

Ambient Air Temperature:	Operation -25 ... +70 °C Storage -30 ... +85 °C
RoHS Status:	Following EU Directive 2002/95/EC August 18, 2005 and amendment

Additional Information

Actuator Type:	Mushroom 40mm
Bezel Material:	Black plastic
Block:	1NO+1NC
Color:	Red
Degree of Protection:	acc. to IEC 60529, IEC 60947-1, EN 60529 Auxiliary Terminals IP20
Function:	Twist release
Illumination:	Non-illuminated

Mechanical Durability: 0.5 million
Number of Auxiliary Contacts NC: 1
Number of Auxiliary Contacts NO: 1
Product Main Type: CE4T
Product Name: Emergency Stop
Product Range: Compact
Product Type: CE
Rated Frequency (f): Supply Circuit 50 Hz
Supply Circuit 60 Hz
Rated Operational Current AC-15 (I_e): (220 / 240V) 1 A
(24 / 127V) 1.5 A
Rated Operational Current DC-13 (I_e): (125V) 0.2 A
(24V) 0.3 A
RoHS Date: 0626 5

Certificates and Declarations (Document Number)

Declaration of Conformity - CE: 1SFA1-82
RoHS Information: 1SFC151012D0202

Classifications

E-nummer: 3711520
ETIM 4.0: EC002024 - Accessories for control circuit devices
ETIM 5.0: EC002024 - Accessories for control circuit devices
Object Classification Code: S
UNSPSC: 39121500
