


Shelves - Dual Pair Rail Mount

FIXED SHELVES

- Heavy duty, 14 Ga. steel construction, folded edges on all four sides for extra strength
- The vented version provides a sturdy shelf without obstructing upward heat movement
- Weight load tested to 350 pounds
- Sides folded up for easy hardware installation from above the shelf
- Sides are slotted for easy adjustment with most rail depth locations
- Rugged textured powder paint finish
- If used with our square hole rails you will need to order P/N **CPRSA** rail adaptor for each shelf ordered
- **MOUNTS ON TWO PAIR OF MOUNTING RAILS (FRONT & BACK)**

| Part Number | | Shelf Type | Shelf Depth |
|-----------------------------|-----------------------------|------------|-------------|
| Black Textured | Beige Textured | | |
| 19" Width | | | |
| RFVS1918BK1 | RFVS1918CG1 | Vented | 18" |
| RFVS1921BK1 | RFVS1921CG1 | Vented | 21" |
| RFVS1926BK1 | RFVS1926CG1 | Vented | 26" |
| RFVS1931BK1 | RFVS1931CG1 | Vented | 31" |
| RFUS1918BK1 | RFUS1918CG1 | Unvented | 18" |
| RFUS1921BK1 | RFUS1921CG1 | Unvented | 21" |
| RFUS1926BK1 | RFUS1926CG1 | Unvented | 26" |
| RFUS1931BK1 | RFUS1931CG1 | Unvented | 31" |
| 24" Width | | | |
| RFVS2418BK1 | RFVS2418CG1 | Vented | 18" |
| RFVS2421BK1 | RFVS2421CG1 | Vented | 21" |
| RFVS2426BK1 | RFVS2426CG1 | Vented | 26" |
| RFVS2431BK1 | RFVS2431CG1 | Vented | 31" |
| RFUS2418BK1 | RFUS2418CG1 | Unvented | 18" |
| RFUS2421BK1 | RFUS2421CG1 | Unvented | 21" |
| RFUS2426BK1 | RFUS2426CG1 | Unvented | 26" |
| RFUS2431BK1 | RFUS2431CG1 | Unvented | 31" |

Vented



Unvented



SLIDING SHELVES


- Heavy duty, 14 Ga. steel construction, folded edges on all four sides for extra strength
- The vented version provides a sturdy shelf without obstructing upward heat movement
- Weight load tested to 120 pounds
- Slides are slotted for easy adjustment with most rail depth locations
- Rugged textured powder paint finish

| Part Number | | Shelf Type | Shelf Depth |
|-----------------------------|-----------------------------|------------|-------------|
| Black Textured | Beige Textured | | |
| 19" Width | | | |
| RSVS1918BK1 | RSVS1918CG1 | Vented | 18" |
| RSVS1921BK1 | RSVS1921CG1 | Vented | 21" |
| RSVS1926BK1 | RSVS1926CG1 | Vented | 26" |
| RSVS1931BK1 | RSVS1931CG1 | Vented | 31" |
| RSUS1918BK1 | RSUS1918CG1 | Unvented | 18" |
| RSUS1921BK1 | RSUS1921CG1 | Unvented | 21" |
| RSUS1926BK1 | RSUS1926CG1 | Unvented | 26" |
| RSUS1931BK1 | RSUS1931CG1 | Unvented | 31" |
| 24" Width | | | |
| RSVS2418BK1 | RSVS2418CG1 | Vented | 18" |
| RSVS2421BK1 | RSVS2421CG1 | Vented | 21" |
| RSVS2426BK1 | RSVS2426CG1 | Vented | 26" |
| RSVS2431BK1 | RSVS2431CG1 | Vented | 31" |
| RSUS2418BK1 | RSUS2418CG1 | Unvented | 18" |
| RSUS2421BK1 | RSUS2421CG1 | Unvented | 21" |
| RSUS2426BK1 | RSUS2426CG1 | Unvented | 26" |
| RSUS2431BK1 | RSUS2431CG1 | Unvented | 31" |

Vented



Unvented



Accessories



Hammond Manufacturing Co. Ltd.
394 Edinburgh Rd. North
Guelph, Ontario N1H 1E5 CANADA
© Phone: 519-822-2960 Fax: 519-822-0715



Hammond Manufacturing Co. Inc.
475 Cayuga Rd. #100
Cheektowaga, NY 14225 USA
Phone: 716-630-7030 Fax: 716-630-7042