

# Voice/Data/Video

**NEW!**

## ProTech™ Kits

For data and coaxial cable installations



Cat No.	Product	Description	ProTech™ Data VDV026-831	ProTech™ Coaxial VDV011-832	ProTech™ Data & Coaxial VDV001-833
VDV000-133	 VDV ProTech™ Transport	Lightweight tool case with 12 organizational compartments for small parts and a large, open section to hold hand tools	●	●	●
VDV824-632	 Strain Relief Boot for Modular Data Plug – RJ45	Protects from wear and tear as well as minimizes cable bending that can reduce data speed	● 10 pack		● 10 pack
VDV826-600	 Telephone Plug - RJ11 - 6P6C	Thick 50 micro-inch gold-plated and 3-pronged contacts with durable housing – for 1, 2 or 3 line telephones	● 25 pack		● 25 pack
VDV826-603	 Modular Data Plug – RJ45 - CAT6	Thick 50 micro-inch gold-plated and 3-pronged contacts with durable housing – 8 position, 8 contact 3-piece design for solid and stranded wire	● 25 pack		● 25 pack
VDV826-628	 Modular Data Plug – RJ45 - CAT5e	Thick 50 micro-inch gold-plated and 3-pronged contacts with durable housing – 8 position, 8 contact for solid or stranded wire	● 10 pack (x2)		● 10 pack (x2)
VDV812-606	 Universal F Compression Connector – RG6/6Q	Patented universal sleeve technology installs up to 5X faster and fits all diameter variations of RG6/6Q cable		● 10 pack (x2)	● 10 pack (x2)
VDV812-615	 Universal F Compression Connector – RG59	Patented universal sleeve technology installs up to 2X faster and fits all diameter variations of RG59 cable		● 10 pack	● 10 pack
VDV812-623	 F Compression Connector – RG6	All metal construction with dual O-ring to seal out moisture – satellite provider approved		● 10 pack (x2)	● 10 pack (x2)
VDV813-607	 Universal BNC Compression Connector – RG6/6Q	Patented universal sleeve technology installs up to 5X faster and fits all diameter variations of RG6/6Q cable.		● 10 pack	● 10 pack
VDV813-616	 Universal BNC Compression Connector - RG59	Patented universal sleeve technology installs up to 2X faster and fits all diameter variations of RG59 cable		● 10 pack	● 10 pack
2100-8	 Free-Fall Snip – Stainless Steel	Stainless steel blades maintain blade durability and sharpness when cutting 19 and 23 AWG wire	●		●
VDV226-107	 Compact Ratcheting Modular Crimper	All inclusive tool cuts, strips and crimps data cables and modular data plugs	●		●
VDV211-048	 Compression Crimper – Compact, Multi-Connector	Crimps compression (F, BNC, RCA) connectors to coaxial cable		●	
VDV211-063	 Compression Crimper-Lateral, Multi-Connector	One tool crimps most compression (F, BNC, RCA) connectors to most coaxial cables including Mini-Coax, RG58, RG59, RG62, RG6Q, RG7 and RG11			●
VDV110-061	 Coax Cable Stripper – 2-Level, Radial	Provides one step, two-level stripping: 5/16" (7.9 mm) and 1/4" (6.4 mm)		●	●
63020	 Multi-Cable Cutter Klein-Kurve®	Cutter has a wide range of blades designed to cut various types of cable including solid and stranded copper wire, RG-59, RG6Q and RG-62 coaxial cable as well as other conductors		●	●

# Voice/Data/Video

## Modular/Coax Connectors and Accessories

### Klein Tools' Universal Compression Connector


Installs up to  
**5x faster!**



Compact ferrule

**Patented universal sleeve design** provides excellent holding power and signal strength.

### Standard Compression Connector



Full ferrule

### Modular Connector



Klein's data and telephone plugs are professional-grade and deliver consistent, reliable performance. They feature thick 50 micro-inch gold plating on the contact plates, three-pronged solid and stranded wire contacts, and durable connector housings.

## Universal Compression Connectors

- Fit all manufacturers' diameter variations within a cable series.

### F • RG6-RG6Q



VDV812-612

### BNC • RG6-RG6Q



VDV813-613

### RCA • RG6-RG6Q



VDV813-614

### F • RG59



VDV812-615

### BNC • RG59



VDV813-619

### RCA • RG59



VDV813-620

Cat. No.	Connector Type	Cable Type	Pack Qty.
VDV812-618	F-Connector	RG59	50
VDV812-612	F-Connector	RG6 - RG6Q	50
VDV813-619	BNC Connector	RG59	35
VDV813-613	BNC Connector	RG6 - RG6Q	35
VDV813-620	RCA Connector	RG59	35
VDV813-614	RCA Connector	RG6 - RG6Q	35

## Compression Connectors

- Full ferrule design.



VDV812-623

Cat. No.	Connector Type	Cable Type	Pack Qty.
VDV812-623	F-Connector	RG6	10
VDV812-624	F-Connector	RG6	50



## RJ45 Modular Data/RJ11 Telephone Plugs

- Three-pronged contacts for more reliable connections.



VDV826-628



VDV826-600



VDV826-604  
(26-22 AWG)



VDV826-605  
(26-19 AWG)

Cat. No.	Connector Type	Cable Type	Position & Contacts	Pack Qty.
VDV826-628	RJ45	CAT 5 / CAT 5e	8C8P	10
VDV826-602	RJ45	CAT 5 / CAT 5e	8C8P	50
VDV826-611	RJ45	CAT 5 / CAT 5e	8C8P	100
VDV826-603	RJ45	CAT 6	8C8P	25
VDV826-601	RJ11	CAT 4	6P4C	25
VDV826-600	RJ11	CAT 4	6P6C	25
VDV826-604	UY	twisted pair	2P2C	25
VDV826-605	UR	twisted pair	3P3C	25

