


Low Voltage / Telecommunication

Cable Supports



Features

- Extra-wide base provides cable support on a flat surface, eliminating kinking, bending and crimping
- Accommodates category 5, fiber optic cable and innerduct
- Available in 1-5/16 in. and 2 in. diameter size cable support clips
- Complies with UL, CSA, NEC and EIA/TIA requirements for structured cabling systems
- Supports 100 lb. per hook static load limit
- VJ Series cable support clips can be snapped together with VB-10 hanger bracket without hardware or tools




Fig. 1




Fig. 2




Fig. 3

Cat. No.	Fig. No.	Description	Qty. Per Box
Cable Support Hook			
SSF-VJ1 5/16-UC	1	Cable support hook, 1-5/16 in. diameter clip to #12 drop wire thru 3/8 in. rod	25
SSF-VJ2-UC	1	Cable support hook, 2 in. diameter clip to #12 drop wire thru 3/8 in. rod	
SSF-VJ1 5/16-AB	2	Cable support hook, 1-5/16 in. diameter clip rotates 360°	
SSF-VJ2-AB	2	Cable support hook, 2 in. diameter clip rotates 360°	
SSF-VJ1 5/16-A7	3	Cable support hook, 1-5/16 in. diameter clip to acoustical tee	
SSF-VJ2-A7	3	Cable support hook, 3 in. diameter clip to acoustical tee	




Fig. 4




Fig. 5





Fig. 6



Cat. No.	Fig. No.	Description	Static Load Limit	Qty. Per Box
Cable Support Hook				
SSF-VJ1 5/16-H1/4-AB	4	Cable support hook, 1-5/16 in. diameter clip to 1/8 in. to 1/4 in. flange, rotates 360°	100	25
SSF-VJ1 5/16-H1/2-AB	4	Cable support hook, 1-5/16 in. diameter clip to 5/16 in. to 1/2 in. flange, rotates 360°		
SSF-VJ1 5/16-H13/4-AB	4	Cable support hook, 1-5/16 in. diameter clip to 9/16 in. to 3/4 in. flange, rotates 360°		
SSF-VJ2-H1/4-AB	4	Cable support hook, 2 in. diameter clip to 1/8 in. to 1/4 in. flange, rotates 360°		
SSF-VJ2-H1/2-AB	4	Cable support hook, 2 in. diameter clip to 5/16 in. to 1/2 in. flange, rotates 360°		
SSF-VJ2-H13/4-AB	4	Cable support hook, 2 in. diameter clip to 9/16 in. to 3/4 in. flange, rotates 360°		
SSF-VJ1 5/16-V1/4	5	Cable support hook, 1-5/16 in. diameter clip to 3/32 in. to 9/32 in. vertical flange		
SSF-VJ2-V1/4	5	Cable support hook, 2 in. diameter clip to 3/32 in. to 9/32 in. vertical flange		
SSF-VJ1 5/16-A1/4	6	Cable support hook, 1-5/16 in. diameter clip to 1/6 in. to 1/4 in. Z purlin		
SSF-VJ2-A1/4	6	Cable support hook, 2 in. diameter clip to 1/6 in. to 1/4 in. Z purlin		