


Selection and ordering data

For contactors	Version	Rated control supply voltage U_s ¹⁾		DT	Article No. ²⁾	Price per PU	PU (UNIT, SET, M)	PKG ²⁾	PG
		AC operation	DC operation						
Type		V AC	V DC						

Surge suppressors without LED (also for spring-type terminals)

Size S00



3RT2916-1B.00

For plugging onto the front side of the contactors
(with and without auxiliary switch block)

For contactors	Version	Rated control supply voltage U_s ¹⁾	DT	Article No. ²⁾	Price per PU	PU (UNIT, SET, M)	PKG ²⁾	PG
Type		V AC	V DC					
3RT2.1, 3RH2.	Varistors	24 ... 48	24 ... 70	▶	3RT2916-1BB00	1	1 unit	41B
		48 ... 127	70 ... 150	▶	3RT2916-1BC00	1	1 unit	41B
		127 ... 240	150 ... 250	▶	3RT2916-1BD00	1	1 unit	41B
		240 ... 400	--	▶	3RT2916-1BE00	1	1 unit	41B
		400 ... 600	--	A	3RT2916-1BF00	1	1 unit	41B
3RT2.1, 3RH2.	RC elements	24 ... 48	24 ... 70	▶	3RT2916-1CB00	1	1 unit	41B
		48 ... 127	70 ... 150	▶	3RT2916-1CC00	1	1 unit	41B
		127 ... 240	150 ... 250	▶	3RT2916-1CD00	1	1 unit	41B
		240 ... 400	--	A	3RT2916-1CE00	1	1 unit	41B
		400 ... 600	--	A	3RT2916-1CF00	1	1 unit	41B
3RT2.1, 3RH2.	Noise suppression diodes	--	12 ... 250	▶	3RT2916-1DG00	1	1 unit	41B
3RT2.1, 3RH2.	Diode assemblies (diode and Zener diode) for DC operation	--	12 ... 250	▶	3RT2916-1EH00	1	1 unit	41B

Size S0



3RT2926-1E.00

For plugging onto the front side of the contactors
(prior to mounting of the auxiliary switch block)

For contactors	Version	Rated control supply voltage U_s ¹⁾	DT	Article No. ²⁾	Price per PU	PU (UNIT, SET, M)	PKG ²⁾	PG
Type		V AC	V DC					
3RT2.2	Varistors	24 ... 48	24 ... 70	▶	3RT2926-1BB00	1	1 unit	41B
		48 ... 127	70 ... 150	▶	3RT2926-1BC00	1	1 unit	41B
		127 ... 240	150 ... 250	▶	3RT2926-1BD00	1	1 unit	41B
		240 ... 400	--	▶	3RT2926-1BE00	1	1 unit	41B
		400 ... 600	--	A	3RT2926-1BF00	1	1 unit	41B
3RT2.2	RC elements	24 ... 48	24 ... 70	▶	3RT2926-1CB00	1	1 unit	41B
		48 ... 127	70 ... 150	▶	3RT2926-1CC00	1	1 unit	41B
		127 ... 240	150 ... 250	▶	3RT2926-1CD00	1	1 unit	41B
		240 ... 400	--	A	3RT2926-1CE00	1	1 unit	41B
		400 ... 600	--	A	3RT2926-1CF00	1	1 unit	41B
3RT2.2	Diode assembly for DC operation	--	24	▶	3RT2926-1ER00	1	1 unit	41B
		--	30 ... 250	▶	3RT2926-1ES00	1	1 unit	41B

Size S2 **NEW**

3RT2936-1B.00

For plugging onto the front side of the contactors
(prior to mounting of the auxiliary switch block)

For contactors	Version	Rated control supply voltage U_s ¹⁾	DT	Article No. ²⁾	Price per PU	PU (UNIT, SET, M)	PKG ²⁾	PG
Type		V AC	V DC					
3RT2.3.	Varistors	24 ... 48	24 ... 70	▶	3RT2936-1BB00	1	1 unit	41B
		48 ... 127	70 ... 150	▶	3RT2936-1BC00	1	1 unit	41B
		127 ... 240	150 ... 250	▶	3RT2936-1BD00	1	1 unit	41B
		240 ... 400	--	B	3RT2936-1BE00	1	1 unit	41B
		400 ... 600	--	B	3RT2936-1BF00	1	1 unit	41B
3RT2.3.	RC elements	24 ... 48	24 ... 70	▶	3RT2936-1CB00	1	1 unit	41B
		48 ... 127	70 ... 150	▶	3RT2936-1CC00	1	1 unit	41B
		127 ... 240	150 ... 250	▶	3RT2936-1CD00	1	1 unit	41B
		240 ... 400	--	B	3RT2936-1CE00	1	1 unit	41B
		400 ... 600	--	B	3RT2936-1CF00	1	1 unit	41B
3RT2.3.	Diode assembly for DC operation	--	24	▶	3RT2936-1ER00	1	1 unit	41B
		--	30 ... 250	▶	3RT2936-1ES00	1	1 unit	41B



3RT2936-1E.00

¹⁾ Can be used for AC operation for 50/60 Hz.
Please inquire about further voltages.

²⁾ For packs of 10 or 5 units, "-Z" and order code "X90" must be added to the article number.