









F-Style Coaxial Connectors System

- Nickel plated for corrosion resistance

F-STYLE CONNECTORS

DESCRIPTION						RECOMMENDED TOOL			
						STRIPPER		CRIMPER	
CONNECTOR TYPE	CABLE TYPE	QUANTITY	CAT. NO.	UPC NO.	CAT. NO.	UPC NO.	CAT. NO.	UPC NO.	
	'F' Connector Twist-on	RG59	10/Pack	45735	45735	45576	45576		
			50/Pack	45749	45749	45578	45578		
						45677	45677		
	'F' Connector Crimp	RG59	10/Pack	45734	45734	45576	45576	46801	46801
			50/Pack	45748	45748	45578	45578		
						45677	45677		
	'F' Connector Twist-on	RG6	10/Pack	45327	45327	45576	45576		
			50/Pack	45328	45328	45578	45578		
						45677	45677		
	'F' Connector Crimp	RG6	10/Pack	45315	45315	45576	45576	46801	46801
			50/Pack	45316	45316	45578	45578		
						45677	45677		
	'F' Connector Crimp	RG59 Quad-shield	10/Pack	45321	45321	45576	45576	46801	46801
			50/Pack	45322	45322	45578	45578		
						45677	45677		
	'F' Connector Crimp	RG6 Quad-shield	10/Pack	45323	45323	45576	45576	46801	46801
			50/Pack	45324	45324	45578	45578		
						45677	45677		

F-STYLE ADAPTERS

DESCRIPTION			
ADAPTER/TERMINATOR TYPE	QUANTITY	CAT. NO.	UPC NO.
 'F' Female Adapter	5/Pack	45325	45325
 'F' Terminator	5/Pack	45326	45326

XFC Series Weatherproof Compression F-Style Connectors



- Dual-protection with external sleeve and internal o-ring.
- 360-degree sleeve crimp prevents moisture migration.
- O-ring provides internal seal when the 7/16" nut is tightened.
- Use for both indoor and outdoor applications.
- Color-coded sleeves for easy identification of cable compatibility.
- 70 lbs pull-out strength exceeds SCTE cable retention standard IPS-SP-405.
- Terminates easily using any compression tool.

CAT. NO.	UPC NO.	DESCRIPTION
XFC-6-10	12578	RG6 - 10 Pack
XFC-6-50	12586	RG6 - 50 Pack
XFC-6-100	12587	RG6 - 100 Pack
XFC-6Q-10	12589	RG6 Quad - 10 Pack
XFC-6Q-50	12590	RG6 Quad - 50 Pack
XFC-6Q-100	12591	RG6 Quad - 100 Pack
XFC-59-10	12593	RG59 - 10 Pack
XFC-59-50	12594	RG59 - 50 Pack
XFC-59-100	12595	RG59 - 100 Pack

Communications

USA
Tel: 800.435.0786
Fax: 800.451.2632

CANADA
Tel: 800.435.0786
Fax: 800.524.2653

INTERNATIONAL
Tel: +1.815.397.7070
Fax: +1.815.397.9247