MEASURING TAPES

High-Strength Polyaramid Measuring/Pulling Tapes



- Pull small cables or install pull rope for large cable pulling jobs.
- Made of Polyaramid (equivalent to Kevlar®*), will not rot or deteriorate. Can be left in ducts indefinitely for future use.
- · Low stretch properties make measurements accurate.
- Printed measurements every foot from zero to 3000' (914 m).
- Use 406 Dispenser (see page 165).

CAT. NO. UPC NO. DESCRIPTION	
39243 39243 Conduit Measuring Tape 1/4" × 3000' (6.4 mm	× 914 m)
39244 39244 Conduit Measuring Tape 3/8" × 3000' (9.5 mm	× 914 m)
39245 39245 Conduit Measuring Tape 1/2" × 3000' (12.7 mn	n × 914 m)

SPECIFICATIONS

Cat. No.	Average Breaking Strength	Length	Weight
39243	1250 lbs. (5.56 kN)	3000' (914 m)	10.5 lbs. (4.8 kg)
39244	1800 lbs. (8.01 kN)	3000' (914 m)	14.5 lbs. (6.6 kg)
39245	2500 lbs. (11.12 kN)	3000' (914 m)	18 lbs. (8.2 kg)

* Kevlar is a registered trademark of E. I. DuPont, Inc.

High-Strength Polyester Measuring/Pulling Tapes



advotas entitas: areata tates tates

- Durable and stretch-resistant tape for easily pulling and installing wire and fiber optic cables within PVC and HDPE ducts.
- Factory-lubricated to reduce burn-through in innerduct.
- Easy-to-read footage markings for quick and accurate measurements.
- Available in various tensile strengths for use in any application.

	CAT. NO.	UPC NO.	DESCRIPTION
1	4435	10445	Polyester Measure/Pulling Tape 1/2" x 3,000' (12.7 mm x 914m)
	4436	10446	Polyester Measure/Pulling Tape 5/8" x 3,000' (15.9 mm x 914m)
	4437	10447	Polyester Measure/Pulling Tape 3/4" x 3,000' (19.1 mm x 914m)

SPECIFICATIONS

Cat. No.	Average Breaking Strength	Length	Weight
4435	1250 lbs. (5.56 kN)	3000' (914 m)	23.6 lbs. (10.7 kg)
4436	1800 lbs. (8.01 kN)	3000' (914 m)	31.2 lbs. (14.2 kg)
4437	2500 lbs. (11.12 kN)	3000' (914 m)	39.4 lbs. (17.9 kg)

Polyester Measuring Tape and Dispenser



- Fish and measure conduit runs in one operation.
- · Permanently printed measurements every foot from zero to 3000' (914 m).
- Made of strong, waterproof polyester.
- · Pay-out dispenser has anti-skid pads, handle and built-in cutter.

CAT. NO.	UPC NO.	DESCRIPTION	
435 434	21562 21875	Conduit Measuring Tape 3/16" \times 3000' (4.8 mm \times 914 m) Pay-Out Dispenser for 435 Conduit Measuring Tape	
SPECIFICATIONS			
Size	3000' (914 m)		
Capacity	170	170 lbs. (756 kN) average breaking strength	
Weight		135: 4.4 lbs. (2.0 kg), 434: 3.5 lbs. (1.6 kg)	

USA Tel: 800.435.0786 Fax: 800.451.2632