

Weatherproof Metallic Boxes

Deep Boxes — Single- and Multi-Gang

CAT. NO.	HUB SIZE (IN.)	OUTLETS	
Three Outlets			
IHD3-1•	½	Top	1
IHD3-2•	¾	Bottom	1
IHD3-3•	1	Back	1
TOTAL			3



Four Outlets

IHD4-1•	½	Top	2
IHD4-2•	¾	Bottom	1
		Back	1
TOTAL			4



Two-Gang Five Outlets

2IHD5-1•	½	Top	2
2IHD5-2•	¾		
2IHD5-3•	1	Bottom	2
		Back	1
TOTAL			5



Three-Gang Seven Outlets

3IHD7-2•	¾	Top	3
3IHD7-3•	1	Bottom	3
		Back	1
TOTAL			7



Close-Up Plugs — Zinc

CAT. NO.	COLOR	HUB SIZE (IN.)
PLG-1-RD	Silver	½
PLG-2-RD	Silver	¾
PLG-3-RD	Silver	1

D-PAK®

CAT. NO.	COLOR	HUB SIZE (IN.)
DPLG-1	Silver	½
DPLG-1-BR	Bronze	½
DPLG-1-WH	White	½
DPLG-2	Silver	¾



Extensions — Single-Gang

CAT. NO.	HUB SIZE (IN.)	OUTLETS	DESCRIPTION
No Outlets — 1" Deep			
IHE	N/A	0	Extension Ring for One-Gang Box with Gasket and Screws



Four Outlets — 1½" Deep

IHE4-1	1/2	Top	2	4-Hole Extension Ring for One-Gang Box with 4 Plugs, Gasket and Screws
		Bottom	2	
TOTAL			4	



Two Outlets, Flanged — 1½" Deep Add-On

IHEF2-1	½	Top	1	2-Hole Flanged Box Extension Adapter with 1 Plug Gasket and Screws
		Bottom	1	
IHEF2-2	¾			
TOTAL			2	



Six Outlets, Flanged — 1½" Deep Add-On

IHEF6S2-1	½	Top	2	6-Hole Flanged Box Extension Adapter with 4 Plugs, Gasket and Screws
		Bottom	2	
IHEF6S2-2	¾	Side	1	
		Side	1	
TOTAL			6	



Extensions — Two-Gang

CAT. NO.	HUB SIZE (IN.)	OUTLETS	DESCRIPTION
Deep			
2IHE	N/A	0	Extension Ring for Two-Gang Boxes with Gasket and Screws



Extensions — Round

CAT. NO.	HUB SIZE (IN.)	OUTLETS	DESCRIPTION
Four Outlets — 1½" Deep			
SE-47	½	4	Round Extension with Gasket and Screws
SE-48	¾	4	



Mounting Lugs

CAT. NO.	DESCRIPTION
LM	2 Mounting Lugs with Self-Tapping Screws, for LM Boxes Only

