

Ceiling/Acoustical



Ceiling/Acoustical

Ceiling/Acoustical


Independent Electrical Drop Wire/Rod Securing Clips

Plastic Electrical Drop Wire Securing Clip

- Helps prevent sway of dedicated electrical drop wire/rod
- Will not affect ceiling grid systems negatively
- No tools required for installation
- Forgiving design doesn't require exact cutting of rod/wire
- Easy identification by the inspector
- Plenum rated



Material: Polypropylene
Finish: Plain

Part Number	Description	
EC311P	1/4" Hole	100 pc

Consult local authority for application approval. Refer to NEC® 300.13.



Independent Support Clip

- Provides a means of independent support of fixtures
- No tools required for installation
- Includes mounting hardware



Material: Spring Steel
Finish: CADDY® ARMOUR



Part Number	Description			Certifications
IDS	15/16" T-Grid, 5/8" Screw Length, Washer-Wing Nut	65 lb	100 pc	UL
IDS15	15/16" T-Grid, 1 1/2" Screw Length, Washer-Wing Nut	65 lb	100 pc	UL
IDS2	15/16" T-Grid, 2" Screw Length, Washer-Wing Nut	65 lb	100 pc	UL
IDS9	9/16" T-Grid, 5/8" Screw Length, Washer-Wing Nut	65 lb	100 pc	UL
IDS915	9/16" T-Grid, 1 1/2" Screw Length, Washer-Wing Nut	65 lb	100 pc	-
IDS95	9/16" T-Grid, 5/8" Screw Length, Washer-Wing Nut	65 lb	100 pc	UL
IDS95LN	9/16", 15/16" T-Grid, 5/8" Screw Length	65 lb	100 pc	-
IDS95T	9/16" T-Grid, 9/16" Screw Length, Pal Nut, Washer-Wing Nut	65 lb	100 pc	-
IDS95TWB	9/16", 15/16" T-Grid, 9/16" Screw Length, Brass Barrel Nut	65 lb	100 pc	-
IDS9LN	9/16" T-Grid, 5/8" Screw Length	65 lb	100 pc	-
IDS9T	9/16" T-Grid, 9/16" Screw Length, Pal Nut	65 lb	100 pc	-
IDS9TWB	9/16" T-Grid, 9/16" Screw Length, Brass Barrel Nut	65 lb	100 pc	-
IDSLN	15/16" T-Grid, 5/8" Screw Length	65 lb	100 pc	-
IDST	15/16" T-Grid, 9/16" Screw Length, Pal Nut	65 lb	100 pc	-
IDSTWB	15/16" T-Grid, 9/16" Screw Length, Brass Barrel Nut	65 lb	100 pc	-

IDS9 for use with Ultra Line 3500, AWW Ultra Line 3600 (a trademark product of Chicago Metallics Corp.)