


525 SERIES™ SERVICE FITTINGS


525 Series Service Fittings Ordering Information

525RT Four-Piece Communication Service Fitting




Includes faceplate with opening one side. Ortronics® Series II and TracJack adapters included.

525D Four-Piece Communication Service Fitting




1 1/4" [32mm] I.D. grommets hole on both sides.

525ACT Four-Piece Communication Service Fitting




6A opening with communication adapter on one side. Accommodates Wiremold Open System communication modules.

525F Four-Piece Power Service Fitting




Duplex opening one side. Receptacle not included.

525A Four-Piece Communication Service Fitting




1" [25mm] I.D. grommets hole one side. Blank plate other side.

525G Four-Piece Power Service Fitting




Duplex opening both sides. Receptacles not included.

525B Four-Piece Communication Service Fitting




1" [25mm] I.D. grommets hole two sides.

525H Four-Piece Power Service Fitting




20A 125V duplex plate one side. Blank plate other side. 20A 125V Receptacle included.

525C Four-Piece Communication Service Fitting



1 1/4" [32mm] I.D. grommets hole one side. Blank plate other side.

525I Four-Piece Power Service Fitting




20A 125V duplex plate two sides. 20A 125V Receptacles included.

NOTE: Four-piece service fittings include: housing and base plate. Receptacles included when indicated in part number description. 525 Series Service Fittings have 27 cubic inches [442ml] of capacity.

WALKERDUCT® UNDERFLOOR DUCT SYSTEMS

Walkerduct Underfloor Duct Systems Service Fitting Compatibility



| PRODUCT FAMILY | CATALOG NUMBER | ACTIVATION LOCATION | | SERVICE CAPACITY | | | SERVICE COMPATIBILITY | | | MATERIAL/COLORS | | | | |
|---|----------------|---------------------|----------|------------------|--------------|----------------|-----------------------|---------------|--------------|-----------------|----------|-------|------|-------|
| | | Flush | Pedestal | Single Service | Dual Service | Triple Service | Power | Communication | Audio/Visual | Polycarbonate | Aluminum | Brass | Gray | Black |
|  | 817B | • | | • | | | • | • | | | | • | | |
| | 827B | • | | | • | | • | • | | | | • | | |
| | 837B | • | | | | • | • | • | | | | • | | |
| | 817PCC | • | | • | | | • | • | | • | | | | • |
| | 827PCC | • | | | • | | • | • | | • | | | | • |
| | 837PCC | • | | | | • | • | • | | • | | | | • |
| | 818TCAL | • | | • | | | • | • | | | • | | | |
| | 828TCAL | • | | | • | | • | • | | | • | | | |
| | 838TCAL | • | | | | • | • | • | | | • | | | |
|  | S165B | • | | • | | | • | | | | | • | | |
| | S165BLK/BRN | • | | • | | | | | | • | | | | • |
| | S166B | • | | • | | | | • | | | | • | | |
| | S166BLK/BRN | • | | • | | | | • | | • | | | | • |
| | S175BLK/BRN | • | | • | | | • | | | • | | | | • |
|  | PSRC9TC | • | | • | | | • | | | | • | • | • | • |
| | PSRC9AMDTC | • | | • | | | | • | | | • | • | • | • |
| | PSRC9FFTC | • | | • | | | | • | | | • | • | • | • |
|  | 1204BF | | • | • | | | | • | | | | • | | |
| | 1204AL | | • | • | | | | • | | | • | | | |
| | 1223BF | | • | • | | | • | | | | | • | | |
| | 1223AL | | • | • | | | • | | | | • | | | |
|  | MP4 | | • | • | | | • | • | • | | • | | | |
| | MP8 | | • | | • | | • | • | • | | • | | | |
| | MP8-1 | | • | | • | | • | • | • | | • | | | |
|  | 525A | | • | • | | | | • | • | | • | | | |
| | 525B | | • | • | | | | • | • | | • | | | |
| | 525C | | • | • | | | | • | • | | • | | | |
| | 525D | | • | • | | | | • | • | | • | | | |
| | 525F | | • | • | | | • | | | | • | | | |
| | 25G | | • | • | | | • | | | | • | | | |
| | 525H | | • | • | | | • | | | | • | | | |
| | 525I | | • | • | | | • | | | | • | | | |
| | 525J | | • | • | | | • | • | • | | • | | | |
| | 525RT | | • | • | | | | • | | | • | | | |
| 525ACT | | • | • | | | | • | | | • | | | | |

FLUSHDUCT INFLOOR DUCT SYSTEMS

Flushduct Quick Selection Guide





| DUCT | 1-DUCT SYSTEM | 2-DUCT SYSTEM | 3-DUCT SYSTEM |
|-------------------------------------|--------------------------------------|--------------------------------------|--------------------------------------|
| BLANK | 12F-0 | 222F-0 | 3222F-0 |
| STAGGERED 1 5/8" [41mm] OPENINGS | 12FST | 222FST | 3222FST |
| JUNCTION BOX | 12FB | 222FB | 3222FB 3222FBCC |
| ACCESSORIES | 1-DUCT SYSTEM | 2-DUCT SYSTEM | 3-DUCT SYSTEM |
| COUPLINGS | 12FC | 222FC | 3222FC |
| COUPLINGS/SUPPORTS | 12FCS 12FCSA-* | 222FCS 222FCSA-* | 3222FCS 3222FCSA-* |
| BOX OPENING CLOSURES | 12F-WS | 222F-WS | 3222F-WS |
| DUCT CONDUIT ADAPTERS | 312F-* 314F-* 324- | 312F-* 314F-* 324- | 312F-* 314F-* 324-* |
| BOX CORNER CONDUIT ADAPTER | 255-* | 255-* | 255-* |
| DUCT END CLOSURE | 304 | 304 | 304 |
| VERTICAL ELBOWS | 332F 336F | 333F-2 336F-2 | 336F-3 |
| TERMINAL BUSHINGS | 334UF | 334F-1-2 | 334F-1-3 |
| HORIZONTAL ELBOWS | 338UF 342F | 338F-2 342F-2 | 338F-3 342F-3 |
| OFFSET | 372F | 372F | 372F |
| CROSSUNDERS | 362F | 362F-2 | 362F-3 |
| DUCT OUTLET FLANGE | 455F-1 | 455F-1 | 455F-1 |
| FERRULE | 450F-1 | 450F-1 | 450F-1 |
| CRIMPING TOOL | 470F-1 | 470F-1 | 470F-1 |
| DUCT OPENING PLUGS | 7140F 7141F 455FP-1 450FP-1 | 7140F 7141F 455FP-1 450FP-1 | 7140F 7141F 455FP-1 450FP-1 |
| SEALANT | 290G | 290G | 290G |
| TAPE | H296 | H296 | H296 |

Flushduct Infloor Duct Systems Service Fitting Compatibility

| PRODUCT FAMILY | CATALOG NUMBER | ACTIVATION LOCATION | SERVICE CAPACITY | | SERVICE COMPATIBILITY | | | MATERIAL/COLORS |
|---|----------------|---------------------|------------------|--------------|-----------------------|---------------|--------------|-----------------|
| | | Pedestal | Single Service | Dual Service | Power | Communication | Audio/Visual | Aluminum |
|  | Multiplex | MP4 | • | • | | • | • | • |
| | MP8 | • | | • | • | • | • | • |
| | MP8-1 | • | | • | • | • | • | • |
|  | 525 Series | 525A | • | • | | • | • | • |
| | | 525B | • | • | | • | • | • |
| | | 525C | • | • | | • | • | • |
| | | 525D | • | • | | • | • | • |
| | | 525F | • | • | | • | | • |
| | | 525G | • | • | | • | | • |
| | | 525H | • | • | | • | | • |
| | | 525I | • | • | | • | | • |
| | | 525J | • | • | | • | • | • |
| | | 525RT | • | • | | • | • | • |
| | | 525ACT | • | • | | • | • | • |

WALKERCELL® CELLULAR RACEWAY SYSTEMS

Walkercell Service Fitting Compatibility

| PRODUCT FAMILY | CATALOG NUMBER | ACTIVATION LOCATION | | | SERVICE CAPACITY | | | SERVICE COMPATIBILITY | | | MATERIAL/COLORS | | | | | |
|--|----------------|---------------------|----------|----------|------------------|--------------|----------------|-----------------------|---------------|--------------|-----------------|-------|------|-------|--------|--------|
| | | Flush | Recessed | Pedestal | Single Service | Dual Service | Triple Service | Power | Communication | Audio/Visual | Aluminum | Brass | Gray | Black | Nickel | Bronze |
|  FloorPort | FPCTC Series | | • | | | | • | • | • | • | • | • | • | • | • | • |
| | FPBTC Series | • | | | | | • | • | • | • | • | • | • | • | • | • |
| | FPFFTC Series | • | | | | | • | • | • | • | • | • | • | • | • | • |
| | FPCT Series | | • | | | | • | • | • | • | • | • | • | • | • | • |
| | FPBT Series | | • | | | | • | • | • | • | • | • | • | • | • | • |
| | FPFFT Series | • | | | | | • | • | • | • | • | • | • | • | • | • |
|  1200 Series | 1204BF | | | • | • | | | • | | | | • | | | | |
| | 1204AL | | | • | • | | | • | | | • | | | | | |
| | 1223BF | | | • | • | | | • | | | • | | | | | |
| | 1223AL | | | • | • | | | • | | | • | | | | | |
|  Multiplex | MP4 | | | • | • | | | • | • | • | • | | | | | |
| | MP8 | | | • | | • | | • | • | • | • | | | | | |
| | MP8-1 | | | • | | • | | • | • | • | • | | | | | |
|  525 Series | 525A | | | • | • | | | • | • | • | • | | | | | |
| | 525B | | | • | • | | | • | • | • | • | | | | | |
| | 525C | | | • | • | | | • | • | • | • | | | | | |
| | 525D | | | • | • | | | • | • | • | • | | | | | |
| | 525F | | | • | • | | | • | | | • | | | | | |
| | 525G | | | • | • | | | • | | | • | | | | | |
| | 525H | | | • | • | | | • | | | • | | | | | |
| | 525I | | | • | • | | | • | | | • | | | | | |
| | 525J | | | • | • | | | • | • | • | • | | | | | |
| | 525RT | | | • | • | | | • | • | | • | | | | | |
| | 525ACT | | | • | • | | | • | | | • | | | | | |