


Special Application Breakers

GFCI Personnel Protection (Class A) (5mA)

Breaker Type	Ampere Rating	Complete Breaker UL Unenclosed		UL Interrupting Ratings (KA) (RMS Symmetrical Amperes)	
		Catalog Number	List Price \$	Volts AC	
				120	120/240
QPF 1-Pole 120V AC Plug-In	15	QF115 [®]	175.00	10	
	20	QF120 [®]	175.00	10	
	25	QF125 [®] ■	175.00	10	
	30	QF130 [®]	175.00	10	
QPF 2-Pole 120/240V AC Plug-In	15	QF215 [®]	312.00		10
	20	QF220 [®]	312.00		10
	30	QF230 [®]	312.00		10
	40	QF240 [®]	312.00		10
	50	QF250 [®]	312.00		10
	60	QF260 [®]	312.00		10
QPHF 1-Pole 120V AC Plug-In	15	QF115H [®]	346.00	22	
	20	QF120H [®] ■	346.00	22	
	30	QF130H [®]	346.00	22	



EQF Equipment Protection (30mA)

QE 1-Pole 120V AC Plug-In	15	QE115 [®]	320.00	10	
	20	QE120 [®]	320.00	10	
	30	QE130 [®]	320.00	10	
QE 2-Pole 120/240V AC Plug-In	15	QE215	423.00		10
	20	QE220	423.00		10
	30	QE230	423.00		10
	40	QE240	423.00		10
	50	QE250	423.00		10
	60	QE260 ■	423.00		10



Switching Neutrals

QG 2 Wire Common Trip Plug-In 120V AC	15	QG215	80.00	10	
	20	QG220	80.00	10	
QG 3 Wire Common Trip Plug-In 120/240V AC	20	QG320	116.00		10



HID Lighting

QP 1-Pole 120V AC	15	Q115HID [®] ■	30.00	10	
	20	Q120HID [®]	30.00	10	
	30	Q130HID	30.00	10	
QP 2-Pole 120/240V AC	15	Q215HID	61.00		10
	20	Q220HID ■	61.00		10
	30	Q230HID ■	61.00		10

Surge Arrestor

QP 1-Pole 120/240V AC	(2) 15	QSA1515	179.00		10
	(2) 20	QSA2020	179.00		10
	(2) 20	QSA2020TVSS	259.00		10

AFCI Circuit Breakers (Arc Fault Circuit Interrupter)

QAF 1-Pole 120V AC	15	Q115AF	179.00	10	
	20	Q120AF	179.00	10	
	15	Q115AFH ■	346.00	22	
	20	Q120AFH ■	346.00	22	



■ Built to order. Allow 2-3 weeks for delivery.
 © UL Listed as SWD (Switching Duty) Rated, suitable for
 120V AC Fluorescent Lighting.
 © CSA Listed.

CIRCUIT BREAKERS