

Ceiling/Acoustical





Ceiling/Acoustical

Ceiling/Acoustical T-Grid Twist Clips

Twist Clip with Wing Nut

- Supports electrical fixtures from acoustical T-grid
- 6WN wing nut included
- No tools required for installation



Part Number	Description			Certifications
Material: Spring Steel — Finish: CADDY® ARMOUR				
4G16	15/16" T-Grid, 9/16" Screw Length	50 lb	100 pc	UL
4G161	15/16" T-Grid, 1" Screw Length	50 lb	100 pc	—
4G1615	15/16" T-Grid, 1 1/2" Screw Length	50 lb	100 pc	UL
4G162	15/16" T-Grid, 2" Screw Length	50 lb	100 pc	UL
4G163	15/16" T-Grid, 3" Screw Length	50 lb	100 pc	UL
4G16.375	15/16" T-Grid, 3/8" Screw Length	50 lb	100 pc	—
4G16.5LN	15/16" T-Grid, 1/2" Screw Length	50 lb	100 pc	—
4G16BP	15/16" T-Grid, 9/16" Screw Length	50 lb	1 pc	—
4G16LN	15/16" T-Grid, 9/16" Screw Length	50 lb	100 pc	—
4G16LS	15/16" T-Grid	50 lb	100 pc	—
4G24	1 1/2" T-Grid, 5/8" Screw Length	40 lb	100 pc	—
4G9	9/16" T-Grid, 5/8" Screw Length	40 lb	100 pc	UL
4G915	9/16" T-Grid, 1 1/2" Screw Length	40 lb	100 pc	—
4G9.375	9/16" T-Grid, 3/8" Screw Length	40 lb	100 pc	—
4G9.5LN	9/16" T-Grid, 1/2" Screw Length	40 lb	100 pc	—
4G9LS	9/16" T-Grid	40 lb	100 pc	—
PT16	15/16" T-Grid, 3/4" Screw Length	50 lb	100 pc	—
PT16LN	15/16" T-Grid, 3/4" Screw Length	50 lb	100 pc	—
Material: Spring Steel — Finish: CADDY® ARMOUR, Felt-Lined				
PT16FP	15/16" T-Grid, 3/4" Screw Length	50 lb	100 pc	—
Material: Steel — Finish: Painted				
4G161WH	15/16" T-Grid, 1" Screw Length	50 lb	100 pc	—
4G162WH	15/16" T-Grid, 2" Screw Length	50 lb	100 pc	—
4G16WH	15/16" T-Grid, 9/16" Screw Length	50 lb	100 pc	—

